

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519392

Luminaire Tested: **SQ4-WB-100U-075D-930-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519392
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-100U-075D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5181.2 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519392
CATALOG NUMBER: SQ4-WB-100U-075D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519392

CATALOG NUMBER: SQ4-WB-100U-075D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	96	92	89	85	87	84	81	78	69	67	65	54	53	52	41	41	40	34
2	88	81	76	71	80	74	70	66	61	58	55	49	47	45	38	36	35	30
3	81	72	66	60	74	66	61	56	55	51	47	44	41	39	34	32	31	26
4	75	65	57	52	68	59	53	48	49	45	41	40	37	34	31	29	27	24
5	69	58	51	45	62	53	47	42	45	40	36	36	33	30	29	26	25	21
6	64	52	45	40	58	48	42	37	40	36	32	33	30	27	26	24	22	19
7	59	48	40	35	54	44	37	33	37	32	29	30	27	24	24	22	20	17
8	55	43	36	31	50	40	34	29	34	29	26	28	24	22	23	20	18	16
9	51	40	33	28	47	37	31	26	31	26	23	26	22	20	21	19	17	15
10	48	37	30	25	44	34	28	24	29	24	21	24	21	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12562	12562	12562
5°	12406	12361	12433
10°	11721	11827	12101
15°	10820	11071	11568
20°	9826	10195	10870
25°	8813	9293	10127
30°	7880	8396	9357
35°	6891	7389	8445
40°	5800	6260	7311
45°	4786	5200	6104
50°	3996	4356	5085
55°	3392	3738	4200
60°	2899	3242	3351
65°	2310	2727	2166
70°	2047	2128	1322
75°	1896	1725	809
80°	1748	1589	696
85°	1577	1450	572



TEST NUMBER: P519392

CATALOG NUMBER: SQ4-WB-100U-075D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.9	2.4
10°-20°	324.9	6.3
20°-30°	420.8	8.1
30°-40°	412.0	8.0
40°-50°	315.4	6.1
50°-60°	210.2	4.1
60°-70°	114.7	2.2
70°-80°	47.8	0.9
80°-90°	14.6	0.3
90°-100°	230.4	4.4
100°-110°	635.9	12.3
110°-120°	655.9	12.7
120°-130°	527.0	10.2
130°-140°	414.2	8.0
140°-150°	317.7	6.1
150°-160°	228.3	4.4
160°-170°	139.6	2.7
170°-180°	47.1	0.9
0°-30°	870.5	16.8
0°-40°	1282.6	24.8
0°-60°	1808.1	34.9
0°-90°	1985.2	38.3
90°-120°	1522.1	29.4
90°-150°	2781.0	53.7
90°-180°	3196.0	61.7
0°-180°	5181.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1362	1362	1362	1362	1362	
5°	1340	1326	1335	1338	1342	125
15°	1133	1129	1159	1191	1211	316
25°	866	868	913	953	995	398
35°	612	615	656	700	750	380
45°	367	374	398	429	468	286
55°	211	220	232	241	261	191
65°	106	114	125	109	99	110
75°	53	53	48	33	23	57
85°	15	15	14	9	5	16
90°	2	3	6	7	8	3
95°	34	125	418	172	112	36
105°	113	175	700	1068	1006	121
115°	203	245	564	1116	1269	200
125°	279	317	511	864	1014	248
135°	335	371	497	700	789	259
145°	389	416	490	596	641	243
155°	438	453	486	535	552	202
165°	475	481	489	508	512	134
175°	492	493	490	497	495	47
180°	492	492	492	492	492	

TEST NUMBER: P519392

CATALOG NUMBER: SQ4-WB-100U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1361.6	1361.6	1361.6	1361.6	1361.6
2.5°	1365.0	1352.8	1355.9	1355.8	1352.1
5°	1339.5	1326.1	1334.7	1337.8	1342.5
7.5°	1289.8	1279.6	1295.4	1307.1	1316.6
10°	1251.1	1242.3	1262.4	1279.5	1291.7
12.5°	1206.2	1198.8	1223.7	1246.6	1262.6
15°	1132.8	1128.7	1159.1	1190.6	1211.1
17.5°	1054.3	1052.3	1087.2	1124.0	1150.1
20°	1000.8	1000.2	1038.4	1076.7	1107.1
22.5°	946.7	948.0	988.2	1028.1	1062.7
25°	865.7	868.1	912.9	952.7	994.8
27.5°	790.8	791.9	838.2	880.3	925.1
30°	739.7	742.6	788.1	831.5	878.3
32.5°	688.5	691.9	736.4	781.4	829.0
35°	611.8	614.7	656.0	700.2	749.8
37.5°	532.7	536.7	573.3	615.1	663.9
40°	481.6	487.4	519.8	559.1	607.0
42.5°	432.3	439.6	469.6	506.9	550.1
45°	366.8	373.9	398.5	428.7	467.8
47.5°	310.4	318.5	337.4	363.4	396.8
50°	278.4	286.0	303.5	322.8	354.3
52.5°	250.2	257.8	273.4	288.2	315.1
55°	210.9	219.7	232.4	241.2	261.1
57.5°	178.6	187.1	197.2	201.1	213.2
60°	157.1	166.5	175.7	175.2	181.6
62.5°	137.5	145.5	154.6	148.3	148.6
65°	105.8	114.5	124.9	109.1	99.2
67.5°	85.4	87.3	98.0	76.1	64.3
70°	75.9	75.9	78.9	58.9	49.0
72.5°	66.8	66.8	64.0	47.9	37.5
75°	53.2	53.2	48.4	33.2	22.7
77.5°	41.0	40.5	37.0	24.8	16.5
80°	32.9	32.9	29.9	19.6	13.1
82.5°	25.7	25.7	23.2	15.3	9.8
85°	14.9	14.9	13.7	8.9	5.4
87.5°	5.6	5.9	6.0	4.3	4.0
90°	1.6	3.1	6.3	7.1	7.9
92.5°	14.2	58.8	105.1	38.4	29.9
95°	33.8	124.6	417.9	171.8	111.8
97.5°	56.0	139.6	619.1	476.6	345.2
100°	72.4	148.6	693.4	698.3	567.4
102.5°	88.1	158.8	707.8	862.7	738.7
105°	113.3	174.9	699.7	1068.1	1005.8
107.5°	140.1	194.9	660.6	1167.2	1190.0
110°	159.0	208.2	630.4	1188.5	1262.4

TEST NUMBER: P519392

CATALOG NUMBER: SQ4-WB-100U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.0	223.4	602.1	1171.7	1280.6
115°	203.0	245.4	563.5	1115.5	1268.7
117.5°	226.7	268.8	538.2	1036.5	1210.7
120°	242.4	284.0	528.1	983.0	1158.5
122.5°	257.5	297.2	519.9	933.1	1099.3
125°	278.6	317.1	510.8	864.4	1014.5
127.5°	296.5	335.0	505.4	806.3	935.8
130°	308.5	347.0	502.9	770.8	888.5
132.5°	319.8	356.5	500.4	741.0	847.6
135°	335.3	371.4	496.6	700.1	789.4
137.5°	352.6	385.5	494.7	665.8	742.0
140°	362.0	394.3	493.5	642.9	709.9
142.5°	372.7	402.6	492.2	622.6	681.6
145°	388.8	415.7	490.3	596.0	641.4
147.5°	404.2	427.8	488.6	573.6	608.8
150°	415.5	434.8	487.9	560.2	588.7
152.5°	424.4	442.4	487.3	548.8	572.3
155°	438.4	453.0	486.4	534.8	551.7
157.5°	451.3	462.5	486.5	524.6	536.1
160°	458.8	468.8	487.2	518.8	527.3
162.5°	465.1	473.9	487.8	513.8	520.4
165°	474.6	480.7	488.7	507.7	511.6
167.5°	481.8	485.5	489.5	504.0	505.3
170°	485.6	488.7	489.5	502.1	502.1
172.5°	488.7	490.6	489.5	499.6	499.0
175°	491.9	492.7	489.5	496.6	495.0
177.5°	493.1	492.5	489.4	493.7	492.5
180°	491.9	491.9	491.9	491.9	491.9

(END OF REPORT)