

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519632

Luminaire Tested: **SQ4-WB-150U-125D-930-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519632
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-150U-125D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8061.6 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 83.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519632
CATALOG NUMBER: SQ4-WB-150U-125D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519632

CATALOG NUMBER: SQ4-WB-150U-125D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41				41
1	97	93	89	86	88	85	82	79	70	68	66	56	55	53	43	43	42	36				36
2	89	82	76	72	81	75	70	66	62	59	56	50	48	46	39	38	37	32				32
3	82	73	66	61	74	67	61	57	56	52	48	45	43	40	36	34	32	28				28
4	75	65	58	52	68	60	54	49	50	46	42	41	38	35	33	31	29	25				25
5	69	59	51	46	63	54	48	43	45	41	37	37	34	31	30	28	26	22				22
6	64	53	45	40	59	49	42	38	41	36	33	34	31	28	28	25	23	20				20
7	59	48	41	35	54	45	38	33	38	33	29	31	28	25	25	23	21	18				18
8	55	44	37	32	51	41	34	30	35	30	26	29	25	23	24	21	19	17				17
9	52	40	33	28	47	37	31	27	32	27	24	27	23	21	22	19	18	15				15
10	48	37	30	26	44	34	28	24	30	25	22	25	21	19	21	18	16	14				14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20682	20682	20682
5°	20424	20351	20470
10°	19296	19472	19923
15°	17814	18226	19044
20°	16177	16784	17896
25°	14510	15301	16672
30°	12973	13822	15404
35°	11344	12164	13903
40°	9548	10307	12037
45°	7880	8561	10049
50°	6580	7172	8372
55°	5585	6154	6914
60°	4774	5336	5517
65°	3801	4488	3565
70°	3369	3501	2177
75°	3119	2841	1333
80°	2874	2614	1148
85°	2604	2392	942



TEST NUMBER: P519632

CATALOG NUMBER: SQ4-WB-150U-125D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.6	2.6
10°-20°	534.8	6.6
20°-30°	692.7	8.6
30°-40°	678.4	8.4
40°-50°	519.3	6.4
50°-60°	346.0	4.3
60°-70°	188.8	2.3
70°-80°	78.7	1.0
80°-90°	23.8	0.3
90°-100°	345.5	4.3
100°-110°	934.2	11.6
110°-120°	982.2	12.2
120°-130°	797.8	9.9
130°-140°	625.8	7.8
140°-150°	480.3	6.0
150°-160°	345.4	4.3
160°-170°	211.0	2.6
170°-180°	71.1	0.9
0°-30°	1433.2	17.8
0°-40°	2111.5	26.2
0°-60°	2976.8	36.9
0°-90°	3268.1	40.5
90°-120°	2262.0	28.1
90°-150°	4166.0	51.7
90°-180°	4794.0	59.5
0°-180°	8061.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2242	2242	2242	2242	2242	
5°	2205	2183	2197	2202	2210	205
15°	1865	1858	1908	1960	1994	521
25°	1425	1429	1503	1568	1638	655
35°	1007	1012	1080	1153	1234	626
45°	604	616	656	706	770	471
55°	347	362	383	397	430	315
65°	174	188	206	180	163	181
75°	88	88	80	55	37	93
85°	25	25	23	15	9	27
90°	2	5	10	11	10	5
95°	54	188	575	297	177	56
105°	174	268	1036	1529	1466	183
115°	306	374	860	1664	1878	302
125°	419	480	775	1307	1536	373
135°	502	561	754	1056	1195	388
145°	583	627	744	904	972	365
155°	659	684	737	810	837	304
165°	717	724	740	769	773	202
175°	744	744	741	751	749	71
180°	744	744	744	744	744	

TEST NUMBER: P519632

CATALOG NUMBER: SQ4-WB-150U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2241.7	2241.7	2241.7	2241.7	2241.7
2.5°	2247.2	2227.2	2232.2	2232.1	2225.9
5°	2205.3	2183.2	2197.4	2202.5	2210.2
7.5°	2123.4	2106.7	2132.7	2151.9	2167.5
10°	2059.7	2045.3	2078.4	2106.4	2126.6
12.5°	1985.7	1973.6	2014.7	2052.2	2078.6
15°	1865.0	1858.2	1908.2	1960.1	1993.8
17.5°	1735.7	1732.4	1789.8	1850.4	1893.5
20°	1647.6	1646.6	1709.5	1772.6	1822.7
22.5°	1558.7	1560.8	1626.9	1692.5	1749.5
25°	1425.3	1429.1	1503.0	1568.5	1637.7
27.5°	1301.9	1303.7	1380.0	1449.2	1523.0
30°	1217.7	1222.5	1297.4	1369.0	1445.9
32.5°	1133.5	1139.1	1212.4	1286.4	1364.9
35°	1007.2	1012.0	1080.0	1152.7	1234.4
37.5°	877.0	883.5	943.9	1012.6	1093.0
40°	792.8	802.4	855.8	920.5	999.4
42.5°	711.8	723.7	773.1	834.6	905.7
45°	603.9	615.5	656.1	705.7	770.2
47.5°	511.1	524.4	555.6	598.3	653.3
50°	458.4	470.9	499.7	531.4	583.3
52.5°	411.9	424.4	450.1	474.5	518.8
55°	347.2	361.6	382.6	397.1	429.8
57.5°	294.1	308.0	324.6	331.1	351.0
60°	258.7	274.1	289.2	288.4	299.0
62.5°	226.4	239.5	254.6	244.1	244.7
65°	174.1	188.5	205.6	179.6	163.3
67.5°	140.7	143.7	161.3	125.3	105.8
70°	124.9	124.9	129.8	97.0	80.7
72.5°	110.0	110.0	105.4	78.9	61.8
75°	87.5	87.5	79.7	54.7	37.4
77.5°	67.5	66.7	61.0	40.8	27.1
80°	54.1	54.1	49.2	32.2	21.6
82.5°	42.3	42.3	38.2	25.2	16.1
85°	24.6	24.6	22.6	14.6	8.9
87.5°	9.0	9.6	9.9	6.9	6.0
90°	1.6	4.7	10.4	11.2	10.4
92.5°	22.7	82.8	163.4	70.9	51.4
95°	53.6	188.2	574.6	297.4	176.9
97.5°	86.1	215.9	895.7	741.3	544.4
100°	110.4	227.0	995.6	1038.3	839.5
102.5°	132.9	242.6	1030.8	1263.5	1114.8
105°	173.7	268.4	1036.4	1528.8	1466.2
107.5°	211.4	297.8	991.1	1694.3	1715.1
110°	240.9	319.1	950.8	1738.7	1827.1



TEST NUMBER: P519632

CATALOG NUMBER: SQ4-WB-150U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	267.1	340.4	913.6	1729.8	1878.3
115°	305.7	373.8	859.5	1663.9	1878.3
117.5°	343.5	407.4	823.8	1563.3	1806.3
120°	366.5	429.1	802.7	1491.0	1739.1
122.5°	388.3	449.7	789.9	1413.6	1663.5
125°	418.6	479.6	774.7	1307.3	1535.8
127.5°	446.4	506.4	765.7	1220.6	1421.5
130°	461.8	523.6	761.9	1167.0	1348.5
132.5°	477.8	539.0	758.1	1118.6	1285.8
135°	501.8	561.3	753.9	1055.6	1194.9
137.5°	526.0	582.2	750.4	1004.4	1117.9
140°	542.6	595.0	749.1	971.5	1072.4
142.5°	558.6	607.9	746.5	941.7	1030.2
145°	583.4	627.3	743.5	903.5	972.4
147.5°	606.0	644.8	740.0	868.9	921.8
150°	622.6	657.1	738.7	850.1	892.4
152.5°	638.0	668.1	738.1	832.6	867.4
155°	658.7	684.5	737.1	810.5	837.1
157.5°	680.1	698.1	737.3	795.1	812.6
160°	692.3	707.1	737.9	785.4	797.9
162.5°	701.9	714.2	738.5	777.6	787.0
165°	717.1	724.1	740.3	769.2	773.1
167.5°	727.5	732.3	740.5	761.9	763.8
170°	733.9	736.2	741.1	758.7	758.7
172.5°	739.0	739.5	741.1	754.8	754.2
175°	744.3	743.5	741.1	750.7	749.1
177.5°	746.1	744.2	740.9	747.3	745.4
180°	743.5	743.5	743.5	743.5	743.5

(END OF REPORT)