

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519657

Luminaire Tested: **SQ4-025U-0D-930-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519657
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-025U-0D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1153.0 lumens
Efficiency: N/A
Efficacy: 140.6 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519657
CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519657

CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20			
RC	80								50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0		
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0		
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0		
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0		
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0		
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0		
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0		
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0		
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0		
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0		
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	805	10544	3705
100°	928	8724	6865
105°	974	5989	8482
110°	1025	4061	8202
115°	1062	2937	6688
120°	1080	2329	5120
125°	1088	1969	3925
130°	1069	1724	3066
135°	1052	1547	2470
140°	1053	1419	2051
145°	1053	1319	1729
150°	1061	1247	1506
155°	1076	1192	1346
160°	1082	1149	1239
165°	1089	1118	1176
170°	1097	1104	1132
175°	1098	1091	1105



TEST NUMBER: P519657

CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	86.7	7.5
100°-110°	227.9	19.8
110°-120°	236.3	20.5
120°-130°	189.6	16.4
130°-140°	148.7	12.9
140°-150°	114.2	9.9
150°-160°	82.2	7.1
160°-170°	50.3	4.4
170°-180°	17.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	551.0	47.8
90°-150°	1003.4	87.0
90°-180°	1153.0	100.0
0°-180°	1153.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	3	9	5	5	
95°	11	45	149	77	52	14
105°	41	62	252	382	357	43
115°	73	89	202	403	460	72
125°	102	114	184	310	366	90
135°	121	133	178	250	284	94
145°	140	149	176	214	230	88
155°	158	163	176	193	198	73
165°	171	173	176	182	185	48
175°	178	178	177	179	179	17
180°	178	178	178	178	178	



TEST NUMBER: P519657

CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.1	3.4	9.1	4.6	4.6
92.5°	4.8	23.1	51.1	22.6	14.6
95°	11.4	44.9	149.4	77.0	52.5
97.5°	19.8	49.3	223.5	177.7	130.9
100°	26.2	53.0	246.3	249.6	193.8
102.5°	31.7	56.7	252.7	310.9	263.2
105°	41.0	62.2	252.0	382.5	356.9
107.5°	50.6	70.3	237.6	419.8	426.0
110°	57.0	74.9	225.8	429.3	456.1
112.5°	63.4	80.3	214.8	423.3	464.3
115°	73.0	88.6	201.8	402.7	459.5
117.5°	82.3	96.6	192.9	374.1	437.2
120°	87.8	101.2	189.3	354.9	416.2
122.5°	93.3	106.7	186.5	335.7	396.1
125°	101.5	113.7	183.6	310.3	366.0
127.5°	108.1	120.6	181.1	289.8	336.8
130°	111.7	125.1	180.2	276.9	320.4
132.5°	115.4	128.8	179.2	265.9	304.9
135°	120.9	133.1	177.9	250.5	283.9
137.5°	126.6	138.6	177.7	238.9	266.4
140°	131.1	142.3	176.7	229.8	255.4
142.5°	134.8	145.0	176.7	223.3	245.4
145°	140.3	149.2	175.6	213.6	230.3
147.5°	145.7	154.4	175.6	205.6	219.4
150°	149.4	157.2	175.6	200.9	212.1
152.5°	153.0	159.0	175.6	197.2	205.7
155°	158.5	163.0	175.6	192.8	198.4
157.5°	162.6	166.8	175.6	188.9	192.9
160°	165.3	168.7	175.6	187.1	189.3
162.5°	168.1	170.5	175.6	185.2	187.5
165°	171.0	173.3	175.6	182.5	184.7
167.5°	173.8	174.9	176.7	181.3	182.2
170°	175.6	176.7	176.7	181.3	181.3
172.5°	176.5	176.7	176.7	180.4	179.5
175°	177.9	177.9	176.7	179.0	179.0
177.5°	177.9	177.9	177.0	178.8	177.9
180°	177.9	177.9	177.9	177.9	177.9

(END OF REPORT)