

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519705

Luminaire Tested: **SQ4-075U-0D-930-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519705
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3573.5 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 27.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519705
CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519705

CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	2717	32287	8815
100°	2851	27409	22570
105°	3023	18639	26488
110°	3169	12698	25438
115°	3278	9156	20689
120°	3345	7251	15965
125°	3329	6120	12127
130°	3283	5361	9515
135°	3258	4822	7685
140°	3252	4423	6372
145°	3251	4101	5381
150°	3283	3863	4667
155°	3327	3683	4174
160°	3354	3552	3850
165°	3374	3470	3634
170°	3382	3411	3499
175°	3387	3372	3408



TEST NUMBER: P519705

CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	258.7	7.2
100°-110°	711.8	19.9
110°-120°	734.7	20.6
120°-130°	588.6	16.5
130°-140°	462.3	12.9
140°-150°	354.3	9.9
150°-160°	254.7	7.1
160°-170°	155.8	4.4
170°-180°	52.5	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1705.2	47.7
90°-150°	3110.5	87.0
90°-180°	3573.0	100.0
0°-180°	3573.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	5	8	10	10	
95°	38	141	458	196	125	43
105°	127	196	784	1194	1115	134
115°	225	274	629	1253	1422	222
125°	310	354	571	965	1131	277
135°	375	416	554	781	884	289
145°	433	463	546	665	717	272
155°	490	506	543	598	615	225
165°	530	537	545	567	571	149
175°	548	550	546	553	552	52
180°	548	548	548	548	548	



TEST NUMBER: P519705

CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.2	4.6	8.2	10.5	10.5
92.5°	16.1	68.8	119.3	45.8	37.6
95°	38.5	141.2	457.5	195.6	124.9
97.5°	62.8	156.6	698.2	537.9	379.5
100°	80.5	166.1	773.8	781.0	637.2
102.5°	97.3	177.4	793.4	969.0	837.0
105°	127.2	195.7	784.3	1194.5	1114.6
107.5°	155.7	218.2	739.7	1304.9	1328.6
110°	176.2	233.3	706.1	1332.4	1414.5
112.5°	194.9	250.1	672.5	1314.7	1439.7
115°	225.2	274.3	629.1	1252.6	1421.5
117.5°	254.2	299.4	601.5	1165.6	1356.6
120°	271.9	315.3	589.4	1100.4	1297.8
122.5°	287.8	331.2	581.0	1043.2	1230.6
125°	310.4	353.8	570.7	965.4	1130.9
127.5°	331.9	373.2	563.9	900.6	1045.7
130°	343.1	385.3	560.2	862.0	994.4
132.5°	356.2	398.4	557.4	828.1	947.7
135°	374.6	415.7	554.4	780.8	883.5
137.5°	391.9	430.0	551.8	742.6	827.2
140°	405.0	440.4	550.9	717.2	793.6
142.5°	416.2	448.8	549.0	694.5	760.0
145°	433.0	462.7	546.2	665.2	716.6
147.5°	451.0	476.5	544.8	639.3	680.4
150°	462.2	485.0	543.9	625.1	657.1
152.5°	472.4	493.4	542.9	612.9	639.3
155°	490.2	506.2	542.7	597.9	615.1
157.5°	503.0	516.0	542.7	585.7	597.6
160°	512.4	522.6	542.7	579.1	588.2
162.5°	519.8	528.3	543.6	573.4	580.7
165°	529.9	536.7	545.0	567.3	570.7
167.5°	536.9	542.1	546.2	562.1	563.0
170°	541.5	545.0	546.2	560.2	560.2
172.5°	545.3	546.9	546.2	557.4	556.5
175°	548.5	549.7	546.2	553.2	552.0
177.5°	549.5	549.5	545.7	551.3	549.5
180°	548.5	548.5	548.5	548.5	548.5

(END OF REPORT)