

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938409

Luminaire Tested: SQ4-FB-150U-100D-830-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938409
REPORT IS A COMBINATION OF REPORTS P933623 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-100D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 26404.7 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 217.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938409
CATALOG NUMBER: SQ4-FB-150U-100D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P938409

CATALOG NUMBER: SQ4-FB-150U-100D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	35				35
1	94	90	86	82	85	81	78	75	65	63	60	50	49	47	36	35	35	28				28
2	85	78	72	66	77	70	65	61	56	53	49	43	41	39	32	30	29	23				23
3	77	68	61	55	69	61	55	50	49	45	41	38	35	32	28	26	24	19				19
4	71	60	52	46	63	54	47	42	43	38	34	34	30	27	24	22	20	16				16
5	64	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17	14				14
6	59	47	39	33	53	43	36	30	34	29	25	27	23	20	19	17	15	12				12
7	54	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13	10				10
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	13	11	9				9
9	47	35	27	22	42	31	25	20	26	20	17	20	16	14	15	12	10	8				8
10	43	31	24	20	39	29	22	18	23	18	15	18	15	12	13	11	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3645	3645	3645
5°	3562	4214	4900
10°	3232	6144	8122
15°	2748	8029	9808
20°	2238	9307	9996
25°	1868	9741	9793
30°	1576	9805	9774
35°	1394	9645	10027
40°	1215	9436	10288
45°	1101	9284	10329
50°	1011	9148	10157
55°	969	8947	9707
60°	993	8558	8996
65°	1035	7965	8019
70°	1105	6951	6775
75°	1230	5672	5287
80°	1352	3939	3562
85°	1228	2093	1824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10329 cd/sqm



TEST NUMBER: P938409

CATALOG NUMBER: SQ4-FB-150U-100D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.4	0.6
10°-20°	675.6	2.6
20°-30°	1181.7	4.5
30°-40°	1521.2	5.8
40°-50°	1699.2	6.4
50°-60°	1627.4	6.2
60°-70°	1289.7	4.9
70°-80°	758.4	2.9
80°-90°	220.9	0.8
90°-100°	1299.2	4.9
100°-110°	3415.7	12.9
110°-120°	3541.7	13.4
120°-130°	2840.9	10.8
130°-140°	2229.1	8.4
140°-150°	1710.9	6.5
150°-160°	1232.1	4.7
160°-170°	753.9	2.9
170°-180°	254.7	1.0
0°-30°	2009.8	7.6
0°-40°	3531.0	13.4
0°-60°	6857.6	26.0
0°-90°	9126.6	34.6
90°-120°	8256.6	31.3
90°-150°	15037.4	56.9
90°-180°	17278.0	65.4
0°-180°	26404.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1178	1178	1178	1178	1178	
5°	1148	1232	1387	1569	1626	106
15°	860	1588	2675	3244	3346	239
25°	549	1800	3187	3327	3331	253
35°	371	1720	3001	3172	3297	232
45°	254	1372	2652	3039	3175	196
55°	182	872	2251	2615	2687	166
65°	144	462	1671	1879	1906	143
75°	106	284	917	1008	1012	111
85°	38	87	227	250	254	40
90°	18	50	136	68	68	17
95°	172	672	2238	1154	785	191
105°	615	932	3776	5733	5348	652
115°	1093	1327	3025	6034	6887	1080
125°	1520	1705	2751	4649	5484	1350
135°	1812	1994	2665	3753	4256	1402
145°	2102	2236	2631	3202	3452	1317
155°	2376	2442	2631	2889	2973	1092
165°	2563	2597	2631	2735	2769	723
175°	2665	2665	2649	2683	2683	253
180°	2665	2665	2665	2665	2665	



TEST NUMBER: P938409

CATALOG NUMBER: SQ4-FB-150U-100D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5
2.5°	1178.5	1178.5	1186.0	1189.8	1197.4	1201.2	1208.8	1216.3	1239.1	1242.9	1250.4
5°	1148.2	1163.3	1212.6	1231.5	1284.6	1356.6	1386.9	1436.1	1538.4	1568.7	1587.6
7.5°	1102.7	1136.8	1258.0	1288.3	1420.9	1610.4	1690.0	1796.0	1959.0	2038.6	2103.0
10°	1030.7	1102.7	1318.6	1390.6	1606.7	1894.6	2042.4	2190.2	2436.5	2546.3	2588.0
12.5°	951.1	1068.5	1383.0	1481.6	1792.3	2212.9	2391.0	2554.0	2834.3	2982.1	3004.8
15°	860.1	1019.3	1443.7	1587.6	1989.3	2478.1	2675.2	2876.0	3137.5	3243.5	3270.1
17.5°	780.6	981.4	1500.5	1652.1	2140.9	2716.9	2917.7	3084.4	3296.6	3368.6	3387.6
20°	682.0	920.8	1538.4	1735.4	2300.0	2891.1	3084.4	3213.2	3357.2	3402.7	3410.2
22.5°	610.0	856.4	1561.1	1765.7	2406.2	2997.3	3160.2	3262.5	3361.0	3376.2	3379.9
25°	549.4	784.4	1557.3	1799.9	2497.1	3061.7	3186.7	3262.5	3319.3	3326.9	3326.9
27.5°	492.6	704.8	1542.2	1807.4	2565.3	3076.8	3175.4	3228.4	3254.9	3270.1	3270.1
30°	443.3	629.0	1504.3	1792.3	2595.6	3061.7	3141.2	3167.8	3194.3	3217.0	3228.4
32.5°	405.4	557.0	1447.5	1762.0	2599.4	3023.8	3080.6	3095.8	3133.7	3186.7	3205.7
35°	371.3	485.0	1383.0	1720.3	2576.6	2963.1	3001.1	3016.2	3092.0	3171.5	3198.1
37.5°	337.3	432.0	1299.7	1648.3	2542.6	2891.1	2917.7	2944.2	3061.7	3156.4	3186.7
40°	303.1	386.5	1201.2	1568.7	2489.5	2804.0	2826.7	2868.4	3023.8	3133.7	3164.0
42.5°	276.6	348.7	1095.1	1485.3	2421.3	2705.5	2739.6	2800.2	2978.3	3095.8	3129.8
45°	253.9	310.7	981.4	1371.7	2334.2	2603.2	2652.4	2735.8	2925.3	3038.9	3069.2
47.5°	231.2	284.2	863.9	1254.3	2239.4	2500.9	2565.3	2660.0	2853.3	2963.1	2989.7
50°	212.2	257.6	746.4	1129.2	2137.1	2391.0	2466.8	2565.3	2762.4	2864.7	2898.8
52.5°	197.0	234.9	636.6	1004.2	2019.6	2277.3	2364.5	2466.8	2652.4	2751.0	2773.7
55°	181.9	216.0	541.9	871.5	1898.4	2156.1	2250.8	2349.3	2531.2	2614.6	2629.7
57.5°	174.3	200.9	462.3	746.4	1769.6	2019.6	2125.8	2216.7	2387.2	2451.6	2466.8
60°	162.9	189.5	401.6	640.3	1629.3	1890.8	1981.8	2072.7	2216.7	2269.7	2281.1
62.5°	151.5	181.9	356.2	538.0	1485.3	1739.3	1830.2	1913.5	2034.8	2072.7	2087.8
65°	144.0	174.3	322.1	462.3	1337.6	1580.1	1671.0	1743.1	1841.5	1879.4	1887.0
67.5°	136.4	166.7	295.6	397.9	1189.8	1420.9	1489.2	1557.3	1633.1	1671.0	1674.8
70°	125.0	159.2	272.8	352.4	1038.2	1239.1	1296.0	1367.9	1428.6	1447.5	1458.9
72.5°	117.5	147.8	257.6	318.3	882.9	1064.8	1117.9	1159.5	1212.6	1231.5	1231.5
75°	106.1	132.6	242.5	284.2	723.7	871.5	917.0	958.7	1000.4	1007.9	996.5
77.5°	94.7	117.5	208.4	238.7	564.6	689.7	727.5	750.3	784.4	792.0	795.8
80°	79.5	102.3	162.9	185.7	409.3	507.7	534.3	553.2	583.5	583.5	591.1
82.5°	60.6	79.5	117.5	132.6	276.6	348.7	371.3	382.7	401.6	401.6	401.6
85°	37.9	49.2	75.8	87.2	166.7	212.2	227.3	231.2	246.3	250.1	250.1
87.5°	18.9	26.5	49.2	53.1	87.2	109.8	109.8	117.5	117.5	113.7	109.8
90°	17.9	32.2	46.6	50.1	78.7	116.8	135.9	120.8	90.6	68.0	68.0
92.5°	71.5	193.1	314.8	345.2	485.4	672.2	765.6	670.9	481.7	339.9	326.4
95°	171.7	394.3	616.9	672.5	1194.3	1890.0	2237.8	1996.9	1515.2	1153.8	1112.9
97.5°	296.9	493.3	689.7	738.8	1608.8	2768.7	3348.6	3196.4	2891.9	2663.5	2585.6
100°	393.5	571.6	749.7	794.2	1759.6	3046.7	3690.3	3701.3	3723.6	3740.4	3647.5
102.5°	475.8	642.0	808.1	849.7	1828.7	3134.2	3786.9	3980.9	4368.8	4659.8	4580.3
105°	615.4	756.1	896.8	932.0	1880.1	3144.1	3776.1	4211.0	5080.8	5733.0	5690.3
107.5°	758.5	889.7	1020.8	1053.6	1889.5	3004.1	3561.5	4168.1	5381.2	6291.1	6301.5
110°	855.0	973.5	1091.9	1121.6	1875.3	2880.1	3382.6	4060.8	5417.1	6434.3	6478.8



TEST NUMBER: P938409

CATALOG NUMBER: SQ4-FB-150U-100D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	949.9	1062.8	1175.7	1203.9	1875.9	2771.8	3219.8	3913.9	5302.0	6343.1	6411.4
115°	1093.0	1197.1	1301.3	1327.3	1893.2	2647.6	3024.9	3693.5	5030.7	6033.6	6128.4
117.5°	1234.3	1328.8	1423.5	1447.1	1928.3	2569.8	2890.7	3494.1	4700.9	5606.1	5711.2
120°	1316.5	1405.6	1494.6	1516.9	1956.9	2543.6	2837.0	3388.4	4491.0	5318.0	5420.2
122.5°	1397.0	1486.9	1576.7	1599.2	1998.1	2530.0	2795.9	3292.4	4285.4	5030.1	5130.9
125°	1520.5	1602.4	1684.3	1704.7	2053.6	2518.7	2751.2	3173.0	4016.4	4649.0	4741.9
127.5°	1620.6	1703.3	1786.0	1806.6	2108.9	2512.1	2713.6	3075.7	3800.0	4343.2	4421.5
130°	1674.3	1763.3	1852.3	1874.6	2149.5	2516.0	2699.3	3021.6	3666.5	4150.0	4222.4
132.5°	1729.8	1818.8	1907.8	1930.1	2182.3	2518.6	2686.7	2975.4	3552.6	3985.5	4050.3
135°	1812.0	1893.1	1974.2	1994.5	2218.1	2516.3	2665.3	2907.0	3390.4	3752.9	3808.7
137.5°	1896.1	1976.4	2056.7	2076.8	2271.7	2531.7	2661.7	2866.0	3274.7	3581.2	3626.9
140°	1965.9	2039.8	2113.8	2132.3	2304.5	2534.3	2649.2	2825.6	3178.7	3443.4	3486.1
142.5°	2019.6	2087.9	2156.3	2173.4	2332.0	2543.4	2649.2	2804.2	3114.3	3346.9	3383.7
145°	2101.9	2161.5	2221.1	2236.0	2367.7	2543.4	2631.3	2758.1	3011.7	3201.9	3229.8
147.5°	2184.1	2242.1	2300.1	2314.7	2420.2	2560.9	2631.3	2731.1	2930.6	3080.3	3103.4
150°	2237.8	2290.3	2342.8	2355.9	2447.6	2570.1	2631.3	2715.6	2884.2	3010.5	3029.2
152.5°	2293.3	2333.0	2372.7	2382.6	2465.5	2576.0	2631.3	2703.3	2847.2	2955.1	2969.2
155°	2375.6	2405.0	2434.4	2441.7	2504.9	2589.1	2631.3	2688.6	2803.1	2888.9	2898.3
157.5°	2436.4	2465.0	2493.5	2500.7	2544.2	2602.2	2631.3	2675.8	2764.8	2831.7	2838.3
160°	2477.5	2499.7	2522.0	2527.6	2562.2	2608.3	2631.3	2669.4	2745.7	2803.0	2806.8
162.5°	2518.6	2535.3	2551.9	2556.2	2581.2	2614.6	2631.3	2663.5	2727.9	2776.2	2779.8
165°	2563.3	2578.4	2593.5	2597.4	2608.6	2623.7	2631.3	2654.3	2700.4	2735.0	2738.8
167.5°	2604.5	2611.7	2618.8	2620.6	2630.1	2642.9	2649.2	2664.3	2694.5	2717.1	2718.8
170°	2631.3	2638.5	2645.6	2647.5	2648.0	2648.8	2649.2	2664.3	2694.5	2717.1	2717.1
172.5°	2645.6	2647.2	2648.8	2649.2	2649.2	2649.2	2649.2	2661.1	2685.0	2702.9	2701.5
175°	2665.3	2665.3	2665.3	2665.3	2660.0	2652.8	2649.2	2656.7	2671.8	2683.2	2683.2
177.5°	2665.3	2665.3	2665.3	2665.3	2661.1	2655.6	2652.8	2658.7	2670.7	2679.6	2677.9
180°	2665.3	2665.3	2665.3	2665.3	2665.3	2665.3	2665.3	2665.3	2665.3	2665.3	2665.3



TEST NUMBER: P938409

CATALOG NUMBER: SQ4-FB-150U-100D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1178.5	1178.5
2.5°	1258.0	1250.4
5°	1618.0	1625.6
7.5°	2178.8	2175.0
10°	2709.3	2743.3
12.5°	3095.8	3103.4
15°	3330.7	3345.9
17.5°	3421.6	3425.4
20°	3425.4	3417.9
22.5°	3383.8	3376.2
25°	3334.5	3330.7
27.5°	3289.0	3292.8
30°	3270.1	3281.5
32.5°	3270.1	3289.0
35°	3277.6	3296.6
37.5°	3273.8	3296.6
40°	3258.7	3285.2
42.5°	3217.0	3236.0
45°	3152.6	3175.4
47.5°	3069.2	3084.4
50°	2963.1	2978.3
52.5°	2830.5	2834.3
55°	2671.4	2686.6
57.5°	2500.9	2504.6
60°	2311.4	2322.8
62.5°	2110.6	2110.6
65°	1898.4	1906.0
67.5°	1678.6	1697.6
70°	1455.0	1458.9
72.5°	1235.2	1235.2
75°	1007.9	1011.7
77.5°	792.0	792.0
80°	587.4	591.1
82.5°	405.4	413.0
85°	253.9	253.9
87.5°	117.5	106.1
90°	68.0	68.0
92.5°	272.3	218.3
95°	949.0	785.3
97.5°	2273.9	1962.3
100°	3276.3	2905.0
102.5°	4262.3	3944.3
105°	5519.5	5348.5
107.5°	6342.9	6384.2
110°	6656.9	6835.0



TEST NUMBER: P938409

CATALOG NUMBER: SQ4-FB-150U-100D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	6684.9	6958.4
115°	6507.6	6886.8
117.5°	6131.8	6552.3
120°	5828.8	6237.5
122.5°	5534.0	5937.0
125°	5113.2	5484.5
127.5°	4734.8	5048.0
130°	4511.7	4801.1
132.5°	4309.4	4568.5
135°	4032.1	4255.5
137.5°	3809.8	3992.5
140°	3657.1	3828.0
142.5°	3530.7	3677.7
145°	3341.1	3452.4
147.5°	3195.6	3287.8
150°	3103.9	3178.7
152.5°	3025.6	3082.0
155°	2935.6	2973.0
157.5°	2864.5	2890.7
160°	2821.9	2837.0
162.5°	2794.1	2808.4
165°	2753.9	2769.1
167.5°	2725.1	2731.5
170°	2717.1	2717.1
172.5°	2695.9	2690.4
175°	2683.2	2683.2
177.5°	2671.6	2665.3
180°	2665.3	2665.3



TEST NUMBER: P938409
 CATALOG NUMBER: SQ4-FB-150U-100D-830-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.90	4.66	4.97	5.74	7.21	17.09	17.85	18.16	18.93	20.40
	3H	4.59	5.28	5.68	6.36	7.85	18.92	19.61	20.01	20.70	22.19
	4H	4.89	5.54	5.98	6.62	8.12	19.57	20.22	20.66	21.31	22.80
	6H	5.13	5.73	6.23	6.82	8.33	20.00	20.60	21.10	21.69	23.20
	8H	5.20	5.77	6.30	6.87	8.38	20.12	20.69	21.22	21.80	23.30
	12H	5.21	5.75	6.32	6.85	8.38	20.19	20.73	21.30	21.83	23.36
4H	2H	11.11	11.76	12.21	12.84	14.34	17.35	18.00	18.45	19.09	20.58
	3H	12.66	13.21	13.77	14.32	15.83	19.39	19.93	20.50	21.05	22.56
	4H	12.75	13.25	13.87	14.36	15.89	20.16	20.66	21.27	21.76	23.29
	6H	12.76	13.19	13.88	14.32	15.84	20.69	21.12	21.81	22.25	23.77
	8H	12.73	13.13	13.85	14.25	15.79	20.86	21.26	21.98	22.38	23.92
	12H	12.68	13.05	13.82	14.18	15.72	20.95	21.31	22.08	22.44	23.99
8H	4H	14.19	14.59	15.31	15.71	17.25	20.21	20.61	21.33	21.73	23.27
	6H	14.43	14.76	15.57	15.92	17.46	20.84	21.17	21.98	22.33	23.87
	8H	14.45	14.74	15.60	15.88	17.44	21.06	21.35	22.21	22.49	24.05
	12H	14.41	14.67	15.56	15.81	17.40	21.20	21.46	22.35	22.59	24.19
12H	4H	14.33	14.70	15.47	15.83	17.37	20.16	20.52	21.29	21.65	23.20
	6H	14.69	14.98	15.84	16.12	17.68	20.82	21.11	21.97	22.25	23.81
	8H	14.75	15.01	15.91	16.15	17.74	21.05	21.30	22.20	22.44	24.03