

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P519753

Luminaire Tested: **SQ4-125U-0D-930-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519753  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-125U-0D-930-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5967.3 lumens  
Efficiency: N/A  
Efficacy: 125.6 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Indirect

Input Watts (W): 47.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519753  
CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P519753

CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	4651	50029	17700
100°	4796	43922	38124
105°	5121	30614	42984
110°	5316	21282	40956
115°	5535	15612	34122
120°	5621	12298	26610
125°	5569	10329	20545
130°	5498	9059	16012
135°	5439	8143	12936
140°	5409	7470	10741
145°	5429	6941	9054
150°	5503	6523	7886
155°	5570	6217	7057
160°	5627	6004	6498
165°	5669	5856	6119
170°	5707	5751	5891
175°	5714	5685	5751



TEST NUMBER: P519753

CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	432.4	7.2
100°-110°	1164.8	19.5
110°-120°	1222.5	20.5
120°-130°	992.0	16.6
130°-140°	778.0	13.0
140°-150°	597.3	10.0
150°-160°	429.5	7.2
160°-170°	262.4	4.4
170°-180°	88.5	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2819.7	47.3
90°-150°	5187.0	86.9
90°-180°	5967.0	100.0
0°-180°	5967.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	7	14	15	15	
95°	66	235	709	362	251	73
105°	216	335	1288	1927	1809	227
115°	380	466	1073	2073	2344	374
125°	519	596	963	1628	1916	464
135°	625	698	936	1313	1487	483
145°	723	779	924	1123	1206	453
155°	821	851	916	1008	1040	378
165°	890	901	920	956	961	251
175°	926	924	921	934	931	88
180°	924	924	924	924	924	

TEST NUMBER: P519753

CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	2.4	7.0	14.1	15.3	15.3
92.5°	28.7	101.5	200.7	96.6	67.1
95°	65.9	235.2	708.9	362.5	250.8
97.5°	105.3	269.2	1111.8	928.8	700.4
100°	135.4	282.8	1240.0	1297.3	1076.3
102.5°	164.6	301.9	1282.3	1573.3	1391.9
105°	215.5	335.2	1288.2	1927.3	1808.7
107.5°	263.5	370.4	1233.4	2109.2	2139.8
110°	295.6	396.9	1183.4	2165.7	2277.4
112.5°	329.5	423.4	1135.4	2153.2	2336.7
115°	380.3	465.5	1072.7	2072.8	2344.5
117.5°	426.7	506.6	1024.2	1944.4	2247.0
120°	456.9	534.0	999.7	1852.3	2163.1
122.5°	483.3	559.5	981.8	1758.0	2068.0
125°	519.3	596.4	963.2	1628.0	1915.9
127.5°	553.9	629.9	951.5	1513.3	1770.3
130°	574.6	650.6	946.7	1447.6	1673.3
132.5°	595.4	670.4	942.0	1389.7	1597.0
135°	625.3	697.8	936.1	1313.4	1487.2
137.5°	653.8	723.3	933.1	1248.6	1391.4
140°	673.6	740.3	930.3	1208.7	1337.7
142.5°	694.3	756.5	928.4	1171.5	1280.2
145°	723.0	779.4	924.4	1122.9	1205.8
147.5°	754.1	803.1	920.4	1082.0	1147.2
150°	774.8	817.4	918.5	1056.3	1110.4
152.5°	793.7	830.7	917.5	1035.4	1079.3
155°	820.7	850.7	916.1	1007.5	1039.8
157.5°	844.5	867.8	916.4	988.0	1009.6
160°	859.6	879.2	917.3	976.5	992.7
162.5°	872.8	888.7	918.2	967.0	978.5
165°	890.2	900.6	919.7	956.3	960.9
167.5°	904.4	910.3	920.8	948.0	949.8
170°	913.8	916.1	920.8	943.2	943.2
172.5°	919.4	919.9	921.8	938.5	938.5
175°	925.5	924.4	920.8	933.7	931.4
177.5°	928.1	926.3	921.5	929.0	927.2
180°	924.4	924.4	924.4	924.4	924.4

(END OF REPORT)