

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519777

Luminaire Tested: **SQ4-150U-0D-930-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519777
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-150U-0D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7190.4 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 57.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519777
CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519777

CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20			
RC	80								50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0		
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0		
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0		
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0		
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0		
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0		
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0		
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0		
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0		
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0		
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	5674	60826	18723
100°	5869	52898	44606
105°	6191	36945	52266
110°	6498	25648	49288
115°	6674	18765	41006
120°	6763	14812	32090
125°	6732	12462	24704
130°	6628	10936	19356
135°	6547	9836	15590
140°	6535	9022	12916
145°	6571	8374	10952
150°	6634	7869	9506
155°	6705	7503	8522
160°	6797	7245	7834
165°	6849	7071	7385
170°	6875	6943	7108
175°	6893	6863	6937



TEST NUMBER: P519777

CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	518.3	7.2
100°-110°	1401.4	19.5
110°-120°	1473.3	20.5
120°-130°	1196.7	16.6
130°-140°	938.7	13.1
140°-150°	720.5	10.0
150°-160°	518.2	7.2
160°-170°	316.5	4.4
170°-180°	106.7	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	3393.0	47.2
90°-150°	6249.0	86.9
90°-180°	7190.0	100.0
0°-180°	7190.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	7	16	17	16	
95°	80	282	862	446	265	89
105°	260	402	1555	2293	2199	274
115°	459	561	1289	2496	2818	453
125°	628	719	1162	1961	2304	560
135°	753	842	1131	1583	1792	582
145°	875	941	1115	1355	1459	547
155°	988	1027	1106	1216	1256	456
165°	1076	1086	1110	1154	1160	303
175°	1116	1115	1112	1126	1124	106
180°	1115	1115	1115	1115	1115	



TEST NUMBER: P519777

CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.4	7.1	15.6	16.8	15.6
92.5°	34.1	124.2	245.1	106.4	77.1
95°	80.4	282.3	861.9	446.1	265.3
97.5°	129.2	323.8	1343.6	1111.9	816.6
100°	165.7	340.6	1493.4	1557.4	1259.3
102.5°	199.3	363.8	1546.2	1895.3	1672.3
105°	260.5	402.5	1554.6	2293.2	2199.3
107.5°	317.2	446.8	1486.7	2541.4	2572.6
110°	361.3	478.7	1426.2	2608.0	2740.7
112.5°	400.7	510.6	1370.5	2594.7	2817.5
115°	458.6	560.7	1289.3	2495.9	2817.5
117.5°	515.2	611.0	1235.8	2344.9	2709.5
120°	549.8	643.7	1204.1	2236.5	2608.6
122.5°	582.5	674.5	1184.9	2120.4	2495.3
125°	627.8	719.4	1162.1	1961.0	2303.7
127.5°	669.6	759.5	1148.6	1830.9	2132.3
130°	692.7	785.4	1142.9	1750.5	2022.8
132.5°	716.7	808.5	1137.1	1678.0	1928.7
135°	752.7	841.9	1130.8	1583.4	1792.3
137.5°	789.0	873.2	1125.6	1506.6	1676.8
140°	813.9	892.6	1123.6	1457.2	1608.6
142.5°	837.9	911.9	1119.8	1412.6	1545.3
145°	875.1	940.9	1115.2	1355.3	1458.6
147.5°	909.0	967.2	1110.0	1303.4	1382.7
150°	934.0	985.6	1108.0	1275.1	1338.5
152.5°	957.0	1002.1	1107.1	1249.0	1301.1
155°	988.0	1026.7	1105.6	1215.8	1255.7
157.5°	1020.2	1047.2	1105.9	1192.7	1219.0
160°	1038.4	1060.7	1106.8	1178.1	1196.9
162.5°	1052.8	1071.4	1107.8	1166.5	1180.5
165°	1075.6	1086.2	1110.4	1153.8	1159.7
167.5°	1091.2	1098.5	1110.7	1142.9	1145.7
170°	1100.8	1104.4	1111.6	1138.1	1138.1
172.5°	1108.5	1109.2	1111.6	1132.3	1131.3
175°	1116.4	1115.3	1111.6	1126.0	1123.6
177.5°	1119.1	1116.3	1111.4	1120.9	1118.1
180°	1115.2	1115.2	1115.2	1115.2	1115.2

(END OF REPORT)