

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562841

Luminaire Tested: **SQ4-PC3-0U-100D-830-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562841
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10913.2 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Direct


Input Watts (W): 108.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562841

CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562841

CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85				
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71				
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60				
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51				
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44				
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39				
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34				
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31				
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28				
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12298	12298	12298
5°	12390	12310	12265
10°	12360	12302	12267
15°	12295	12295	12283
20°	12214	12251	12251
25°	12099	12187	12149
30°	11952	12096	12044
35°	11774	11954	11871
40°	11579	11743	11624
45°	11369	11449	11272
50°	11072	11072	10894
55°	10720	10581	10422
60°	10202	9998	9838
65°	9430	9242	9160
70°	8256	8323	8290
75°	6643	7347	7391
80°	4722	6229	6294
85°	2876	5226	5226



TEST NUMBER: P562841

CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.4	3.5
10°-20°	1086.0	10.0
20°-30°	1644.6	15.1
30°-40°	1971.7	18.1
40°-50°	2010.4	18.4
50°-60°	1755.0	16.1
60°-70°	1256.4	11.5
70°-80°	647.1	5.9
80°-90°	163.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3109.0	28.5
0°-40°	5080.7	46.6
0°-60°	8846.0	81.1
0°-90°	10913.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10913.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3999	3999	3999	3999	3999	
5°	4014	3974	3988	3976	3973	381
15°	3862	3829	3862	3862	3858	1089
25°	3566	3540	3591	3580	3580	1641
35°	3136	3129	3184	3162	3162	1961
45°	2614	2607	2632	2599	2592	2012
55°	1999	1974	1973	1944	1944	1782
65°	1296	1267	1270	1259	1259	1282
75°	559	584	618	622	622	604
85°	82	125	148	152	148	114
90°	0	0	0	0	0	



TEST NUMBER: P562841

CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3998.7	3998.7	3998.7	3998.7	3998.7
2.5°	4022.4	3987.6	3998.7	3989.5	3975.0
5°	4013.5	3973.7	3987.6	3976.4	3972.8
7.5°	3984.6	3944.8	3963.1	3955.7	3952.0
10°	3958.0	3918.1	3939.5	3932.0	3928.3
12.5°	3922.4	3885.5	3909.8	3902.4	3901.7
15°	3861.7	3829.1	3861.7	3861.6	3858.0
17.5°	3785.4	3755.7	3790.6	3792.8	3790.6
20°	3732.1	3699.5	3743.2	3739.6	3743.2
22.5°	3666.9	3640.2	3686.9	3677.4	3681.0
25°	3565.5	3540.2	3591.4	3580.3	3580.3
27.5°	3445.5	3427.4	3483.3	3471.5	3471.5
30°	3365.6	3347.5	3406.3	3391.5	3391.5
32.5°	3276.7	3264.4	3320.4	3302.6	3302.6
35°	3136.0	3128.8	3184.1	3161.9	3161.9
37.5°	2990.9	2984.4	3034.6	3007.7	2999.0
40°	2884.2	2880.6	2925.0	2895.3	2895.3
42.5°	2777.6	2774.0	2812.4	2776.9	2776.9
45°	2614.0	2606.7	2632.5	2599.0	2591.7
47.5°	2435.5	2428.3	2444.4	2408.0	2404.4
50°	2314.1	2306.8	2314.1	2280.7	2277.0
52.5°	2189.7	2176.6	2177.8	2144.5	2143.7
55°	1999.3	1974.0	1973.4	1943.8	1943.8
57.5°	1797.9	1764.6	1767.6	1742.3	1738.7
60°	1658.7	1622.5	1625.4	1603.1	1599.5
62.5°	1522.5	1480.5	1489.1	1463.9	1463.2
65°	1295.9	1266.9	1270.0	1258.8	1258.8
67.5°	1078.2	1051.4	1070.8	1061.9	1061.1
70°	918.2	900.1	925.6	925.5	921.9
72.5°	770.1	769.4	801.2	801.3	803.4
75°	559.1	584.4	618.3	622.0	622.0
77.5°	373.2	418.1	455.4	456.9	456.1
80°	266.6	317.3	351.7	359.1	355.4
82.5°	180.7	234.3	262.9	270.2	266.6
85°	81.5	124.9	148.1	151.7	148.1
87.5°	23.7	49.8	59.2	59.1	53.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)