

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563081

Luminaire Tested: **SQ4-PC3-150U-050D-830-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563081
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22636.0 lumens
Efficiency: N/A
Efficacy: 134.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 168.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563081
CATALOG NUMBER: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563081

CATALOG NUMBER: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25				
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21				
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	24	23	17				
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20	15				
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13				
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11				
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10				
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8				
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10	8				
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7				
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6280	6280	6280
5°	6327	6286	6263
10°	6312	6282	6264
15°	6278	6278	6272
20°	6237	6256	6256
25°	6178	6223	6204
30°	6103	6177	6150
35°	6012	6104	6062
40°	5913	5996	5936
45°	5805	5846	5756
50°	5653	5653	5563
55°	5474	5403	5322
60°	5210	5105	5023
65°	4815	4719	4678
70°	4216	4250	4233
75°	3392	3751	3774
80°	2410	3181	3214
85°	1468	2668	2668



TEST NUMBER: P563081

CATALOG NUMBER: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.2	0.9
10°-20°	554.5	2.4
20°-30°	839.8	3.7
30°-40°	1006.8	4.4
40°-50°	1026.6	4.5
50°-60°	896.1	4.0
60°-70°	641.6	2.8
70°-80°	330.4	1.5
80°-90°	89.1	0.4
90°-100°	1229.6	5.4
100°-110°	3324.5	14.7
110°-120°	3495.2	15.4
120°-130°	2839.1	12.5
130°-140°	2227.0	9.8
140°-150°	1709.2	7.6
150°-160°	1229.3	5.4
160°-170°	750.9	3.3
170°-180°	253.2	1.1
0°-30°	1587.6	7.0
0°-40°	2594.4	11.5
0°-60°	4517.1	20.0
0°-90°	5578.1	24.6
90°-120°	8049.2	35.6
90°-150°	14824.5	65.5
90°-180°	17058.0	75.4
0°-180°	22636.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2042	2042	2042	2042	2042	
5°	2049	2029	2036	2030	2029	195
15°	1972	1955	1972	1972	1970	556
25°	1821	1808	1834	1828	1828	838
35°	1601	1598	1626	1615	1615	1001
45°	1335	1331	1344	1327	1323	1027
55°	1021	1008	1008	993	993	910
65°	662	647	648	643	643	654
75°	286	298	316	318	318	309
85°	42	64	76	78	76	57
90°	6	17	37	40	37	14
95°	191	670	2045	1058	629	200
105°	618	955	3688	5440	5217	651
115°	1088	1330	3059	5921	6684	1074
125°	1490	1707	2757	4652	5465	1328
135°	1786	1997	2683	3756	4252	1380
145°	2076	2232	2646	3215	3460	1299
155°	2344	2436	2623	2884	2979	1081
165°	2552	2577	2634	2737	2751	719
175°	2649	2646	2637	2671	2666	251
180°	2646	2646	2646	2646	2646	

TEST NUMBER: P563081

CATALOG NUMBER: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2041.9	2041.9	2041.9	2041.9	2041.9
2.5°	2054.0	2036.2	2041.9	2037.2	2029.8
5°	2049.4	2029.1	2036.2	2030.5	2028.6
7.5°	2034.7	2014.3	2023.7	2019.9	2018.0
10°	2021.1	2000.7	2011.6	2007.8	2005.9
12.5°	2002.9	1984.1	1996.5	1992.7	1992.3
15°	1971.9	1955.3	1971.9	1971.9	1970.0
17.5°	1933.0	1917.8	1935.6	1936.7	1935.6
20°	1905.7	1889.1	1911.4	1909.6	1911.4
22.5°	1872.5	1858.8	1882.7	1877.8	1879.6
25°	1820.7	1807.7	1833.9	1828.2	1828.2
27.5°	1759.4	1750.2	1778.7	1772.6	1772.6
30°	1718.6	1709.3	1739.4	1731.8	1731.8
32.5°	1673.2	1666.9	1695.5	1686.4	1686.4
35°	1601.4	1597.7	1625.9	1614.6	1614.6
37.5°	1527.2	1523.9	1549.5	1535.8	1531.4
40°	1472.8	1470.9	1493.6	1478.5	1478.5
42.5°	1418.3	1416.5	1436.1	1418.0	1418.0
45°	1334.8	1331.1	1344.2	1327.1	1323.4
47.5°	1243.6	1239.9	1248.2	1229.6	1227.8
50°	1181.6	1177.9	1181.6	1164.6	1162.7
52.5°	1118.1	1111.5	1112.1	1095.0	1094.7
55°	1020.9	1008.0	1007.7	992.6	992.6
57.5°	918.1	901.1	902.6	889.7	887.8
60°	847.0	828.5	830.0	818.6	816.7
62.5°	777.4	756.0	760.4	747.5	747.2
65°	661.7	646.9	648.5	642.8	642.8
67.5°	550.5	536.9	546.8	542.2	541.8
70°	468.9	459.6	472.7	472.6	470.8
72.5°	393.2	392.9	409.1	409.2	410.3
75°	285.5	298.4	315.7	317.6	317.6
77.5°	190.6	213.5	232.5	233.3	232.9
80°	136.1	162.0	179.6	183.3	181.5
82.5°	92.3	119.6	134.2	138.0	136.1
85°	41.6	63.8	75.6	77.5	75.6
87.5°	13.2	28.8	37.7	38.1	34.6
90°	5.7	16.8	37.0	39.8	37.0
92.5°	80.9	294.7	581.5	252.5	182.8
95°	190.8	669.8	2044.8	1058.2	629.4
97.5°	306.4	768.1	3187.4	2637.8	1937.2
100°	393.0	807.9	3542.8	3694.8	2987.5
102.5°	472.8	863.2	3668.1	4496.2	3967.1
105°	618.0	954.9	3688.0	5440.1	5217.4
107.5°	752.4	1059.8	3526.9	6029.0	6103.1
110°	857.2	1135.7	3383.3	6187.1	6501.8

TEST NUMBER: P563081

CATALOG NUMBER: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	950.6	1211.3	3251.2	6155.5	6684.1
115°	1087.9	1330.2	3058.7	5921.1	6684.1
117.5°	1222.3	1449.6	2931.6	5562.8	6427.7
120°	1304.3	1527.1	2856.5	5305.8	6188.5
122.5°	1381.8	1600.1	2810.9	5030.3	5919.7
125°	1489.5	1706.7	2756.8	4652.0	5465.1
127.5°	1588.6	1801.9	2724.9	4343.4	5058.5
130°	1643.2	1863.2	2711.2	4152.7	4798.7
132.5°	1700.2	1918.0	2697.5	3980.7	4575.5
135°	1785.6	1997.3	2682.7	3756.3	4251.9
137.5°	1871.6	2071.6	2670.2	3574.2	3978.0
140°	1930.9	2117.5	2665.6	3457.0	3816.2
142.5°	1987.8	2163.3	2656.5	3351.2	3665.8
145°	2076.1	2232.1	2645.7	3215.2	3460.2
147.5°	2156.4	2294.6	2633.2	3092.0	3280.2
150°	2215.7	2338.2	2628.6	3025.1	3175.4
152.5°	2270.4	2377.3	2626.3	2962.9	3086.6
155°	2343.8	2435.7	2622.9	2884.2	2978.9
157.5°	2420.2	2484.2	2623.5	2829.4	2891.8
160°	2463.4	2516.4	2625.8	2794.8	2839.4
162.5°	2497.6	2541.6	2628.1	2767.2	2800.6
165°	2551.7	2576.8	2634.3	2737.2	2751.1
167.5°	2588.8	2606.0	2634.9	2711.4	2718.0
170°	2611.5	2619.9	2637.2	2699.8	2699.8
172.5°	2629.8	2631.4	2637.2	2686.1	2683.9
175°	2648.6	2645.8	2637.2	2671.2	2665.6
177.5°	2654.8	2648.1	2636.6	2659.2	2652.5
180°	2645.7	2645.7	2645.7	2645.7	2645.7

(END OF REPORT)