

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562543

Luminaire Tested: **SQ4-PC3-025U-075D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562543
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4616.1 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562543
CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562543

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75		
1	103	99	95	91	98	94	91	88	86	83	80	78	75	73	70	69	67	63		
2	94	87	80	75	89	83	77	72	75	70	67	68	65	61	62	59	57	53		
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48	45		
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	41	38		
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	33		
6	67	54	46	39	63	52	44	38	48	41	36	44	38	34	40	35	32	29		
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	36	32	28	26		
8	57	45	36	31	55	43	35	30	39	33	28	36	31	27	33	29	25	23		
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	31	26	23	21		
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	29	24	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7803	7803	7803
5°	7862	7811	7782
10°	7843	7806	7784
15°	7801	7801	7794
20°	7750	7773	7773
25°	7676	7733	7708
30°	7583	7675	7641
35°	7470	7585	7532
40°	7347	7450	7375
45°	7214	7264	7152
50°	7025	7025	6913
55°	6802	6714	6613
60°	6473	6344	6242
65°	5983	5864	5813
70°	5239	5282	5260
75°	4216	4663	4689
80°	2997	3953	3995
85°	1821	3317	3317



TEST NUMBER: P562543

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.1	2.6
10°-20°	344.5	7.5
20°-30°	521.7	11.3
30°-40°	625.5	13.6
40°-50°	637.8	13.8
50°-60°	556.8	12.1
60°-70°	398.6	8.6
70°-80°	205.3	4.4
80°-90°	52.9	1.1
90°-100°	86.7	1.9
100°-110°	227.9	4.9
110°-120°	236.3	5.1
120°-130°	189.6	4.1
130°-140°	148.7	3.2
140°-150°	114.2	2.5
150°-160°	82.2	1.8
160°-170°	50.3	1.1
170°-180°	17.0	0.4
0°-30°	986.3	21.4
0°-40°	1611.8	34.9
0°-60°	2806.4	60.8
0°-90°	3463.1	75.0
90°-120°	551.0	11.9
90°-150°	1003.4	21.7
90°-180°	1153.0	25.0
0°-180°	4616.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1273	1261	1265	1262	1260	121
15°	1225	1215	1225	1225	1224	345
25°	1131	1123	1139	1136	1136	521
35°	995	993	1010	1003	1003	622
45°	829	827	835	824	822	638
55°	634	626	626	617	617	565
65°	411	402	403	399	399	407
75°	177	185	196	197	197	192
85°	26	40	47	48	47	35
90°	1	3	9	5	5	2
95°	11	45	149	77	52	13
105°	41	62	252	382	357	43
115°	73	89	202	403	460	72
125°	102	114	184	310	366	90
135°	121	133	178	250	284	94
145°	140	149	176	214	230	88
155°	158	163	176	193	198	73
165°	171	173	176	182	185	48
175°	178	178	177	179	179	17
180°	178	178	178	178	178	

TEST NUMBER: P562543

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.6	1268.6	1268.6	1268.6	1268.6
2.5°	1276.1	1265.1	1268.6	1265.7	1261.1
5°	1273.3	1260.6	1265.1	1261.5	1260.4
7.5°	1264.1	1251.5	1257.3	1254.9	1253.8
10°	1255.7	1243.0	1249.8	1247.4	1246.3
12.5°	1244.4	1232.7	1240.4	1238.0	1237.8
15°	1225.1	1214.8	1225.1	1225.1	1223.9
17.5°	1200.9	1191.5	1202.6	1203.3	1202.6
20°	1184.0	1173.7	1187.5	1186.4	1187.5
22.5°	1163.3	1154.8	1169.7	1166.6	1167.8
25°	1131.1	1123.1	1139.4	1135.8	1135.8
27.5°	1093.1	1087.3	1105.1	1101.3	1101.3
30°	1067.7	1062.0	1080.6	1075.9	1075.9
32.5°	1039.5	1035.6	1053.4	1047.8	1047.8
35°	994.9	992.6	1010.2	1003.1	1003.1
37.5°	948.8	946.8	962.7	954.2	951.4
40°	915.0	913.9	927.9	918.5	918.5
42.5°	881.2	880.0	892.2	881.0	881.0
45°	829.3	827.0	835.1	824.5	822.2
47.5°	772.7	770.4	775.5	763.9	762.8
50°	734.1	731.8	734.1	723.5	722.4
52.5°	694.7	690.5	690.9	680.3	680.1
55°	634.3	626.2	626.1	616.7	616.7
57.5°	570.4	559.8	560.8	552.7	551.6
60°	526.2	514.7	515.7	508.6	507.4
62.5°	483.0	469.7	472.4	464.4	464.2
65°	411.1	401.9	402.9	399.4	399.4
67.5°	342.0	333.5	339.7	336.9	336.6
70°	291.3	285.6	293.7	293.6	292.5
72.5°	244.3	244.1	254.2	254.2	254.9
75°	177.4	185.4	196.2	197.3	197.3
77.5°	118.4	132.6	144.5	144.9	144.7
80°	84.6	100.7	111.6	113.9	112.8
82.5°	57.3	74.3	83.4	85.7	84.6
85°	25.8	39.6	47.0	48.1	47.0
87.5°	7.7	16.5	20.6	19.7	17.8
90°	1.1	3.4	9.1	4.6	4.6
92.5°	4.8	23.1	51.1	22.6	14.6
95°	11.4	44.9	149.4	77.0	52.5
97.5°	19.8	49.3	223.5	177.7	130.9
100°	26.2	53.0	246.3	249.6	193.8
102.5°	31.7	56.7	252.7	310.9	263.2
105°	41.0	62.2	252.0	382.5	356.9
107.5°	50.6	70.3	237.6	419.8	426.0
110°	57.0	74.9	225.8	429.3	456.1



TEST NUMBER: P562543

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	63.4	80.3	214.8	423.3	464.3
115°	73.0	88.6	201.8	402.7	459.5
117.5°	82.3	96.6	192.9	374.1	437.2
120°	87.8	101.2	189.3	354.9	416.2
122.5°	93.3	106.7	186.5	335.7	396.1
125°	101.5	113.7	183.6	310.3	366.0
127.5°	108.1	120.6	181.1	289.8	336.8
130°	111.7	125.1	180.2	276.9	320.4
132.5°	115.4	128.8	179.2	265.9	304.9
135°	120.9	133.1	177.9	250.5	283.9
137.5°	126.6	138.6	177.7	238.9	266.4
140°	131.1	142.3	176.7	229.8	255.4
142.5°	134.8	145.0	176.7	223.3	245.4
145°	140.3	149.2	175.6	213.6	230.3
147.5°	145.7	154.4	175.6	205.6	219.4
150°	149.4	157.2	175.6	200.9	212.1
152.5°	153.0	159.0	175.6	197.2	205.7
155°	158.5	163.0	175.6	192.8	198.4
157.5°	162.6	166.8	175.6	188.9	192.9
160°	165.3	168.7	175.6	187.1	189.3
162.5°	168.1	170.5	175.6	185.2	187.5
165°	171.0	173.3	175.6	182.5	184.7
167.5°	173.8	174.9	176.7	181.3	182.2
170°	175.6	176.7	176.7	181.3	181.3
172.5°	176.5	176.7	176.7	180.4	179.5
175°	177.9	177.9	176.7	179.0	179.0
177.5°	177.9	177.9	177.0	178.8	177.9
180°	177.9	177.9	177.9	177.9	177.9

(END OF REPORT)