

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562783

Luminaire Tested: **SQ4-PC3-075U-125D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562783
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-125D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9445.4 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 97.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562783
CATALOG NUMBER: SQ4-PC3-075U-125D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562783

CATALOG NUMBER: SQ4-PC3-075U-125D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	73	86	79	73	69	69	65	62	61	57	55	52	50	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13230	13230	13230
5°	13330	13244	13195
10°	13298	13235	13198
15°	13228	13228	13215
20°	13141	13180	13180
25°	13017	13111	13070
30°	12858	13014	12957
35°	12666	12861	12772
40°	12457	12633	12506
45°	12231	12318	12128
50°	11911	11911	11721
55°	11533	11384	11213
60°	10977	10755	10584
65°	10146	9942	9856
70°	8882	8954	8918
75°	7146	7904	7952
80°	5079	6702	6773
85°	3091	5625	5625



TEST NUMBER: P562783

CATALOG NUMBER: SQ4-PC3-075U-125D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.6	2.2
10°-20°	584.2	6.2
20°-30°	884.7	9.4
30°-40°	1060.6	11.2
40°-50°	1081.5	11.4
50°-60°	944.0	10.0
60°-70°	675.9	7.2
70°-80°	348.1	3.7
80°-90°	89.4	0.9
90°-100°	258.7	2.7
100°-110°	711.8	7.5
110°-120°	734.7	7.8
120°-130°	588.6	6.2
130°-140°	462.3	4.9
140°-150°	354.3	3.8
150°-160°	254.7	2.7
160°-170°	155.8	1.6
170°-180°	52.5	0.6
0°-30°	1672.4	17.7
0°-40°	2733.0	28.9
0°-60°	4758.5	50.4
0°-90°	5871.9	62.2
90°-120°	1705.2	18.1
90°-150°	3110.5	32.9
90°-180°	3573.0	37.8
0°-180°	9445.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2151	2151	2151	2151	2151	
5°	2159	2138	2145	2139	2137	205
15°	2077	2060	2077	2077	2075	586
25°	1918	1904	1932	1926	1926	883
35°	1687	1683	1713	1701	1701	1055
45°	1406	1402	1416	1398	1394	1082
55°	1076	1062	1062	1046	1046	959
65°	697	682	683	677	677	689
75°	301	314	333	335	335	325
85°	44	67	80	82	80	60
90°	1	5	8	10	10	4
95°	38	141	458	196	125	41
105°	127	196	784	1194	1115	134
115°	225	274	629	1253	1422	222
125°	310	354	571	965	1131	277
135°	375	416	554	781	884	289
145°	433	463	546	665	717	272
155°	490	506	543	598	615	225
165°	530	537	545	567	571	149
175°	548	550	546	553	552	52
180°	548	548	548	548	548	

TEST NUMBER: P562783

CATALOG NUMBER: SQ4-PC3-075U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2151.0	2151.0	2151.0	2151.0	2151.0
2.5°	2163.7	2145.1	2151.0	2146.0	2138.3
5°	2159.0	2137.5	2145.0	2139.0	2137.1
7.5°	2143.4	2122.0	2131.9	2127.9	2125.9
10°	2129.1	2107.7	2119.1	2115.1	2113.2
12.5°	2110.0	2090.1	2103.2	2099.2	2098.8
15°	2077.3	2059.8	2077.3	2077.3	2075.3
17.5°	2036.3	2020.3	2039.1	2040.2	2039.1
20°	2007.6	1990.1	2013.6	2011.6	2013.6
22.5°	1972.5	1958.1	1983.3	1978.2	1980.1
25°	1918.0	1904.3	1931.9	1925.9	1925.9
27.5°	1853.4	1843.7	1873.8	1867.4	1867.4
30°	1810.4	1800.7	1832.3	1824.4	1824.4
32.5°	1762.6	1756.0	1786.1	1776.6	1776.6
35°	1686.9	1683.0	1712.8	1700.9	1700.9
37.5°	1608.9	1605.4	1632.4	1617.9	1613.3
40°	1551.5	1549.6	1573.4	1557.5	1557.5
42.5°	1494.2	1492.2	1512.9	1493.8	1493.8
45°	1406.1	1402.2	1416.1	1398.1	1394.2
47.5°	1310.1	1306.2	1314.9	1295.3	1293.4
50°	1244.8	1240.9	1244.8	1226.8	1224.9
52.5°	1177.9	1170.9	1171.5	1153.6	1153.2
55°	1075.5	1061.9	1061.6	1045.6	1045.6
57.5°	967.2	949.2	950.8	937.2	935.3
60°	892.3	872.8	874.3	862.3	860.4
62.5°	819.0	796.4	801.0	787.5	787.1
65°	697.1	681.5	683.1	677.2	677.2
67.5°	580.0	565.6	576.0	571.2	570.8
70°	493.9	484.2	497.9	497.9	495.9
72.5°	414.3	413.9	431.0	431.0	432.2
75°	300.7	314.4	332.6	334.6	334.6
77.5°	200.8	224.9	245.0	245.8	245.4
80°	143.4	170.7	189.2	193.1	191.2
82.5°	97.2	126.0	141.4	145.3	143.4
85°	43.8	67.2	79.7	81.6	79.7
87.5°	13.0	27.7	33.5	33.9	30.8
90°	1.2	4.6	8.2	10.5	10.5
92.5°	16.1	68.8	119.3	45.8	37.6
95°	38.5	141.2	457.5	195.6	124.9
97.5°	62.8	156.6	698.2	537.9	379.5
100°	80.5	166.1	773.8	781.0	637.2
102.5°	97.3	177.4	793.4	969.0	837.0
105°	127.2	195.7	784.3	1194.5	1114.6
107.5°	155.7	218.2	739.7	1304.9	1328.6
110°	176.2	233.3	706.1	1332.4	1414.5

TEST NUMBER: P562783

CATALOG NUMBER: SQ4-PC3-075U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	194.9	250.1	672.5	1314.7	1439.7
115°	225.2	274.3	629.1	1252.6	1421.5
117.5°	254.2	299.4	601.5	1165.6	1356.6
120°	271.9	315.3	589.4	1100.4	1297.8
122.5°	287.8	331.2	581.0	1043.2	1230.6
125°	310.4	353.8	570.7	965.4	1130.9
127.5°	331.9	373.2	563.9	900.6	1045.7
130°	343.1	385.3	560.2	862.0	994.4
132.5°	356.2	398.4	557.4	828.1	947.7
135°	374.6	415.7	554.4	780.8	883.5
137.5°	391.9	430.0	551.8	742.6	827.2
140°	405.0	440.4	550.9	717.2	793.6
142.5°	416.2	448.8	549.0	694.5	760.0
145°	433.0	462.7	546.2	665.2	716.6
147.5°	451.0	476.5	544.8	639.3	680.4
150°	462.2	485.0	543.9	625.1	657.1
152.5°	472.4	493.4	542.9	612.9	639.3
155°	490.2	506.2	542.7	597.9	615.1
157.5°	503.0	516.0	542.7	585.7	597.6
160°	512.4	522.6	542.7	579.1	588.2
162.5°	519.8	528.3	543.6	573.4	580.7
165°	529.9	536.7	545.0	567.3	570.7
167.5°	536.9	542.1	546.2	562.1	563.0
170°	541.5	545.0	546.2	560.2	560.2
172.5°	545.3	546.9	546.2	557.4	556.5
175°	548.5	549.7	546.2	553.2	552.0
177.5°	549.5	549.5	545.7	551.3	549.5
180°	548.5	548.5	548.5	548.5	548.5

(END OF REPORT)