

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562831

Luminaire Tested: **SQ4-PC3-0U-075D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562831
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-075D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3462.2 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562831
CATALOG NUMBER: SQ4-PC3-0U-075D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562831

CATALOG NUMBER: SQ4-PC3-0U-075D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7803	7803	7803
5°	7862	7811	7782
10°	7843	7806	7784
15°	7801	7801	7794
20°	7750	7773	7773
25°	7676	7733	7708
30°	7583	7675	7641
35°	7470	7585	7532
40°	7347	7450	7375
45°	7214	7264	7152
50°	7025	7025	6913
55°	6802	6714	6613
60°	6473	6344	6242
65°	5983	5864	5813
70°	5239	5282	5260
75°	4216	4663	4689
80°	2997	3953	3995
85°	1821	3317	3317



TEST NUMBER: P562831

CATALOG NUMBER: SQ4-PC3-0U-075D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.1	3.5
10°-20°	344.5	10.0
20°-30°	521.7	15.1
30°-40°	625.5	18.1
40°-50°	637.8	18.4
50°-60°	556.8	16.1
60°-70°	398.6	11.5
70°-80°	205.3	5.9
80°-90°	51.9	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	986.3	28.5
0°-40°	1611.8	46.6
0°-60°	2806.4	81.1
0°-90°	3462.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3462.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1273	1261	1265	1262	1260	121
15°	1225	1215	1225	1225	1224	345
25°	1131	1123	1139	1136	1136	521
35°	995	993	1010	1003	1003	622
45°	829	827	835	824	822	638
55°	634	626	626	617	617	565
65°	411	402	403	399	399	407
75°	177	185	196	197	197	192
85°	26	40	47	48	47	36
90°	0	0	0	0	0	



TEST NUMBER: P562831

CATALOG NUMBER: SQ4-PC3-0U-075D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.6	1268.6	1268.6	1268.6	1268.6
2.5°	1276.1	1265.1	1268.6	1265.7	1261.1
5°	1273.3	1260.6	1265.1	1261.5	1260.4
7.5°	1264.1	1251.5	1257.3	1254.9	1253.8
10°	1255.7	1243.0	1249.8	1247.4	1246.3
12.5°	1244.4	1232.7	1240.4	1238.0	1237.8
15°	1225.1	1214.8	1225.1	1225.1	1223.9
17.5°	1200.9	1191.5	1202.6	1203.3	1202.6
20°	1184.0	1173.7	1187.5	1186.4	1187.5
22.5°	1163.3	1154.8	1169.7	1166.6	1167.8
25°	1131.1	1123.1	1139.4	1135.8	1135.8
27.5°	1093.1	1087.3	1105.1	1101.3	1101.3
30°	1067.7	1062.0	1080.6	1075.9	1075.9
32.5°	1039.5	1035.6	1053.4	1047.8	1047.8
35°	994.9	992.6	1010.2	1003.1	1003.1
37.5°	948.8	946.8	962.7	954.2	951.4
40°	915.0	913.9	927.9	918.5	918.5
42.5°	881.2	880.0	892.2	881.0	881.0
45°	829.3	827.0	835.1	824.5	822.2
47.5°	772.7	770.4	775.5	763.9	762.8
50°	734.1	731.8	734.1	723.5	722.4
52.5°	694.7	690.5	690.9	680.3	680.1
55°	634.3	626.2	626.1	616.7	616.7
57.5°	570.4	559.8	560.8	552.7	551.6
60°	526.2	514.7	515.7	508.6	507.4
62.5°	483.0	469.7	472.4	464.4	464.2
65°	411.1	401.9	402.9	399.4	399.4
67.5°	342.0	333.5	339.7	336.9	336.6
70°	291.3	285.6	293.7	293.6	292.5
72.5°	244.3	244.1	254.2	254.2	254.9
75°	177.4	185.4	196.2	197.3	197.3
77.5°	118.4	132.6	144.5	144.9	144.7
80°	84.6	100.7	111.6	113.9	112.8
82.5°	57.3	74.3	83.4	85.7	84.6
85°	25.8	39.6	47.0	48.1	47.0
87.5°	7.5	15.8	18.8	18.8	16.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)