

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563095

Luminaire Tested: **SQ4-PC3-150U-050D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563095
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9541.7 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563095
CATALOG NUMBER: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563095

CATALOG NUMBER: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	24	23	17
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20	15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5294	5294	5294
5°	5334	5299	5280
10°	5321	5296	5281
15°	5293	5293	5288
20°	5258	5274	5274
25°	5209	5246	5230
30°	5145	5207	5185
35°	5068	5146	5110
40°	4985	5055	5004
45°	4894	4929	4853
50°	4766	4766	4690
55°	4615	4555	4487
60°	4392	4304	4235
65°	4059	3979	3944
70°	3554	3582	3568
75°	2859	3163	3182
80°	2033	2681	2710
85°	1235	2251	2251



TEST NUMBER: P563095

CATALOG NUMBER: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.5	0.9
10°-20°	233.8	2.4
20°-30°	354.0	3.7
30°-40°	424.4	4.4
40°-50°	432.7	4.5
50°-60°	377.7	4.0
60°-70°	270.4	2.8
70°-80°	139.3	1.5
80°-90°	37.6	0.4
90°-100°	518.3	5.4
100°-110°	1401.4	14.7
110°-120°	1473.3	15.4
120°-130°	1196.7	12.5
130°-140°	938.7	9.8
140°-150°	720.5	7.6
150°-160°	518.2	5.4
160°-170°	316.5	3.3
170°-180°	106.7	1.1
0°-30°	669.2	7.0
0°-40°	1093.6	11.5
0°-60°	1904.1	20.0
0°-90°	2351.4	24.6
90°-120°	3393.0	35.6
90°-150°	6249.0	65.5
90°-180°	7190.0	75.4
0°-180°	9541.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	861	861	861	861	861	
5°	864	855	858	856	855	82
15°	831	824	831	831	830	234
25°	768	762	773	771	771	353
35°	675	674	685	681	681	422
45°	563	561	567	559	558	433
55°	430	425	425	418	418	384
65°	279	273	273	271	271	276
75°	120	126	133	134	134	130
85°	18	27	32	33	32	24
90°	2	7	16	17	16	6
95°	80	282	862	446	265	84
105°	260	402	1555	2293	2199	274
115°	459	561	1289	2496	2818	453
125°	628	719	1162	1961	2304	560
135°	753	842	1131	1583	1792	582
145°	875	941	1115	1355	1459	547
155°	988	1027	1106	1216	1256	456
165°	1076	1086	1110	1154	1160	303
175°	1116	1115	1112	1126	1124	106
180°	1115	1115	1115	1115	1115	



TEST NUMBER: P563095

CATALOG NUMBER: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	860.7	860.7	860.7	860.7	860.7
2.5°	865.8	858.3	860.7	858.7	855.6
5°	863.9	855.3	858.3	855.9	855.1
7.5°	857.7	849.1	853.1	851.4	850.7
10°	851.9	843.4	848.0	846.3	845.6
12.5°	844.3	836.3	841.6	840.0	839.8
15°	831.2	824.2	831.2	831.2	830.4
17.5°	814.8	808.4	815.9	816.4	815.9
20°	803.3	796.3	805.7	804.9	805.7
22.5°	789.3	783.5	793.6	791.5	792.3
25°	767.5	762.0	773.0	770.6	770.6
27.5°	741.6	737.7	749.8	747.2	747.2
30°	724.4	720.5	733.2	730.0	730.0
32.5°	705.3	702.6	714.7	710.9	710.9
35°	675.0	673.5	685.4	680.6	680.6
37.5°	643.8	642.4	653.2	647.4	645.5
40°	620.8	620.0	629.6	623.2	623.2
42.5°	597.9	597.1	605.4	597.7	597.7
45°	562.6	561.1	566.6	559.4	557.9
47.5°	524.2	522.7	526.1	518.3	517.5
50°	498.1	496.5	498.1	490.9	490.1
52.5°	471.3	468.5	468.8	461.6	461.4
55°	430.4	424.9	424.8	418.4	418.4
57.5°	387.0	379.8	380.5	375.0	374.2
60°	357.0	349.2	349.9	345.1	344.3
62.5°	327.7	318.7	320.5	315.1	315.0
65°	278.9	272.7	273.4	271.0	271.0
67.5°	232.1	226.3	230.5	228.6	228.4
70°	197.6	193.7	199.2	199.2	198.4
72.5°	165.8	165.6	172.5	172.5	172.9
75°	120.3	125.8	133.1	133.9	133.9
77.5°	80.3	90.0	98.0	98.3	98.2
80°	57.4	68.3	75.7	77.3	76.5
82.5°	38.9	50.4	56.6	58.2	57.4
85°	17.5	26.9	31.9	32.7	31.9
87.5°	5.6	12.1	15.9	16.1	14.6
90°	2.4	7.1	15.6	16.8	15.6
92.5°	34.1	124.2	245.1	106.4	77.1
95°	80.4	282.3	861.9	446.1	265.3
97.5°	129.2	323.8	1343.6	1111.9	816.6
100°	165.7	340.6	1493.4	1557.4	1259.3
102.5°	199.3	363.8	1546.2	1895.3	1672.3
105°	260.5	402.5	1554.6	2293.2	2199.3
107.5°	317.2	446.8	1486.7	2541.4	2572.6
110°	361.3	478.7	1426.2	2608.0	2740.7



TEST NUMBER: P563095

CATALOG NUMBER: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	400.7	510.6	1370.5	2594.7	2817.5
115°	458.6	560.7	1289.3	2495.9	2817.5
117.5°	515.2	611.0	1235.8	2344.9	2709.5
120°	549.8	643.7	1204.1	2236.5	2608.6
122.5°	582.5	674.5	1184.9	2120.4	2495.3
125°	627.8	719.4	1162.1	1961.0	2303.7
127.5°	669.6	759.5	1148.6	1830.9	2132.3
130°	692.7	785.4	1142.9	1750.5	2022.8
132.5°	716.7	808.5	1137.1	1678.0	1928.7
135°	752.7	841.9	1130.8	1583.4	1792.3
137.5°	789.0	873.2	1125.6	1506.6	1676.8
140°	813.9	892.6	1123.6	1457.2	1608.6
142.5°	837.9	911.9	1119.8	1412.6	1545.3
145°	875.1	940.9	1115.2	1355.3	1458.6
147.5°	909.0	967.2	1110.0	1303.4	1382.7
150°	934.0	985.6	1108.0	1275.1	1338.5
152.5°	957.0	1002.1	1107.1	1249.0	1301.1
155°	988.0	1026.7	1105.6	1215.8	1255.7
157.5°	1020.2	1047.2	1105.9	1192.7	1219.0
160°	1038.4	1060.7	1106.8	1178.1	1196.9
162.5°	1052.8	1071.4	1107.8	1166.5	1180.5
165°	1075.6	1086.2	1110.4	1153.8	1159.7
167.5°	1091.2	1098.5	1110.7	1142.9	1145.7
170°	1100.8	1104.4	1111.6	1138.1	1138.1
172.5°	1108.5	1109.2	1111.6	1132.3	1131.3
175°	1116.4	1115.3	1111.6	1126.0	1123.6
177.5°	1119.1	1116.3	1111.4	1120.9	1118.1
180°	1115.2	1115.2	1115.2	1115.2	1115.2

(END OF REPORT)