

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563167

Luminaire Tested: **SQ4-PC3-150U-125D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563167
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-125D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13063.2 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 127.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563167
CATALOG NUMBER: SQ4-PC3-150U-125D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563167

CATALOG NUMBER: SQ4-PC3-150U-125D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	97	92	89	85	88	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	70	80	74	69	65	62	58	55	51	48	46	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13230	13230	13230
5°	13330	13244	13195
10°	13298	13235	13198
15°	13228	13228	13215
20°	13141	13180	13180
25°	13017	13111	13070
30°	12858	13014	12957
35°	12666	12861	12772
40°	12457	12633	12506
45°	12231	12318	12128
50°	11911	11911	11721
55°	11533	11384	11213
60°	10977	10755	10584
65°	10146	9942	9856
70°	8882	8954	8918
75°	7146	7904	7952
80°	5079	6702	6773
85°	3091	5625	5625



TEST NUMBER: P563167

CATALOG NUMBER: SQ4-PC3-150U-125D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.6	1.6
10°-20°	584.2	4.5
20°-30°	884.7	6.8
30°-40°	1060.6	8.1
40°-50°	1081.5	8.3
50°-60°	944.0	7.2
60°-70°	675.9	5.2
70°-80°	348.1	2.7
80°-90°	90.4	0.7
90°-100°	518.3	4.0
100°-110°	1401.4	10.7
110°-120°	1473.3	11.3
120°-130°	1196.7	9.2
130°-140°	938.7	7.2
140°-150°	720.5	5.5
150°-160°	518.2	4.0
160°-170°	316.5	2.4
170°-180°	106.7	0.8
0°-30°	1672.4	12.8
0°-40°	2733.0	20.9
0°-60°	4758.5	36.4
0°-90°	5872.8	45.0
90°-120°	3393.0	26.0
90°-150°	6249.0	47.8
90°-180°	7190.0	55.0
0°-180°	13063.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2151	2151	2151	2151	2151	
5°	2159	2138	2145	2139	2137	205
15°	2077	2060	2077	2077	2075	586
25°	1918	1904	1932	1926	1926	883
35°	1687	1683	1713	1701	1701	1055
45°	1406	1402	1416	1398	1394	1082
55°	1076	1062	1062	1046	1046	959
65°	697	682	683	677	677	689
75°	301	314	333	335	335	325
85°	44	67	80	82	80	60
90°	2	7	16	17	16	7
95°	80	282	862	446	265	84
105°	260	402	1555	2293	2199	274
115°	459	561	1289	2496	2818	453
125°	628	719	1162	1961	2304	560
135°	753	842	1131	1583	1792	582
145°	875	941	1115	1355	1459	547
155°	988	1027	1106	1216	1256	456
165°	1076	1086	1110	1154	1160	303
175°	1116	1115	1112	1126	1124	106
180°	1115	1115	1115	1115	1115	

TEST NUMBER: P563167

CATALOG NUMBER: SQ4-PC3-150U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2151.0	2151.0	2151.0	2151.0	2151.0
2.5°	2163.7	2145.1	2151.0	2146.0	2138.3
5°	2159.0	2137.5	2145.0	2139.0	2137.1
7.5°	2143.4	2122.0	2131.9	2127.9	2125.9
10°	2129.1	2107.7	2119.1	2115.1	2113.2
12.5°	2110.0	2090.1	2103.2	2099.2	2098.8
15°	2077.3	2059.8	2077.3	2077.3	2075.3
17.5°	2036.3	2020.3	2039.1	2040.2	2039.1
20°	2007.6	1990.1	2013.6	2011.6	2013.6
22.5°	1972.5	1958.1	1983.3	1978.2	1980.1
25°	1918.0	1904.3	1931.9	1925.9	1925.9
27.5°	1853.4	1843.7	1873.8	1867.4	1867.4
30°	1810.4	1800.7	1832.3	1824.4	1824.4
32.5°	1762.6	1756.0	1786.1	1776.6	1776.6
35°	1686.9	1683.0	1712.8	1700.9	1700.9
37.5°	1608.9	1605.4	1632.4	1617.9	1613.3
40°	1551.5	1549.6	1573.4	1557.5	1557.5
42.5°	1494.2	1492.2	1512.9	1493.8	1493.8
45°	1406.1	1402.2	1416.1	1398.1	1394.2
47.5°	1310.1	1306.2	1314.9	1295.3	1293.4
50°	1244.8	1240.9	1244.8	1226.8	1224.9
52.5°	1177.9	1170.9	1171.5	1153.6	1153.2
55°	1075.5	1061.9	1061.6	1045.6	1045.6
57.5°	967.2	949.2	950.8	937.2	935.3
60°	892.3	872.8	874.3	862.3	860.4
62.5°	819.0	796.4	801.0	787.5	787.1
65°	697.1	681.5	683.1	677.2	677.2
67.5°	580.0	565.6	576.0	571.2	570.8
70°	493.9	484.2	497.9	497.9	495.9
72.5°	414.3	413.9	431.0	431.0	432.2
75°	300.7	314.4	332.6	334.6	334.6
77.5°	200.8	224.9	245.0	245.8	245.4
80°	143.4	170.7	189.2	193.1	191.2
82.5°	97.2	126.0	141.4	145.3	143.4
85°	43.8	67.2	79.7	81.6	79.7
87.5°	13.2	28.2	35.0	35.2	31.8
90°	2.4	7.1	15.6	16.8	15.6
92.5°	34.1	124.2	245.1	106.4	77.1
95°	80.4	282.3	861.9	446.1	265.3
97.5°	129.2	323.8	1343.6	1111.9	816.6
100°	165.7	340.6	1493.4	1557.4	1259.3
102.5°	199.3	363.8	1546.2	1895.3	1672.3
105°	260.5	402.5	1554.6	2293.2	2199.3
107.5°	317.2	446.8	1486.7	2541.4	2572.6
110°	361.3	478.7	1426.2	2608.0	2740.7



TEST NUMBER: P563167

CATALOG NUMBER: SQ4-PC3-150U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	400.7	510.6	1370.5	2594.7	2817.5
115°	458.6	560.7	1289.3	2495.9	2817.5
117.5°	515.2	611.0	1235.8	2344.9	2709.5
120°	549.8	643.7	1204.1	2236.5	2608.6
122.5°	582.5	674.5	1184.9	2120.4	2495.3
125°	627.8	719.4	1162.1	1961.0	2303.7
127.5°	669.6	759.5	1148.6	1830.9	2132.3
130°	692.7	785.4	1142.9	1750.5	2022.8
132.5°	716.7	808.5	1137.1	1678.0	1928.7
135°	752.7	841.9	1130.8	1583.4	1792.3
137.5°	789.0	873.2	1125.6	1506.6	1676.8
140°	813.9	892.6	1123.6	1457.2	1608.6
142.5°	837.9	911.9	1119.8	1412.6	1545.3
145°	875.1	940.9	1115.2	1355.3	1458.6
147.5°	909.0	967.2	1110.0	1303.4	1382.7
150°	934.0	985.6	1108.0	1275.1	1338.5
152.5°	957.0	1002.1	1107.1	1249.0	1301.1
155°	988.0	1026.7	1105.6	1215.8	1255.7
157.5°	1020.2	1047.2	1105.9	1192.7	1219.0
160°	1038.4	1060.7	1106.8	1178.1	1196.9
162.5°	1052.8	1071.4	1107.8	1166.5	1180.5
165°	1075.6	1086.2	1110.4	1153.8	1159.7
167.5°	1091.2	1098.5	1110.7	1142.9	1145.7
170°	1100.8	1104.4	1111.6	1138.1	1138.1
172.5°	1108.5	1109.2	1111.6	1132.3	1131.3
175°	1116.4	1115.3	1111.6	1126.0	1123.6
177.5°	1119.1	1116.3	1111.4	1120.9	1118.1
180°	1115.2	1115.2	1115.2	1115.2	1115.2

(END OF REPORT)