

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519704

Luminaire Tested: **SQ4-075U-0D-930-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519704
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2382.3 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 18.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519704
CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519704

CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	2721	32287	8818
100°	2853	27411	22570
105°	3023	18640	26486
110°	3170	12697	25438
115°	3279	9156	20689
120°	3345	7250	15965
125°	3330	6120	12127
130°	3284	5361	9515
135°	3259	4822	7685
140°	3252	4423	6372
145°	3252	4101	5380
150°	3282	3863	4666
155°	3327	3683	4174
160°	3354	3552	3850
165°	3374	3471	3634
170°	3382	3411	3499
175°	3387	3372	3408



TEST NUMBER: P519704

CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	172.5	7.2
100°-110°	474.5	19.9
110°-120°	489.8	20.6
120°-130°	392.4	16.5
130°-140°	308.2	12.9
140°-150°	236.2	9.9
150°-160°	169.8	7.1
160°-170°	103.8	4.4
170°-180°	35.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1136.8	47.7
90°-150°	2073.6	87.0
90°-180°	2382.0	100.0
0°-180°	2382.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	3	5	7	7	
95°	26	94	305	130	83	29
105°	85	130	523	796	743	89
115°	150	183	419	835	948	148
125°	207	236	380	644	754	185
135°	250	277	370	520	589	193
145°	289	308	364	444	478	181
155°	327	337	362	399	410	150
165°	353	358	363	378	380	100
175°	366	366	364	369	368	35
180°	366	366	366	366	366	



TEST NUMBER: P519704

CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	0.8	3.1	5.4	7.0	7.0
92.5°	10.7	45.9	79.5	30.5	25.1
95°	25.7	94.1	305.0	130.4	83.3
97.5°	41.9	104.4	465.4	358.6	253.0
100°	53.7	110.7	515.9	520.7	424.8
102.5°	64.9	118.3	528.9	646.0	558.0
105°	84.8	130.5	522.9	796.3	743.0
107.5°	103.8	145.5	493.1	869.9	885.7
110°	117.5	155.5	470.7	888.2	943.0
112.5°	129.9	166.8	448.3	876.4	959.8
115°	150.2	182.9	419.4	835.1	947.7
117.5°	169.5	199.6	401.0	777.1	904.4
120°	181.3	210.2	392.9	733.6	865.2
122.5°	191.9	220.8	387.3	695.5	820.4
125°	207.0	235.9	380.5	643.6	753.9
127.5°	221.3	248.8	376.0	600.4	697.1
130°	228.8	256.9	373.5	574.7	662.9
132.5°	237.5	265.6	371.6	552.1	631.8
135°	249.8	277.1	369.6	520.5	589.0
137.5°	261.3	286.7	367.9	495.0	551.5
140°	270.0	293.6	367.2	478.1	529.1
142.5°	277.5	299.2	366.0	463.0	506.7
145°	288.7	308.4	364.1	443.5	477.7
147.5°	300.6	317.7	363.2	426.2	453.6
150°	308.1	323.3	362.6	416.7	438.0
152.5°	315.0	329.0	362.0	408.6	426.2
155°	326.8	337.4	361.8	398.6	410.0
157.5°	335.3	344.0	361.8	390.5	398.4
160°	341.6	348.4	361.8	386.1	392.1
162.5°	346.5	352.2	362.4	382.3	387.2
165°	353.2	357.8	363.4	378.2	380.5
167.5°	357.9	361.4	364.1	374.7	375.3
170°	361.0	363.3	364.1	373.5	373.5
172.5°	363.5	364.6	364.1	371.6	371.0
175°	365.7	366.4	364.1	368.8	368.0
177.5°	366.3	366.3	363.8	367.5	366.3
180°	365.7	365.7	365.7	365.7	365.7

(END OF REPORT)