

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563191

Luminaire Tested: **SQ4-PP3-025U-050D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563191
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-050D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3480.7 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 34.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563191
CATALOG NUMBER: SQ4-PP3-025U-050D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563191

CATALOG NUMBER: SQ4-PP3-025U-050D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	102	98	94	90	96	92	89	86	82	79	77	72	71	69	64	62	61	57				
2	93	85	79	74	87	81	75	71	72	68	64	64	61	58	56	54	52	48				
3	85	75	68	62	80	71	65	59	64	58	54	57	53	49	50	47	44	41				
4	78	67	59	53	73	63	56	51	57	51	46	51	46	42	45	41	38	35				
5	72	60	51	45	67	57	49	44	51	45	40	46	41	37	41	37	33	31				
6	66	54	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30	27				
7	61	49	40	35	57	46	39	34	42	36	31	38	32	29	34	29	26	24				
8	57	44	36	31	53	42	35	30	38	32	28	34	29	26	31	27	24	21				
9	53	40	33	28	50	39	32	27	35	29	25	32	27	23	29	24	21	19				
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5592	5592	5592
5°	5633	5598	5578
10°	5623	5584	5559
15°	5586	5556	5525
20°	5549	5518	5476
25°	5483	5445	5391
30°	5381	5353	5286
35°	5241	5205	5139
40°	5073	5041	4984
45°	4935	4900	4851
50°	4758	4727	4681
55°	4511	4451	4417
60°	4106	3989	3970
65°	3618	3467	3455
70°	3124	2994	2994
75°	2688	2650	2614
80°	2370	2398	2341
85°	1856	2025	2025



TEST NUMBER: P563191

CATALOG NUMBER: SQ4-PP3-025U-050D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.0	2.5
10°-20°	245.5	7.1
20°-30°	367.7	10.6
30°-40°	431.2	12.4
40°-50°	432.6	12.4
50°-60°	369.0	10.6
60°-70°	240.7	6.9
70°-80°	120.7	3.5
80°-90°	34.4	1.0
90°-100°	86.7	2.5
100°-110°	227.9	6.5
110°-120°	236.3	6.8
120°-130°	189.6	5.4
130°-140°	148.7	4.3
140°-150°	114.2	3.3
150°-160°	82.2	2.4
160°-170°	50.3	1.4
170°-180°	17.0	0.5
0°-30°	699.1	20.1
0°-40°	1130.3	32.5
0°-60°	1931.9	55.5
0°-90°	2327.7	66.9
90°-120°	551.0	15.8
90°-150°	1003.4	28.8
90°-180°	1153.0	33.1
0°-180°	3480.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	909	909	909	909	909	
5°	912	904	907	904	904	87
15°	877	869	872	869	868	247
25°	808	799	802	795	794	372
35°	698	691	693	685	684	436
45°	567	563	563	558	558	437
55°	421	419	415	413	412	374
65°	249	244	238	237	237	248
75°	113	113	112	111	110	123
85°	26	29	29	29	29	31
90°	1	3	9	5	5	2
95°	11	45	149	77	52	13
105°	41	62	252	382	357	43
115°	73	89	202	403	460	72
125°	102	114	184	310	366	90
135°	121	133	178	250	284	94
145°	140	149	176	214	230	88
155°	158	163	176	193	198	73
165°	171	173	176	182	185	48
175°	178	178	177	179	179	17
180°	178	178	178	178	178	

TEST NUMBER: P563191

CATALOG NUMBER: SQ4-PP3-025U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	909.1	909.1	909.1	909.1	909.1
2.5°	914.8	907.4	909.1	907.7	904.0
5°	912.3	903.7	906.7	903.5	903.5
7.5°	906.1	896.7	899.7	896.5	896.4
10°	900.3	891.0	894.0	890.8	890.0
12.5°	892.1	882.7	886.3	882.5	882.3
15°	877.2	868.7	872.5	869.2	867.7
17.5°	860.5	851.2	855.7	851.2	850.6
20°	847.8	838.4	843.0	836.6	836.6
22.5°	832.5	823.1	828.3	820.0	820.0
25°	807.9	798.6	802.3	795.1	794.4
27.5°	778.8	769.6	773.5	765.4	765.2
30°	757.7	749.1	753.7	745.0	744.2
32.5°	734.8	726.8	730.1	721.4	720.6
35°	698.0	690.9	693.2	685.2	684.4
37.5°	659.2	652.1	654.6	647.8	647.4
40°	631.8	627.2	627.8	622.2	620.7
42.5°	606.3	601.0	601.7	596.1	595.8
45°	567.3	563.4	563.3	557.7	557.7
47.5°	525.9	522.9	522.0	517.4	517.3
50°	497.2	494.8	494.0	490.0	489.2
52.5°	467.2	466.1	463.4	460.0	459.9
55°	420.7	419.1	415.1	412.7	411.9
57.5°	370.2	367.1	362.5	359.0	359.7
60°	333.8	330.7	324.3	322.7	322.7
62.5°	298.8	295.0	288.6	286.4	287.6
65°	248.6	243.9	238.2	236.7	237.4
67.5°	203.0	198.8	192.7	192.6	192.0
70°	173.7	171.4	166.5	166.5	166.5
72.5°	147.6	146.5	142.9	142.9	142.3
75°	113.1	113.1	111.5	110.7	110.0
77.5°	84.8	85.1	84.3	83.5	82.1
80°	66.9	68.5	67.7	66.9	66.1
82.5°	50.4	51.9	51.8	50.4	50.2
85°	26.3	28.6	28.7	28.7	28.7
87.5°	7.2	10.2	12.0	11.1	11.7
90°	1.1	3.4	9.1	4.6	4.6
92.5°	4.8	23.1	51.1	22.6	14.6
95°	11.4	44.9	149.4	77.0	52.5
97.5°	19.8	49.3	223.5	177.7	130.9
100°	26.2	53.0	246.3	249.6	193.8
102.5°	31.7	56.7	252.7	310.9	263.2
105°	41.0	62.2	252.0	382.5	356.9
107.5°	50.6	70.3	237.6	419.8	426.0
110°	57.0	74.9	225.8	429.3	456.1



TEST NUMBER: P563191

CATALOG NUMBER: SQ4-PP3-025U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	63.4	80.3	214.8	423.3	464.3
115°	73.0	88.6	201.8	402.7	459.5
117.5°	82.3	96.6	192.9	374.1	437.2
120°	87.8	101.2	189.3	354.9	416.2
122.5°	93.3	106.7	186.5	335.7	396.1
125°	101.5	113.7	183.6	310.3	366.0
127.5°	108.1	120.6	181.1	289.8	336.8
130°	111.7	125.1	180.2	276.9	320.4
132.5°	115.4	128.8	179.2	265.9	304.9
135°	120.9	133.1	177.9	250.5	283.9
137.5°	126.6	138.6	177.7	238.9	266.4
140°	131.1	142.3	176.7	229.8	255.4
142.5°	134.8	145.0	176.7	223.3	245.4
145°	140.3	149.2	175.6	213.6	230.3
147.5°	145.7	154.4	175.6	205.6	219.4
150°	149.4	157.2	175.6	200.9	212.1
152.5°	153.0	159.0	175.6	197.2	205.7
155°	158.5	163.0	175.6	192.8	198.4
157.5°	162.6	166.8	175.6	188.9	192.9
160°	165.3	168.7	175.6	187.1	189.3
162.5°	168.1	170.5	175.6	185.2	187.5
165°	171.0	173.3	175.6	182.5	184.7
167.5°	173.8	174.9	176.7	181.3	182.2
170°	175.6	176.7	176.7	181.3	181.3
172.5°	176.5	176.7	176.7	180.4	179.5
175°	177.9	177.9	176.7	179.0	179.0
177.5°	177.9	177.9	177.0	178.8	177.9
180°	177.9	177.9	177.9	177.9	177.9

(END OF REPORT)