

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563263

Luminaire Tested: **SQ4-PP3-025U-125D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563263
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6968.9 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 77.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563263
CATALOG NUMBER: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563263

CATALOG NUMBER: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	111	111	111	111	102	102	102	94	94	94	87	87	87	83
1	106	101	97	94	101	97	94	91	90	87	85	84	81	79	77	76	74	71
2	96	89	82	77	92	86	80	75	79	75	71	74	70	67	68	66	63	60
3	88	78	71	65	84	76	69	63	70	65	60	65	61	57	61	57	54	51
4	81	70	61	55	77	67	60	54	63	56	51	58	53	49	55	50	47	44
5	74	62	54	48	71	60	52	47	56	50	45	53	47	43	49	45	41	38
6	69	56	48	42	66	54	46	41	51	44	39	48	42	37	45	40	36	34
7	64	51	43	37	61	49	42	36	46	40	35	44	38	33	41	36	32	30
8	59	46	38	33	57	45	37	32	42	36	31	40	34	30	38	33	29	27
9	55	43	35	29	53	41	34	29	39	32	28	37	31	27	35	30	26	24
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	32	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13975	13975	13975
5°	14077	13991	13942
10°	14053	13953	13892
15°	13960	13884	13808
20°	13867	13790	13685
25°	13703	13608	13473
30°	13449	13379	13209
35°	13097	13007	12843
40°	12678	12599	12454
45°	12332	12246	12124
50°	11889	11813	11699
55°	11275	11125	11039
60°	10263	9969	9920
65°	9042	8665	8636
70°	7807	7485	7485
75°	6721	6626	6531
80°	5926	5997	5855
85°	4637	5060	5060



TEST NUMBER: P563263

CATALOG NUMBER: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	3.1
10°-20°	613.4	8.8
20°-30°	918.8	13.2
30°-40°	1077.7	15.5
40°-50°	1081.1	15.5
50°-60°	922.3	13.2
60°-70°	601.5	8.6
70°-80°	301.8	4.3
80°-90°	84.5	1.2
90°-100°	86.7	1.2
100°-110°	227.9	3.3
110°-120°	236.3	3.4
120°-130°	189.6	2.7
130°-140°	148.7	2.1
140°-150°	114.2	1.6
150°-160°	82.2	1.2
160°-170°	50.3	0.7
170°-180°	17.0	0.2
0°-30°	1747.1	25.1
0°-40°	2824.8	40.5
0°-60°	4828.2	69.3
0°-90°	5815.9	83.5
90°-120°	551.0	7.9
90°-150°	1003.4	14.4
90°-180°	1153.0	16.5
0°-180°	6968.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2272	2272	2272	2272	2272	
5°	2280	2258	2266	2258	2258	217
15°	2192	2171	2180	2172	2168	618
25°	2019	1996	2005	1987	1985	928
35°	1744	1727	1732	1712	1710	1090
45°	1418	1408	1408	1394	1394	1092
55°	1051	1048	1037	1031	1029	934
65°	621	610	595	591	593	620
75°	283	283	279	277	275	307
85°	66	72	72	72	72	77
90°	1	3	9	5	5	3
95°	11	45	149	77	52	13
105°	41	62	252	382	357	43
115°	73	89	202	403	460	72
125°	102	114	184	310	366	90
135°	121	133	178	250	284	94
145°	140	149	176	214	230	88
155°	158	163	176	193	198	73
165°	171	173	176	182	185	48
175°	178	178	177	179	179	17
180°	178	178	178	178	178	

TEST NUMBER: P563263

CATALOG NUMBER: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2272.0	2272.0	2272.0	2272.0	2272.0
2.5°	2286.3	2267.6	2272.0	2268.6	2259.2
5°	2279.9	2258.5	2266.0	2258.0	2258.0
7.5°	2264.4	2241.0	2248.5	2240.5	2240.1
10°	2250.1	2226.7	2234.1	2226.1	2224.2
12.5°	2229.3	2206.0	2215.0	2205.4	2205.1
15°	2192.3	2170.9	2180.4	2172.3	2168.4
17.5°	2150.5	2127.1	2138.5	2127.4	2125.8
20°	2118.6	2095.3	2106.7	2090.8	2090.8
22.5°	2080.4	2057.0	2070.0	2049.3	2049.3
25°	2019.1	1995.7	2005.1	1987.2	1985.2
27.5°	1946.2	1923.2	1933.1	1912.7	1912.3
30°	1893.6	1872.2	1883.7	1861.7	1859.8
32.5°	1836.3	1816.4	1824.7	1802.8	1800.8
35°	1744.3	1726.8	1732.3	1712.4	1710.4
37.5°	1647.5	1629.6	1636.0	1618.8	1618.0
40°	1579.0	1567.3	1569.1	1555.0	1551.1
42.5°	1515.3	1502.1	1503.8	1489.8	1489.0
45°	1417.7	1408.0	1407.8	1393.8	1393.8
47.5°	1314.2	1306.8	1304.6	1293.1	1292.7
50°	1242.5	1236.7	1234.5	1224.5	1222.6
52.5°	1167.6	1164.9	1158.1	1149.7	1149.3
55°	1051.4	1047.5	1037.4	1031.4	1029.4
57.5°	925.1	917.3	906.0	897.3	898.8
60°	834.3	826.5	810.4	806.4	806.4
62.5°	746.7	737.4	721.2	715.7	718.8
65°	621.3	609.6	595.4	591.4	593.4
67.5°	507.4	496.8	481.5	481.4	479.9
70°	434.1	428.2	416.2	416.2	416.2
72.5°	368.8	366.0	357.2	357.2	355.6
75°	282.8	282.8	278.8	276.7	274.8
77.5°	211.9	212.6	210.7	208.6	205.1
80°	167.3	171.2	169.3	167.2	165.3
82.5°	125.8	129.7	129.4	125.8	125.4
85°	65.7	71.6	71.7	71.7	71.7
87.5°	17.8	24.4	27.3	26.4	28.0
90°	1.1	3.4	9.1	4.6	4.6
92.5°	4.8	23.1	51.1	22.6	14.6
95°	11.4	44.9	149.4	77.0	52.5
97.5°	19.8	49.3	223.5	177.7	130.9
100°	26.2	53.0	246.3	249.6	193.8
102.5°	31.7	56.7	252.7	310.9	263.2
105°	41.0	62.2	252.0	382.5	356.9
107.5°	50.6	70.3	237.6	419.8	426.0
110°	57.0	74.9	225.8	429.3	456.1



TEST NUMBER: P563263

CATALOG NUMBER: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	63.4	80.3	214.8	423.3	464.3
115°	73.0	88.6	201.8	402.7	459.5
117.5°	82.3	96.6	192.9	374.1	437.2
120°	87.8	101.2	189.3	354.9	416.2
122.5°	93.3	106.7	186.5	335.7	396.1
125°	101.5	113.7	183.6	310.3	366.0
127.5°	108.1	120.6	181.1	289.8	336.8
130°	111.7	125.1	180.2	276.9	320.4
132.5°	115.4	128.8	179.2	265.9	304.9
135°	120.9	133.1	177.9	250.5	283.9
137.5°	126.6	138.6	177.7	238.9	266.4
140°	131.1	142.3	176.7	229.8	255.4
142.5°	134.8	145.0	176.7	223.3	245.4
145°	140.3	149.2	175.6	213.6	230.3
147.5°	145.7	154.4	175.6	205.6	219.4
150°	149.4	157.2	175.6	200.9	212.1
152.5°	153.0	159.0	175.6	197.2	205.7
155°	158.5	163.0	175.6	192.8	198.4
157.5°	162.6	166.8	175.6	188.9	192.9
160°	165.3	168.7	175.6	187.1	189.3
162.5°	168.1	170.5	175.6	185.2	187.5
165°	171.0	173.3	175.6	182.5	184.7
167.5°	173.8	174.9	176.7	181.3	182.2
170°	175.6	176.7	176.7	181.3	181.3
172.5°	176.5	176.7	176.7	180.4	179.5
175°	177.9	177.9	176.7	179.0	179.0
177.5°	177.9	177.9	177.0	178.8	177.9
180°	177.9	177.9	177.9	177.9	177.9

(END OF REPORT)