

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563407

Luminaire Tested: **SQ4-PP3-075U-075D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563407  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7004.3 lumens  
Efficiency: N/A  
Efficacy: 103.0 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 68  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563407  
CATALOG NUMBER: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563407

CATALOG NUMBER: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	43	42	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8241	8241	8241
5°	8302	8251	8222
10°	8288	8229	8192
15°	8233	8188	8143
20°	8179	8132	8071
25°	8082	8026	7946
30°	7932	7890	7790
35°	7724	7672	7574
40°	7477	7430	7345
45°	7273	7222	7150
50°	7012	6967	6899
55°	6649	6561	6510
60°	6052	5880	5851
65°	5333	5110	5094
70°	4604	4413	4413
75°	3964	3907	3852
80°	3493	3535	3454
85°	2738	2985	2985



TEST NUMBER: P563407

CATALOG NUMBER: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.7	1.8
10°-20°	361.8	5.2
20°-30°	541.9	7.7
30°-40°	635.6	9.1
40°-50°	637.6	9.1
50°-60°	543.9	7.8
60°-70°	354.7	5.1
70°-80°	178.0	2.5
80°-90°	50.7	0.7
90°-100°	258.7	3.7
100°-110°	711.8	10.2
110°-120°	734.7	10.5
120°-130°	588.6	8.4
130°-140°	462.3	6.6
140°-150°	354.3	5.1
150°-160°	254.7	3.6
160°-170°	155.8	2.2
170°-180°	52.5	0.7
0°-30°	1030.4	14.7
0°-40°	1666.0	23.8
0°-60°	2847.5	40.7
0°-90°	3430.8	49.0
90°-120°	1705.2	24.3
90°-150°	3110.5	44.4
90°-180°	3573.0	51.0
0°-180°	7004.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1345	1332	1336	1332	1332	128
15°	1293	1280	1286	1281	1279	365
25°	1191	1177	1183	1172	1171	548
35°	1029	1018	1022	1010	1009	643
45°	836	830	830	822	822	644
55°	620	618	612	608	607	551
65°	366	360	351	349	350	366
75°	167	167	164	163	162	181
85°	39	42	42	42	42	46
90°	1	5	8	10	10	4
95°	38	141	458	196	125	41
105°	127	196	784	1194	1115	134
115°	225	274	629	1253	1422	222
125°	310	354	571	965	1131	277
135°	375	416	554	781	884	289
145°	433	463	546	665	717	272
155°	490	506	543	598	615	225
165°	530	537	545	567	571	149
175°	548	550	546	553	552	52
180°	548	548	548	548	548	

TEST NUMBER: P563407

CATALOG NUMBER: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1339.9	1339.9	1339.9	1339.9	1339.9
2.5°	1348.4	1337.3	1339.9	1337.9	1332.4
5°	1344.6	1332.0	1336.4	1331.7	1331.7
7.5°	1335.4	1321.7	1326.1	1321.4	1321.1
10°	1327.0	1313.2	1317.6	1312.9	1311.7
12.5°	1314.8	1301.0	1306.3	1300.7	1300.5
15°	1292.9	1280.3	1285.9	1281.1	1278.8
17.5°	1268.3	1254.5	1261.2	1254.6	1253.7
20°	1249.5	1235.7	1242.4	1233.0	1233.0
22.5°	1226.9	1213.2	1220.8	1208.6	1208.6
25°	1190.8	1177.0	1182.6	1172.0	1170.8
27.5°	1147.8	1134.2	1140.0	1128.1	1127.8
30°	1116.8	1104.2	1110.9	1098.0	1096.8
32.5°	1083.0	1071.3	1076.2	1063.2	1062.1
35°	1028.7	1018.4	1021.7	1009.9	1008.7
37.5°	971.6	961.1	964.8	954.7	954.3
40°	931.2	924.4	925.4	917.1	914.8
42.5°	893.7	885.9	886.9	878.6	878.2
45°	836.1	830.4	830.3	822.0	822.0
47.5°	775.1	770.7	769.4	762.6	762.4
50°	732.8	729.3	728.1	722.2	721.0
52.5°	688.6	687.0	683.0	678.1	677.8
55°	620.0	617.7	611.8	608.3	607.1
57.5°	545.6	541.0	534.3	529.2	530.1
60°	492.0	487.5	478.0	475.6	475.6
62.5°	440.4	434.9	425.3	422.1	423.9
65°	366.4	359.5	351.1	348.8	350.0
67.5°	299.2	293.0	284.0	283.9	283.0
70°	256.0	252.6	245.4	245.4	245.4
72.5°	217.5	215.9	210.7	210.7	209.7
75°	166.8	166.8	164.4	163.2	162.1
77.5°	124.9	125.4	124.2	123.0	121.0
80°	98.6	100.9	99.8	98.6	97.5
82.5°	74.2	76.5	76.3	74.2	74.0
85°	38.8	42.2	42.3	42.3	42.3
87.5°	10.6	14.9	16.7	17.2	18.1
90°	1.2	4.6	8.2	10.5	10.5
92.5°	16.1	68.8	119.3	45.8	37.6
95°	38.5	141.2	457.5	195.6	124.9
97.5°	62.8	156.6	698.2	537.9	379.5
100°	80.5	166.1	773.8	781.0	637.2
102.5°	97.3	177.4	793.4	969.0	837.0
105°	127.2	195.7	784.3	1194.5	1114.6
107.5°	155.7	218.2	739.7	1304.9	1328.6
110°	176.2	233.3	706.1	1332.4	1414.5



TEST NUMBER: P563407

CATALOG NUMBER: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	194.9	250.1	672.5	1314.7	1439.7
115°	225.2	274.3	629.1	1252.6	1421.5
117.5°	254.2	299.4	601.5	1165.6	1356.6
120°	271.9	315.3	589.4	1100.4	1297.8
122.5°	287.8	331.2	581.0	1043.2	1230.6
125°	310.4	353.8	570.7	965.4	1130.9
127.5°	331.9	373.2	563.9	900.6	1045.7
130°	343.1	385.3	560.2	862.0	994.4
132.5°	356.2	398.4	557.4	828.1	947.7
135°	374.6	415.7	554.4	780.8	883.5
137.5°	391.9	430.0	551.8	742.6	827.2
140°	405.0	440.4	550.9	717.2	793.6
142.5°	416.2	448.8	549.0	694.5	760.0
145°	433.0	462.7	546.2	665.2	716.6
147.5°	451.0	476.5	544.8	639.3	680.4
150°	462.2	485.0	543.9	625.1	657.1
152.5°	472.4	493.4	542.9	612.9	639.3
155°	490.2	506.2	542.7	597.9	615.1
157.5°	503.0	516.0	542.7	585.7	597.6
160°	512.4	522.6	542.7	579.1	588.2
162.5°	519.8	528.3	543.6	573.4	580.7
165°	529.9	536.7	545.0	567.3	570.7
167.5°	536.9	542.1	546.2	562.1	563.0
170°	541.5	545.0	546.2	560.2	560.2
172.5°	545.3	546.9	546.2	557.4	556.5
175°	548.5	549.7	546.2	553.2	552.0
177.5°	549.5	549.5	545.7	551.3	549.5
180°	548.5	548.5	548.5	548.5	548.5

(END OF REPORT)