

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563431

Luminaire Tested: **SQ4-PP3-075U-100D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563431
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8131.6 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563431
CATALOG NUMBER: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563431

CATALOG NUMBER: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	53	48
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	46	45	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33	30
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	32	28	25	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	27	23	20	18
9	51	39	32	26	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10950	10950	10950
5°	11031	10964	10925
10°	11012	10934	10886
15°	10939	10880	10820
20°	10867	10805	10724
25°	10738	10664	10558
30°	10539	10484	10351
35°	10264	10193	10064
40°	9935	9872	9760
45°	9664	9596	9501
50°	9316	9257	9167
55°	8835	8717	8651
60°	8043	7813	7773
65°	7085	6789	6768
70°	6118	5864	5864
75°	5266	5190	5117
80°	4644	4697	4587
85°	3634	3966	3966



TEST NUMBER: P563431

CATALOG NUMBER: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.3	2.1
10°-20°	480.7	5.9
20°-30°	720.0	8.9
30°-40°	844.5	10.4
40°-50°	847.2	10.4
50°-60°	722.7	8.9
60°-70°	471.3	5.8
70°-80°	236.5	2.9
80°-90°	66.8	0.8
90°-100°	258.7	3.2
100°-110°	711.8	8.8
110°-120°	734.7	9.0
120°-130°	588.6	7.2
130°-140°	462.3	5.7
140°-150°	354.3	4.4
150°-160°	254.7	3.1
160°-170°	155.8	1.9
170°-180°	52.5	0.6
0°-30°	1369.1	16.8
0°-40°	2213.6	27.2
0°-60°	3783.5	46.5
0°-90°	4558.1	56.1
90°-120°	1705.2	21.0
90°-150°	3110.5	38.3
90°-180°	3573.0	43.9
0°-180°	8131.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1780	1780	1780	1780	1780	
5°	1787	1770	1776	1769	1769	170
15°	1718	1701	1709	1702	1699	485
25°	1582	1564	1571	1557	1556	728
35°	1367	1353	1358	1342	1340	854
45°	1111	1103	1103	1092	1092	855
55°	824	821	813	808	807	732
65°	487	478	466	464	465	486
75°	222	222	218	217	215	240
85°	52	56	56	56	56	61
90°	1	5	8	10	10	4
95°	38	141	458	196	125	41
105°	127	196	784	1194	1115	134
115°	225	274	629	1253	1422	222
125°	310	354	571	965	1131	277
135°	375	416	554	781	884	289
145°	433	463	546	665	717	272
155°	490	506	543	598	615	225
165°	530	537	545	567	571	149
175°	548	550	546	553	552	52
180°	548	548	548	548	548	

TEST NUMBER: P563431

CATALOG NUMBER: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1780.3	1780.3	1780.3	1780.3	1780.3
2.5°	1791.6	1776.9	1780.3	1777.7	1770.4
5°	1786.6	1769.8	1775.7	1769.4	1769.4
7.5°	1774.4	1756.1	1761.9	1755.7	1755.4
10°	1763.2	1744.9	1750.7	1744.4	1742.9
12.5°	1747.0	1728.6	1735.7	1728.2	1727.9
15°	1717.9	1701.1	1708.6	1702.3	1699.2
17.5°	1685.2	1666.9	1675.8	1667.0	1665.8
20°	1660.2	1641.9	1650.8	1638.4	1638.4
22.5°	1630.2	1611.9	1622.1	1605.9	1605.9
25°	1582.2	1563.9	1571.3	1557.2	1555.7
27.5°	1525.1	1507.1	1514.8	1498.9	1498.5
30°	1483.9	1467.1	1476.1	1458.9	1457.4
32.5°	1438.9	1423.4	1429.9	1412.7	1411.2
35°	1366.9	1353.1	1357.5	1341.9	1340.3
37.5°	1291.0	1277.0	1282.0	1268.5	1267.9
40°	1237.3	1228.2	1229.5	1218.6	1215.5
42.5°	1187.4	1177.0	1178.4	1167.4	1166.8
45°	1111.0	1103.3	1103.2	1092.2	1092.2
47.5°	1029.8	1024.0	1022.3	1013.3	1013.0
50°	973.6	969.1	967.4	959.6	958.0
52.5°	915.0	912.8	907.5	900.9	900.6
55°	823.9	820.8	812.9	808.2	806.7
57.5°	724.9	718.8	710.0	703.1	704.3
60°	653.8	647.7	635.1	631.9	631.9
62.5°	585.1	577.8	565.2	560.8	563.3
65°	486.8	477.7	466.5	463.5	465.0
67.5°	397.6	389.3	377.3	377.3	376.0
70°	340.2	335.6	326.1	326.1	326.1
72.5°	289.0	286.8	279.9	279.9	278.7
75°	221.6	221.6	218.4	216.9	215.3
77.5°	166.0	166.6	165.1	163.5	160.7
80°	131.1	134.1	132.6	131.0	129.5
82.5°	98.6	101.7	101.4	98.6	98.3
85°	51.5	56.1	56.2	56.2	56.2
87.5°	14.0	19.5	21.6	22.1	23.3
90°	1.2	4.6	8.2	10.5	10.5
92.5°	16.1	68.8	119.3	45.8	37.6
95°	38.5	141.2	457.5	195.6	124.9
97.5°	62.8	156.6	698.2	537.9	379.5
100°	80.5	166.1	773.8	781.0	637.2
102.5°	97.3	177.4	793.4	969.0	837.0
105°	127.2	195.7	784.3	1194.5	1114.6
107.5°	155.7	218.2	739.7	1304.9	1328.6
110°	176.2	233.3	706.1	1332.4	1414.5

TEST NUMBER: P563431

CATALOG NUMBER: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	194.9	250.1	672.5	1314.7	1439.7
115°	225.2	274.3	629.1	1252.6	1421.5
117.5°	254.2	299.4	601.5	1165.6	1356.6
120°	271.9	315.3	589.4	1100.4	1297.8
122.5°	287.8	331.2	581.0	1043.2	1230.6
125°	310.4	353.8	570.7	965.4	1130.9
127.5°	331.9	373.2	563.9	900.6	1045.7
130°	343.1	385.3	560.2	862.0	994.4
132.5°	356.2	398.4	557.4	828.1	947.7
135°	374.6	415.7	554.4	780.8	883.5
137.5°	391.9	430.0	551.8	742.6	827.2
140°	405.0	440.4	550.9	717.2	793.6
142.5°	416.2	448.8	549.0	694.5	760.0
145°	433.0	462.7	546.2	665.2	716.6
147.5°	451.0	476.5	544.8	639.3	680.4
150°	462.2	485.0	543.9	625.1	657.1
152.5°	472.4	493.4	542.9	612.9	639.3
155°	490.2	506.2	542.7	597.9	615.1
157.5°	503.0	516.0	542.7	585.7	597.6
160°	512.4	522.6	542.7	579.1	588.2
162.5°	519.8	528.3	543.6	573.4	580.7
165°	529.9	536.7	545.0	567.3	570.7
167.5°	536.9	542.1	546.2	562.1	563.0
170°	541.5	545.0	546.2	560.2	560.2
172.5°	545.3	546.9	546.2	557.4	556.5
175°	548.5	549.7	546.2	553.2	552.0
177.5°	549.5	549.5	545.7	551.3	549.5
180°	548.5	548.5	548.5	548.5	548.5

(END OF REPORT)