

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562518

Luminaire Tested: **SQ4-PC3-025U-050D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562518  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2335.3 lumens  
Efficiency: N/A  
Efficacy: 105.7 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 22.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562518  
CATALOG NUMBER: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P562518

CATALOG NUMBER: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	97	93	90	96	92	88	85	82	79	77	72	70	68	64	62	61	57
2	93	85	79	73	87	80	75	70	72	67	63	63	60	57	56	54	51	47
3	85	75	67	61	79	71	64	59	63	58	53	56	52	48	50	46	44	40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	44	41	38	34
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	65	53	45	39	61	50	43	37	45	39	34	41	35	31	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	41	34	29	38	31	27	34	29	25	30	26	23	21
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5294	5294	5294
5°	5334	5299	5280
10°	5321	5296	5281
15°	5293	5293	5288
20°	5258	5273	5273
25°	5208	5247	5230
30°	5146	5207	5185
35°	5068	5146	5110
40°	4985	5055	5004
45°	4894	4929	4852
50°	4767	4767	4689
55°	4615	4555	4486
60°	4392	4303	4235
65°	4061	3978	3943
70°	3555	3582	3569
75°	2859	3162	3183
80°	2035	2683	2710
85°	1239	2255	2255



TEST NUMBER: P562518

CATALOG NUMBER: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.3	2.3
10°-20°	155.8	6.7
20°-30°	236.0	10.1
30°-40°	282.9	12.1
40°-50°	288.5	12.4
50°-60°	251.8	10.8
60°-70°	180.3	7.7
70°-80°	92.9	4.0
80°-90°	24.1	1.0
90°-100°	57.8	2.5
100°-110°	151.9	6.5
110°-120°	157.6	6.7
120°-130°	126.4	5.4
130°-140°	99.2	4.2
140°-150°	76.1	3.3
150°-160°	54.8	2.3
160°-170°	33.5	1.4
170°-180°	11.3	0.5
0°-30°	446.1	19.1
0°-40°	729.1	31.2
0°-60°	1269.4	54.4
0°-90°	1566.7	67.1
90°-120°	367.3	15.7
90°-150°	669.0	28.6
90°-180°	769.0	32.9
0°-180°	2335.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	576	570	572	571	570	55
15°	554	550	554	554	554	156
25°	512	508	515	514	514	235
35°	450	449	457	454	454	281
45°	375	374	378	373	372	289
55°	287	283	283	279	279	256
65°	186	182	182	181	181	184
75°	80	84	89	89	89	87
85°	12	18	21	22	21	16
90°	1	2	6	3	3	1
95°	8	30	100	51	35	8
105°	27	42	168	255	238	29
115°	49	59	135	268	306	48
125°	68	76	122	207	244	60
135°	81	89	119	167	189	62
145°	94	99	117	142	154	59
155°	106	109	117	129	132	49
165°	114	116	117	122	123	32
175°	119	119	118	119	119	11
180°	119	119	119	119	119	

TEST NUMBER: P562518

CATALOG NUMBER: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	573.8	573.8	573.8	573.8	573.8
2.5°	577.2	572.2	573.8	572.5	570.4
5°	575.9	570.2	572.2	570.6	570.1
7.5°	571.8	566.1	568.7	567.6	567.1
10°	568.0	562.2	565.3	564.2	563.7
12.5°	562.9	557.6	561.1	560.0	559.9
15°	554.1	549.5	554.1	554.1	553.6
17.5°	543.2	538.9	543.9	544.3	543.9
20°	535.5	530.9	537.1	536.6	537.1
22.5°	526.2	522.4	529.1	527.7	528.2
25°	511.6	508.0	515.4	513.8	513.8
27.5°	494.4	491.8	499.8	498.1	498.1
30°	483.0	480.4	488.8	486.7	486.7
32.5°	470.2	468.4	476.5	473.9	473.9
35°	450.0	449.0	456.9	453.7	453.7
37.5°	429.2	428.2	435.5	431.6	430.4
40°	413.9	413.4	419.7	415.5	415.5
42.5°	398.6	398.1	403.6	398.5	398.5
45°	375.1	374.1	377.8	372.9	371.9
47.5°	349.5	348.4	350.8	345.5	345.0
50°	332.1	331.0	332.1	327.3	326.7
52.5°	314.2	312.3	312.5	307.7	307.6
55°	286.9	283.3	283.2	278.9	278.9
57.5°	258.0	253.2	253.6	250.0	249.5
60°	238.0	232.8	233.2	230.0	229.5
62.5°	218.5	212.4	213.7	210.1	210.0
65°	186.0	181.8	182.2	180.6	180.6
67.5°	154.7	150.9	153.7	152.4	152.3
70°	131.8	129.2	132.8	132.8	132.3
72.5°	110.5	110.4	115.0	115.0	115.3
75°	80.2	83.9	88.7	89.3	89.3
77.5°	53.6	60.0	65.3	65.6	65.5
80°	38.3	45.5	50.5	51.5	51.0
82.5°	25.9	33.6	37.7	38.8	38.3
85°	11.7	17.9	21.3	21.8	21.3
87.5°	3.6	7.6	9.7	9.1	8.3
90°	0.8	2.2	6.1	3.0	3.0
92.5°	3.2	15.4	34.1	15.1	9.7
95°	7.6	29.9	99.6	51.3	35.0
97.5°	13.2	32.8	149.0	118.5	87.3
100°	17.5	35.3	164.2	166.4	129.2
102.5°	21.1	37.8	168.5	207.3	175.4
105°	27.4	41.5	168.0	255.0	237.9
107.5°	33.8	46.8	158.4	279.8	284.0
110°	38.0	49.9	150.5	286.2	304.1

TEST NUMBER: P562518

CATALOG NUMBER: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	42.3	53.6	143.2	282.2	309.5
115°	48.7	59.1	134.6	268.4	306.4
117.5°	54.9	64.4	128.6	249.4	291.5
120°	58.5	67.5	126.2	236.6	277.5
122.5°	62.2	71.1	124.4	223.8	264.1
125°	67.7	75.8	122.4	206.9	244.0
127.5°	72.1	80.4	120.7	193.2	224.6
130°	74.5	83.4	120.1	184.6	213.6
132.5°	76.9	85.8	119.5	177.3	203.3
135°	80.6	88.8	118.6	167.0	189.3
137.5°	84.4	92.4	118.4	159.3	177.6
140°	87.4	94.9	117.8	153.2	170.3
142.5°	89.9	96.7	117.8	148.9	163.6
145°	93.5	99.4	117.1	142.4	153.6
147.5°	97.2	102.9	117.1	137.0	146.3
150°	99.6	104.8	117.1	134.0	141.4
152.5°	102.0	106.0	117.1	131.5	137.1
155°	105.7	108.6	117.1	128.6	132.3
157.5°	108.4	111.2	117.1	125.9	128.6
160°	110.2	112.5	117.1	124.7	126.2
162.5°	112.0	113.7	117.1	123.5	125.0
165°	114.0	115.5	117.1	121.7	123.1
167.5°	115.9	116.6	117.8	120.9	121.5
170°	117.1	117.8	117.8	120.9	120.9
172.5°	117.7	117.8	117.8	120.2	119.7
175°	118.6	118.6	117.8	119.3	119.3
177.5°	118.6	118.6	118.0	119.2	118.6
180°	118.6	118.6	118.6	118.6	118.6

(END OF REPORT)