

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563863

Luminaire Tested: **SQ4-PR1-025U-050D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563863
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-050D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3466.9 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 34.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563863
CATALOG NUMBER: SQ4-PR1-025U-050D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563863

CATALOG NUMBER: SQ4-PR1-025U-050D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67
1	102	98	94	90	96	92	89	86	82	79	77	72	71	69	64	62	61	57
2	93	86	80	74	88	81	76	71	72	68	64	64	61	58	57	54	52	48
3	85	76	68	63	80	72	65	60	64	59	55	57	53	50	51	47	45	41
4	78	67	59	53	73	64	57	51	57	51	47	51	47	43	45	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	52	44	39	46	40	36	42	37	33	37	33	30	28
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	30	25	32	27	24	29	25	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5691	5691	5691
5°	5742	5698	5669
10°	5724	5684	5654
15°	5699	5664	5633
20°	5670	5634	5592
25°	5630	5592	5528
30°	5570	5530	5451
35°	5487	5439	5362
40°	5362	5305	5209
45°	5143	5054	4949
50°	4759	4644	4553
55°	4153	4059	3974
60°	3500	3470	3401
65°	3027	3039	3016
70°	2780	2795	2795
75°	2671	2671	2690
80°	2511	2540	2511
85°	2025	2251	2251



TEST NUMBER: P563863

CATALOG NUMBER: SQ4-PR1-025U-050D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.5	2.5
10°-20°	250.3	7.2
20°-30°	377.6	10.9
30°-40°	449.9	13.0
40°-50°	443.6	12.8
50°-60°	339.0	9.8
60°-70°	209.8	6.1
70°-80°	119.2	3.4
80°-90°	37.2	1.1
90°-100°	86.7	2.5
100°-110°	227.9	6.6
110°-120°	236.3	6.8
120°-130°	189.6	5.5
130°-140°	148.7	4.3
140°-150°	114.2	3.3
150°-160°	82.2	2.4
160°-170°	50.3	1.5
170°-180°	17.0	0.5
0°-30°	715.4	20.6
0°-40°	1165.3	33.6
0°-60°	1947.9	56.2
0°-90°	2314.0	66.7
90°-120°	551.0	15.9
90°-150°	1003.4	28.9
90°-180°	1153.0	33.3
0°-180°	3466.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	925	925	925	925	925	
5°	930	920	923	920	918	88
15°	895	886	889	886	885	253
25°	830	820	824	815	814	382
35°	731	722	724	715	714	456
45°	591	584	581	571	569	453
55°	387	381	378	372	371	347
65°	208	206	209	207	207	211
75°	112	112	112	113	113	119
85°	29	30	32	32	32	33
90°	1	3	9	5	5	2
95°	11	45	149	77	52	13
105°	41	62	252	382	357	43
115°	73	89	202	403	460	72
125°	102	114	184	310	366	90
135°	121	133	178	250	284	94
145°	140	149	176	214	230	88
155°	158	163	176	193	198	73
165°	171	173	176	182	185	48
175°	178	178	177	179	179	17
180°	178	178	178	178	178	

TEST NUMBER: P563863

CATALOG NUMBER: SQ4-PR1-025U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	925.3	925.3	925.3	925.3	925.3
2.5°	931.0	922.9	925.3	923.2	918.9
5°	930.0	919.9	922.9	919.6	918.1
7.5°	922.9	912.9	915.9	912.6	911.7
10°	916.5	907.1	910.1	906.9	905.3
12.5°	909.5	899.5	903.1	899.2	897.7
15°	895.0	885.6	889.4	886.2	884.6
17.5°	879.0	869.1	872.8	869.1	867.1
20°	866.3	856.9	860.7	855.1	854.3
22.5°	852.3	842.9	846.7	839.2	839.0
25°	829.6	819.5	824.0	815.3	814.5
27.5°	802.7	793.3	797.1	788.2	787.2
30°	784.2	774.8	778.6	769.0	767.5
32.5°	763.2	754.4	757.6	748.0	747.1
35°	730.8	722.2	724.4	714.8	714.1
37.5°	694.0	686.2	687.4	676.9	676.1
40°	667.8	660.0	660.7	649.5	648.7
42.5°	639.2	631.4	630.7	619.5	618.7
45°	591.3	583.5	581.0	570.6	569.0
47.5°	536.8	529.0	524.2	515.8	514.7
50°	497.3	489.5	485.3	478.1	475.8
52.5°	454.6	446.8	443.3	436.7	434.3
55°	387.3	381.1	378.5	372.1	370.6
57.5°	323.4	319.2	318.5	312.2	311.6
60°	284.5	282.2	282.1	276.5	276.5
62.5°	251.4	249.6	250.9	247.2	246.6
65°	208.0	206.4	208.8	207.2	207.2
67.5°	173.7	173.7	175.2	174.5	174.5
70°	154.6	154.6	155.4	155.4	155.4
72.5°	137.4	136.8	138.8	138.8	138.2
75°	112.4	112.4	112.4	113.2	113.2
77.5°	87.5	87.7	88.3	88.1	87.5
80°	70.9	71.7	71.7	70.9	70.9
82.5°	54.4	55.1	55.1	55.0	54.4
85°	28.7	30.2	31.9	31.9	31.9
87.5°	8.5	11.5	14.6	13.6	13.0
90°	1.1	3.4	9.1	4.6	4.6
92.5°	4.8	23.1	51.1	22.6	14.6
95°	11.4	44.9	149.4	77.0	52.5
97.5°	19.8	49.3	223.5	177.7	130.9
100°	26.2	53.0	246.3	249.6	193.8
102.5°	31.7	56.7	252.7	310.9	263.2
105°	41.0	62.2	252.0	382.5	356.9
107.5°	50.6	70.3	237.6	419.8	426.0
110°	57.0	74.9	225.8	429.3	456.1



TEST NUMBER: P563863

CATALOG NUMBER: SQ4-PR1-025U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	63.4	80.3	214.8	423.3	464.3
115°	73.0	88.6	201.8	402.7	459.5
117.5°	82.3	96.6	192.9	374.1	437.2
120°	87.8	101.2	189.3	354.9	416.2
122.5°	93.3	106.7	186.5	335.7	396.1
125°	101.5	113.7	183.6	310.3	366.0
127.5°	108.1	120.6	181.1	289.8	336.8
130°	111.7	125.1	180.2	276.9	320.4
132.5°	115.4	128.8	179.2	265.9	304.9
135°	120.9	133.1	177.9	250.5	283.9
137.5°	126.6	138.6	177.7	238.9	266.4
140°	131.1	142.3	176.7	229.8	255.4
142.5°	134.8	145.0	176.7	223.3	245.4
145°	140.3	149.2	175.6	213.6	230.3
147.5°	145.7	154.4	175.6	205.6	219.4
150°	149.4	157.2	175.6	200.9	212.1
152.5°	153.0	159.0	175.6	197.2	205.7
155°	158.5	163.0	175.6	192.8	198.4
157.5°	162.6	166.8	175.6	188.9	192.9
160°	165.3	168.7	175.6	187.1	189.3
162.5°	168.1	170.5	175.6	185.2	187.5
165°	171.0	173.3	175.6	182.5	184.7
167.5°	173.8	174.9	176.7	181.3	182.2
170°	175.6	176.7	176.7	181.3	181.3
172.5°	176.5	176.7	176.7	180.4	179.5
175°	177.9	177.9	176.7	179.0	179.0
177.5°	177.9	177.9	177.0	178.8	177.9
180°	177.9	177.9	177.9	177.9	177.9

(END OF REPORT)