

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563911

Luminaire Tested: **SQ4-PR1-025U-100D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563911
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-100D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5683.7 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 63.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563911
CATALOG NUMBER: SQ4-PR1-025U-100D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563911

CATALOG NUMBER: SQ4-PR1-025U-100D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80
1	105	101	97	93	100	96	93	90	88	86	83	81	79	77	74	73	71	68
2	96	88	82	77	92	85	79	74	78	74	70	72	68	65	66	63	61	58
3	88	78	71	65	84	75	68	63	69	64	59	64	59	56	59	55	52	49
4	81	70	61	55	77	67	60	54	62	56	51	57	52	48	53	49	45	43
5	74	62	54	48	71	60	52	47	56	49	44	52	46	42	48	43	40	37
6	69	56	48	42	66	54	47	41	50	44	39	47	41	37	44	39	35	33
7	64	51	43	37	61	49	42	36	46	39	35	43	37	33	40	35	31	29
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	37	32	28	26
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	31	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11145	11145	11145
5°	11245	11159	11101
10°	11210	11132	11074
15°	11161	11091	11032
20°	11105	11033	10951
25°	11026	10952	10825
30°	10907	10830	10675
35°	10747	10653	10500
40°	10502	10388	10200
45°	10073	9897	9693
50°	9319	9095	8915
55°	8134	7949	7782
60°	6854	6797	6663
65°	5928	5951	5906
70°	5445	5472	5472
75°	5231	5231	5266
80°	4920	4977	4920
85°	3966	4404	4404



TEST NUMBER: P563911

CATALOG NUMBER: SQ4-PR1-025U-100D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.4	3.0
10°-20°	490.2	8.6
20°-30°	739.5	13.0
30°-40°	881.1	15.5
40°-50°	868.6	15.3
50°-60°	663.9	11.7
60°-70°	410.8	7.2
70°-80°	233.3	4.1
80°-90°	71.9	1.3
90°-100°	86.7	1.5
100°-110°	227.9	4.0
110°-120°	236.3	4.2
120°-130°	189.6	3.3
130°-140°	148.7	2.6
140°-150°	114.2	2.0
150°-160°	82.2	1.4
160°-170°	50.3	0.9
170°-180°	17.0	0.3
0°-30°	1401.1	24.7
0°-40°	2282.1	40.2
0°-60°	3814.6	67.1
0°-90°	4530.7	79.7
90°-120°	551.0	9.7
90°-150°	1003.4	17.7
90°-180°	1153.0	20.3
0°-180°	5683.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1812	1812	1812	1812	1812	
5°	1821	1802	1807	1801	1798	173
15°	1753	1734	1742	1735	1732	495
25°	1625	1605	1614	1597	1595	748
35°	1431	1414	1419	1400	1398	893
45°	1158	1143	1138	1117	1114	887
55°	758	746	741	729	726	680
65°	407	404	409	406	406	413
75°	220	220	220	222	222	232
85°	56	59	62	62	62	65
90°	1	3	9	5	5	3
95°	11	45	149	77	52	13
105°	41	62	252	382	357	43
115°	73	89	202	403	460	72
125°	102	114	184	310	366	90
135°	121	133	178	250	284	94
145°	140	149	176	214	230	88
155°	158	163	176	193	198	73
165°	171	173	176	182	185	48
175°	178	178	177	179	179	17
180°	178	178	178	178	178	

TEST NUMBER: P563911

CATALOG NUMBER: SQ4-PR1-025U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1812.0	1812.0	1812.0	1812.0	1812.0
2.5°	1823.2	1807.3	1812.0	1808.0	1799.5
5°	1821.3	1801.5	1807.3	1801.0	1797.9
7.5°	1807.3	1787.8	1793.6	1787.3	1785.4
10°	1794.8	1776.5	1782.3	1776.0	1773.0
12.5°	1781.1	1761.5	1768.6	1761.0	1758.0
15°	1752.7	1734.4	1741.7	1735.4	1732.4
17.5°	1721.5	1701.9	1709.3	1702.0	1698.0
20°	1696.5	1678.2	1685.6	1674.6	1673.1
22.5°	1669.0	1650.7	1658.1	1643.4	1643.1
25°	1624.7	1604.9	1613.8	1596.6	1595.0
27.5°	1571.9	1553.6	1561.0	1543.5	1541.7
30°	1535.7	1517.4	1524.8	1506.0	1503.0
32.5°	1494.5	1477.4	1483.6	1464.8	1463.0
35°	1431.2	1414.4	1418.7	1399.9	1398.4
37.5°	1359.1	1343.8	1346.3	1325.6	1324.1
40°	1307.9	1292.6	1293.8	1271.9	1270.4
42.5°	1251.7	1236.4	1235.1	1213.3	1211.7
45°	1158.0	1142.8	1137.8	1117.4	1114.3
47.5°	1051.3	1036.0	1026.6	1010.0	1007.9
50°	973.9	958.6	950.5	936.3	931.7
52.5°	890.2	875.0	868.1	855.2	850.6
55°	758.5	746.3	741.3	728.8	725.7
57.5°	633.3	625.1	623.7	611.5	610.2
60°	557.2	552.6	552.5	541.6	541.6
62.5°	492.2	488.9	491.3	484.1	482.9
65°	407.3	404.3	408.9	405.8	405.8
67.5°	340.2	340.2	343.0	341.8	341.8
70°	302.8	302.8	304.3	304.3	304.3
72.5°	269.1	267.8	271.9	271.8	270.6
75°	220.1	220.1	220.1	221.6	221.6
77.5°	171.4	171.7	172.9	172.6	171.4
80°	138.9	140.4	140.5	138.9	138.9
82.5°	106.4	108.0	108.0	107.7	106.4
85°	56.2	59.2	62.4	62.4	62.4
87.5°	16.5	21.8	26.8	25.9	24.6
90°	1.1	3.4	9.1	4.6	4.6
92.5°	4.8	23.1	51.1	22.6	14.6
95°	11.4	44.9	149.4	77.0	52.5
97.5°	19.8	49.3	223.5	177.7	130.9
100°	26.2	53.0	246.3	249.6	193.8
102.5°	31.7	56.7	252.7	310.9	263.2
105°	41.0	62.2	252.0	382.5	356.9
107.5°	50.6	70.3	237.6	419.8	426.0
110°	57.0	74.9	225.8	429.3	456.1

TEST NUMBER: P563911

CATALOG NUMBER: SQ4-PR1-025U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	63.4	80.3	214.8	423.3	464.3
115°	73.0	88.6	201.8	402.7	459.5
117.5°	82.3	96.6	192.9	374.1	437.2
120°	87.8	101.2	189.3	354.9	416.2
122.5°	93.3	106.7	186.5	335.7	396.1
125°	101.5	113.7	183.6	310.3	366.0
127.5°	108.1	120.6	181.1	289.8	336.8
130°	111.7	125.1	180.2	276.9	320.4
132.5°	115.4	128.8	179.2	265.9	304.9
135°	120.9	133.1	177.9	250.5	283.9
137.5°	126.6	138.6	177.7	238.9	266.4
140°	131.1	142.3	176.7	229.8	255.4
142.5°	134.8	145.0	176.7	223.3	245.4
145°	140.3	149.2	175.6	213.6	230.3
147.5°	145.7	154.4	175.6	205.6	219.4
150°	149.4	157.2	175.6	200.9	212.1
152.5°	153.0	159.0	175.6	197.2	205.7
155°	158.5	163.0	175.6	192.8	198.4
157.5°	162.6	166.8	175.6	188.9	192.9
160°	165.3	168.7	175.6	187.1	189.3
162.5°	168.1	170.5	175.6	185.2	187.5
165°	171.0	173.3	175.6	182.5	184.7
167.5°	173.8	174.9	176.7	181.3	182.2
170°	175.6	176.7	176.7	181.3	181.3
172.5°	176.5	176.7	176.7	180.4	179.5
175°	177.9	177.9	176.7	179.0	179.0
177.5°	177.9	177.9	177.0	178.8	177.9
180°	177.9	177.9	177.9	177.9	177.9

(END OF REPORT)