

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P563959

Luminaire Tested: **SQ4-PR1-050U-050D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563959  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-050U-050D-930-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4692.0 lumens  
Efficiency: N/A  
Efficacy: 104.7 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 44.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563959  
CATALOG NUMBER: SQ4-PR1-050U-050D-930-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563959

CATALOG NUMBER: SQ4-PR1-050U-050D-930-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				
1	98	94	90	86	90	87	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36				
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35	31				
4	75	64	56	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26				
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23				
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	20				
7	59	47	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18				
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16				
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15				
10	47	35	28	23	44	33	27	22	29	24	20	25	20	18	21	18	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5691	5691	5691
5°	5742	5698	5669
10°	5724	5684	5654
15°	5699	5664	5633
20°	5670	5634	5592
25°	5630	5592	5528
30°	5570	5530	5451
35°	5487	5439	5362
40°	5362	5305	5209
45°	5143	5054	4949
50°	4759	4644	4553
55°	4153	4059	3974
60°	3500	3470	3401
65°	3027	3039	3016
70°	2780	2795	2795
75°	2671	2671	2690
80°	2511	2540	2511
85°	2025	2251	2251



TEST NUMBER: P563959

CATALOG NUMBER: SQ4-PR1-050U-050D-930-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.5	1.9
10°-20°	250.3	5.3
20°-30°	377.6	8.0
30°-40°	449.9	9.6
40°-50°	443.6	9.5
50°-60°	339.0	7.2
60°-70°	209.8	4.5
70°-80°	119.2	2.5
80°-90°	37.6	0.8
90°-100°	174.8	3.7
100°-110°	474.9	10.1
110°-120°	488.2	10.4
120°-130°	390.4	8.3
130°-140°	306.7	6.5
140°-150°	235.2	5.0
150°-160°	169.1	3.6
160°-170°	103.4	2.2
170°-180°	34.8	0.7
0°-30°	715.4	15.2
0°-40°	1165.3	24.8
0°-60°	1947.9	41.5
0°-90°	2314.4	49.3
90°-120°	1137.9	24.3
90°-150°	2070.2	44.1
90°-180°	2378.0	50.7
0°-180°	4692.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	925	925	925	925	925	
5°	930	920	923	920	918	88
15°	895	886	889	886	885	253
25°	830	820	824	815	814	382
35°	731	722	724	715	714	456
45°	591	584	581	571	569	453
55°	387	381	378	372	371	347
65°	208	206	209	207	207	211
75°	112	112	112	113	113	119
85°	29	30	32	32	32	33
90°	1	5	8	10	10	3
95°	26	96	304	132	89	27
105°	84	131	522	795	748	90
115°	150	182	418	832	947	148
125°	206	235	378	637	752	184
135°	248	276	368	519	585	192
145°	287	308	363	441	474	180
155°	324	336	361	396	408	150
165°	351	356	362	377	378	99
175°	364	365	363	368	366	35
180°	364	364	364	364	364	



TEST NUMBER: P563959

CATALOG NUMBER: SQ4-PR1-050U-050D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	925.3	925.3	925.3	925.3	925.3
2.5°	931.0	922.9	925.3	923.2	918.9
5°	930.0	919.9	922.9	919.6	918.1
7.5°	922.9	912.9	915.9	912.6	911.7
10°	916.5	907.1	910.1	906.9	905.3
12.5°	909.5	899.5	903.1	899.2	897.7
15°	895.0	885.6	889.4	886.2	884.6
17.5°	879.0	869.1	872.8	869.1	867.1
20°	866.3	856.9	860.7	855.1	854.3
22.5°	852.3	842.9	846.7	839.2	839.0
25°	829.6	819.5	824.0	815.3	814.5
27.5°	802.7	793.3	797.1	788.2	787.2
30°	784.2	774.8	778.6	769.0	767.5
32.5°	763.2	754.4	757.6	748.0	747.1
35°	730.8	722.2	724.4	714.8	714.1
37.5°	694.0	686.2	687.4	676.9	676.1
40°	667.8	660.0	660.7	649.5	648.7
42.5°	639.2	631.4	630.7	619.5	618.7
45°	591.3	583.5	581.0	570.6	569.0
47.5°	536.8	529.0	524.2	515.8	514.7
50°	497.3	489.5	485.3	478.1	475.8
52.5°	454.6	446.8	443.3	436.7	434.3
55°	387.3	381.1	378.5	372.1	370.6
57.5°	323.4	319.2	318.5	312.2	311.6
60°	284.5	282.2	282.1	276.5	276.5
62.5°	251.4	249.6	250.9	247.2	246.6
65°	208.0	206.4	208.8	207.2	207.2
67.5°	173.7	173.7	175.2	174.5	174.5
70°	154.6	154.6	155.4	155.4	155.4
72.5°	137.4	136.8	138.8	138.8	138.2
75°	112.4	112.4	112.4	113.2	113.2
77.5°	87.5	87.7	88.3	88.1	87.5
80°	70.9	71.7	71.7	70.9	70.9
82.5°	54.4	55.1	55.1	55.0	54.4
85°	28.7	30.2	31.9	31.9	31.9
87.5°	8.5	11.7	14.4	14.8	14.2
90°	1.2	4.6	8.2	10.5	10.5
92.5°	10.5	47.9	83.1	35.7	30.2
95°	25.8	95.6	304.4	132.5	89.0
97.5°	42.6	105.6	466.7	363.1	255.0
100°	53.9	112.2	516.4	523.4	422.7
102.5°	65.1	118.9	529.5	647.4	558.5
105°	84.3	131.2	522.2	795.1	748.2
107.5°	104.2	145.7	492.0	871.4	884.5
110°	118.3	156.0	469.5	886.5	942.6



TEST NUMBER: P563959

CATALOG NUMBER: SQ4-PR1-050U-050D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	130.4	166.4	447.0	874.0	958.5
115°	149.9	181.9	418.0	831.6	947.2
117.5°	168.1	198.8	399.5	771.5	901.8
120°	180.3	210.1	391.1	731.2	860.6
122.5°	190.6	220.4	385.5	690.9	815.6
125°	206.1	234.7	378.2	637.2	751.7
127.5°	219.9	248.3	374.2	596.6	694.8
130°	228.3	255.8	372.3	571.1	659.2
132.5°	236.8	264.2	370.5	549.3	627.4
135°	248.2	275.7	367.7	519.0	585.4
137.5°	260.6	285.6	366.3	492.3	548.2
140°	268.1	292.2	365.3	475.4	525.7
142.5°	275.6	297.8	364.4	462.1	504.2
145°	286.9	307.5	363.0	441.0	474.2
147.5°	299.5	317.1	361.8	424.5	450.6
150°	307.9	322.8	361.8	415.0	435.6
152.5°	314.5	327.6	360.9	406.4	423.4
155°	324.3	335.8	360.6	396.0	407.5
157.5°	333.9	342.9	360.6	388.9	397.6
160°	339.6	347.6	360.6	384.2	391.1
162.5°	345.2	351.4	361.6	380.4	385.5
165°	351.3	355.8	361.8	377.1	378.2
167.5°	357.6	359.9	363.0	373.1	374.0
170°	359.5	361.8	363.0	371.2	371.2
172.5°	361.3	362.7	363.0	369.3	369.3
175°	364.1	365.3	363.0	367.6	366.5
177.5°	365.1	365.1	362.3	366.0	364.1
180°	364.1	364.1	364.1	364.1	364.1

(END OF REPORT)