

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562950

Luminaire Tested: **SQ4-PC3-100U-100D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562950  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-100U-100D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6263.8 lumens  
Efficiency: N/A  
Efficacy: 108.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 57.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562950  
CATALOG NUMBER: SQ4-PC3-100U-100D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P562950

CATALOG NUMBER: SQ4-PC3-100U-100D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41
2	89	81	75	70	82	75	70	66	64	60	56	53	50	48	43	41	39	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29
4	74	63	55	49	68	59	52	46	50	45	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	38	32	27	33	28	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10367	10367	10367
5°	10446	10378	10339
10°	10421	10372	10342
15°	10365	10365	10356
20°	10297	10328	10328
25°	10200	10275	10242
30°	10076	10198	10154
35°	9926	10078	10008
40°	9762	9900	9799
45°	9585	9653	9503
50°	9334	9334	9185
55°	9038	8921	8786
60°	8601	8429	8294
65°	7951	7792	7724
70°	6960	7016	6989
75°	5600	6196	6231
80°	3980	5249	5308
85°	2424	4404	4404



TEST NUMBER: P562950

CATALOG NUMBER: SQ4-PC3-100U-100D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.3	1.7
10°-20°	305.2	4.9
20°-30°	462.2	7.4
30°-40°	554.1	8.8
40°-50°	565.0	9.0
50°-60°	493.2	7.9
60°-70°	353.1	5.6
70°-80°	181.9	2.9
80°-90°	47.0	0.8
90°-100°	230.4	3.7
100°-110°	635.9	10.2
110°-120°	655.9	10.5
120°-130°	527.0	8.4
130°-140°	414.2	6.6
140°-150°	317.7	5.1
150°-160°	228.3	3.6
160°-170°	139.6	2.2
170°-180°	47.1	0.8
0°-30°	873.7	13.9
0°-40°	1427.8	22.8
0°-60°	2485.9	39.7
0°-90°	3067.8	49.0
90°-120°	1522.1	24.3
90°-150°	2781.0	44.4
90°-180°	3196.0	51.0
0°-180°	6263.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1124	1124	1124	1124	1124	
5°	1128	1117	1121	1117	1116	107
15°	1085	1076	1085	1085	1084	306
25°	1002	995	1009	1006	1006	461
35°	881	879	895	889	889	551
45°	735	732	740	730	728	565
55°	562	555	555	546	546	501
65°	364	356	357	354	354	360
75°	157	164	174	175	175	170
85°	23	35	42	43	42	31
90°	2	3	6	7	8	3
95°	34	125	418	172	112	36
105°	113	175	700	1068	1006	121
115°	203	245	564	1116	1269	200
125°	279	317	511	864	1014	248
135°	335	371	497	700	789	259
145°	389	416	490	596	641	243
155°	438	453	486	535	552	202
165°	475	481	489	508	512	134
175°	492	493	490	497	495	47
180°	492	492	492	492	492	

TEST NUMBER: P562950

CATALOG NUMBER: SQ4-PC3-100U-100D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1123.7	1123.7	1123.7	1123.7	1123.7
2.5°	1130.4	1120.6	1123.7	1121.1	1117.0
5°	1127.9	1116.7	1120.6	1117.4	1116.4
7.5°	1119.8	1108.6	1113.7	1111.6	1110.6
10°	1112.3	1101.1	1107.1	1105.0	1103.9
12.5°	1102.3	1091.9	1098.7	1096.7	1096.4
15°	1085.2	1076.1	1085.2	1085.2	1084.2
17.5°	1063.8	1055.4	1065.2	1065.8	1065.2
20°	1048.8	1039.6	1051.9	1050.9	1051.9
22.5°	1030.5	1023.0	1036.1	1033.4	1034.4
25°	1002.0	994.9	1009.3	1006.1	1006.1
27.5°	968.3	963.2	978.9	975.5	975.5
30°	945.8	940.7	957.2	953.1	953.1
32.5°	920.8	917.4	933.1	928.1	928.1
35°	881.3	879.2	894.8	888.6	888.6
37.5°	840.5	838.7	852.8	845.2	842.8
40°	810.5	809.5	822.0	813.6	813.6
42.5°	780.6	779.5	790.3	780.4	780.4
45°	734.6	732.5	739.8	730.4	728.3
47.5°	684.4	682.4	686.9	676.7	675.7
50°	650.3	648.3	650.3	640.9	639.9
52.5°	615.3	611.7	612.0	602.6	602.4
55°	561.9	554.7	554.6	546.2	546.2
57.5°	505.3	495.9	496.7	489.6	488.6
60°	466.1	456.0	456.8	450.5	449.5
62.5°	427.8	416.0	418.5	411.4	411.2
65°	364.2	356.0	356.9	353.8	353.8
67.5°	303.0	295.5	300.9	298.4	298.2
70°	258.0	252.9	260.1	260.1	259.1
72.5°	216.4	216.2	225.2	225.2	225.8
75°	157.1	164.2	173.8	174.8	174.8
77.5°	104.9	117.5	128.0	128.4	128.2
80°	74.9	89.2	98.8	100.9	99.9
82.5°	50.8	65.8	73.9	75.9	74.9
85°	22.9	35.1	41.6	42.6	41.6
87.5°	7.0	14.6	17.9	18.0	16.6
90°	1.6	3.1	6.3	7.1	7.9
92.5°	14.2	58.8	105.1	38.4	29.9
95°	33.8	124.6	417.9	171.8	111.8
97.5°	56.0	139.6	619.1	476.6	345.2
100°	72.4	148.6	693.4	698.3	567.4
102.5°	88.1	158.8	707.8	862.7	738.7
105°	113.3	174.9	699.7	1068.1	1005.8
107.5°	140.1	194.9	660.6	1167.2	1190.0
110°	159.0	208.2	630.4	1188.5	1262.4



TEST NUMBER: P562950

CATALOG NUMBER: SQ4-PC3-100U-100D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	176.0	223.4	602.1	1171.7	1280.6
115°	203.0	245.4	563.5	1115.5	1268.7
117.5°	226.7	268.8	538.2	1036.5	1210.7
120°	242.4	284.0	528.1	983.0	1158.5
122.5°	257.5	297.2	519.9	933.1	1099.3
125°	278.6	317.1	510.8	864.4	1014.5
127.5°	296.5	335.0	505.4	806.3	935.8
130°	308.5	347.0	502.9	770.8	888.5
132.5°	319.8	356.5	500.4	741.0	847.6
135°	335.3	371.4	496.6	700.1	789.4
137.5°	352.6	385.5	494.7	665.8	742.0
140°	362.0	394.3	493.5	642.9	709.9
142.5°	372.7	402.6	492.2	622.6	681.6
145°	388.8	415.7	490.3	596.0	641.4
147.5°	404.2	427.8	488.6	573.6	608.8
150°	415.5	434.8	487.9	560.2	588.7
152.5°	424.4	442.4	487.3	548.8	572.3
155°	438.4	453.0	486.4	534.8	551.7
157.5°	451.3	462.5	486.5	524.6	536.1
160°	458.8	468.8	487.2	518.8	527.3
162.5°	465.1	473.9	487.8	513.8	520.4
165°	474.6	480.7	488.7	507.7	511.6
167.5°	481.8	485.5	489.5	504.0	505.3
170°	485.6	488.7	489.5	502.1	502.1
172.5°	488.7	490.6	489.5	499.6	499.0
175°	491.9	492.7	489.5	496.6	495.0
177.5°	493.1	492.5	489.4	493.7	492.5
180°	491.9	491.9	491.9	491.9	491.9

(END OF REPORT)