

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564271

Luminaire Tested: **SQ4-PR1-100U-075D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564271  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-100U-075D-930-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8204.7 lumens  
Efficiency: N/A  
Efficacy: 105.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 78  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564271  
CATALOG NUMBER: SQ4-PR1-100U-075D-930-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P564271

CATALOG NUMBER: SQ4-PR1-100U-075D-930-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26	22
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	19
6	62	50	42	37	56	46	39	34	39	33	29	32	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	20	21	18	16	14
9	49	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12
10	46	34	27	23	42	32	25	21	27	22	19	22	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8388	8388	8388
5°	8464	8398	8354
10°	8437	8378	8334
15°	8400	8348	8302
20°	8357	8304	8242
25°	8299	8242	8147
30°	8209	8151	8033
35°	8088	8017	7902
40°	7903	7818	7677
45°	7582	7449	7295
50°	7014	6845	6710
55°	6122	5983	5857
60°	5158	5115	5014
65°	4462	4478	4445
70°	4098	4118	4118
75°	3935	3935	3964
80°	3702	3744	3702
85°	2985	3317	3317



TEST NUMBER: P564271

CATALOG NUMBER: SQ4-PR1-100U-075D-930-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.0	1.6
10°-20°	369.0	4.5
20°-30°	556.5	6.8
30°-40°	663.1	8.1
40°-50°	653.8	8.0
50°-60°	499.6	6.1
60°-70°	309.2	3.8
70°-80°	175.6	2.1
80°-90°	55.0	0.7
90°-100°	345.5	4.2
100°-110°	953.9	11.6
110°-120°	983.8	12.0
120°-130°	790.5	9.6
130°-140°	621.3	7.6
140°-150°	476.5	5.8
150°-160°	342.5	4.2
160°-170°	209.4	2.6
170°-180°	70.6	0.9
0°-30°	1054.4	12.9
0°-40°	1717.5	20.9
0°-60°	2870.9	35.0
0°-90°	3410.7	41.6
90°-120°	2283.2	27.8
90°-150°	4171.5	50.8
90°-180°	4794.0	58.4
0°-180°	8204.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1364	1364	1364	1364	1364	
5°	1371	1356	1360	1355	1353	130
15°	1319	1305	1311	1306	1304	372
25°	1223	1208	1214	1202	1200	563
35°	1077	1064	1068	1054	1052	672
45°	872	860	856	841	839	668
55°	571	562	558	548	546	512
65°	307	304	308	305	305	311
75°	166	166	166	167	167	175
85°	42	45	47	47	47	49
90°	2	5	9	11	12	5
95°	51	187	627	258	168	54
105°	170	262	1050	1602	1509	181
115°	305	368	845	1673	1903	299
125°	418	476	766	1297	1522	372
135°	503	557	745	1050	1184	389
145°	583	624	736	894	962	365
155°	658	680	730	802	828	303
165°	712	721	733	762	767	201
175°	738	739	734	745	742	70
180°	738	738	738	738	738	



TEST NUMBER: P564271

CATALOG NUMBER: SQ4-PR1-100U-075D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1363.7	1363.7	1363.7	1363.7	1363.7
2.5°	1372.2	1360.2	1363.7	1360.8	1354.3
5°	1370.8	1355.8	1360.2	1355.4	1353.1
7.5°	1360.2	1345.5	1349.9	1345.1	1343.7
10°	1350.8	1337.0	1341.4	1336.6	1334.4
12.5°	1340.5	1325.8	1331.1	1325.4	1323.1
15°	1319.1	1305.3	1310.9	1306.1	1303.8
17.5°	1295.6	1280.9	1286.4	1281.0	1278.0
20°	1276.8	1263.0	1268.6	1260.3	1259.2
22.5°	1256.1	1242.3	1247.9	1236.9	1236.6
25°	1222.8	1207.8	1214.5	1201.6	1200.4
27.5°	1183.1	1169.3	1174.8	1161.7	1160.3
30°	1155.8	1142.0	1147.6	1133.4	1131.1
32.5°	1124.8	1111.9	1116.6	1102.5	1101.1
35°	1077.1	1064.5	1067.7	1053.6	1052.4
37.5°	1022.8	1011.4	1013.2	997.7	996.5
40°	984.3	972.8	973.7	957.3	956.1
42.5°	942.0	930.5	929.6	913.1	912.0
45°	871.6	860.1	856.3	841.0	838.7
47.5°	791.2	779.7	772.7	760.2	758.6
50°	733.0	721.5	715.3	704.7	701.2
52.5°	670.0	658.5	653.3	643.6	640.2
55°	570.9	561.7	557.9	548.5	546.2
57.5°	476.7	470.5	469.4	460.2	459.3
60°	419.3	415.9	415.8	407.6	407.6
62.5°	370.5	367.9	369.8	364.3	363.4
65°	306.6	304.3	307.7	305.4	305.4
67.5°	256.1	256.1	258.2	257.2	257.2
70°	227.9	227.9	229.0	229.0	229.0
72.5°	202.5	201.6	204.6	204.6	203.7
75°	165.6	165.6	165.6	166.8	166.8
77.5°	129.0	129.2	130.1	129.9	129.0
80°	104.5	105.7	105.7	104.5	104.5
82.5°	80.1	81.3	81.3	81.0	80.1
85°	42.3	44.6	47.0	47.0	47.0
87.5°	12.7	16.8	20.7	20.9	20.2
90°	2.4	4.7	9.4	10.7	11.8
92.5°	21.2	88.2	157.7	57.6	44.9
95°	50.8	187.0	626.9	257.7	167.6
97.5°	84.1	209.4	928.6	714.9	517.8
100°	108.6	222.9	1040.0	1047.4	851.2
102.5°	132.2	238.2	1061.8	1294.1	1108.0
105°	170.0	262.3	1049.5	1602.2	1508.7
107.5°	210.1	292.3	990.9	1750.8	1784.9
110°	238.5	312.3	945.6	1782.7	1893.6



TEST NUMBER: P564271

CATALOG NUMBER: SQ4-PR1-100U-075D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	264.0	335.1	903.1	1757.5	1920.9
115°	304.6	368.1	845.3	1673.3	1903.0
117.5°	340.0	403.2	807.2	1554.8	1816.1
120°	363.6	425.9	792.1	1474.6	1737.7
122.5°	386.3	445.8	779.9	1399.6	1649.0
125°	417.9	475.6	766.2	1296.6	1521.7
127.5°	444.8	502.5	758.1	1209.5	1403.6
130°	462.8	520.5	754.4	1156.2	1332.8
132.5°	479.8	534.7	750.6	1111.4	1271.4
135°	502.9	557.2	744.9	1050.2	1184.1
137.5°	528.9	578.3	742.1	998.7	1113.0
140°	543.0	591.5	740.2	964.4	1064.8
142.5°	559.1	603.9	738.3	933.9	1022.3
145°	583.2	623.6	735.5	894.0	962.1
147.5°	606.3	641.6	732.9	860.4	913.3
150°	623.3	652.2	731.9	840.3	883.0
152.5°	636.5	663.5	731.0	823.2	858.5
155°	657.6	679.5	729.6	802.2	827.5
157.5°	676.9	693.8	729.8	786.9	804.2
160°	688.2	703.2	730.7	778.3	790.9
162.5°	697.7	710.8	731.7	770.6	780.6
165°	711.9	721.1	733.1	761.6	767.3
167.5°	722.7	728.3	734.3	756.0	757.9
170°	728.4	733.0	734.3	753.2	753.2
172.5°	733.1	735.9	734.3	749.4	748.5
175°	737.8	739.0	734.3	744.9	742.5
177.5°	739.7	738.8	734.0	740.6	738.8
180°	737.8	737.8	737.8	737.8	737.8

(END OF REPORT)