

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563022

Luminaire Tested: **SQ4-PC3-125U-075D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563022
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-075D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6287.8 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563022
CATALOG NUMBER: SQ4-PC3-125U-075D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563022

CATALOG NUMBER: SQ4-PC3-125U-075D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37				31	
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	33	31				26	
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	27				22	
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23				19	
5	66	55	47	41	59	50	43	38	41	36	32	32	29	26	24	22	20				16	
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17				14	
7	56	44	36	31	51	40	33	28	33	28	24	26	23	20	20	17	15				13	
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14				11	
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12				10	
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11				9	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7803	7803	7803
5°	7862	7811	7781
10°	7842	7806	7783
15°	7801	7801	7794
20°	7750	7773	7773
25°	7677	7733	7708
30°	7583	7675	7642
35°	7471	7585	7532
40°	7347	7450	7376
45°	7213	7265	7153
50°	7025	7025	6913
55°	6803	6714	6613
60°	6473	6344	6242
65°	5984	5864	5811
70°	5239	5282	5260
75°	4214	4663	4691
80°	2997	3953	3995
85°	1821	3313	3313



TEST NUMBER: P563022

CATALOG NUMBER: SQ4-PC3-125U-075D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.0	1.3
10°-20°	229.7	3.7
20°-30°	347.8	5.5
30°-40°	417.0	6.6
40°-50°	425.2	6.8
50°-60°	371.2	5.9
60°-70°	265.7	4.2
70°-80°	136.9	2.2
80°-90°	36.0	0.6
90°-100°	288.3	4.6
100°-110°	776.6	12.4
110°-120°	815.0	13.0
120°-130°	661.3	10.5
130°-140°	518.7	8.2
140°-150°	398.2	6.3
150°-160°	286.3	4.6
160°-170°	174.9	2.8
170°-180°	59.0	0.9
0°-30°	657.6	10.5
0°-40°	1074.5	17.1
0°-60°	1870.9	29.8
0°-90°	2309.6	36.7
90°-120°	1879.8	29.9
90°-150°	3458.0	55.0
90°-180°	3978.0	63.3
0°-180°	6287.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	846	846	846	846	846	
5°	849	840	843	841	840	81
15°	817	810	817	817	816	230
25°	754	749	760	757	757	347
35°	663	662	673	669	669	415
45°	553	551	557	550	548	426
55°	423	418	417	411	411	377
65°	274	268	269	266	266	271
75°	118	124	131	132	132	128
85°	17	26	31	32	31	23
90°	2	5	9	10	10	4
95°	44	157	473	242	167	46
105°	144	224	859	1285	1206	151
115°	254	310	715	1382	1563	250
125°	346	398	642	1085	1277	309
135°	417	465	624	876	992	322
145°	482	520	616	749	804	302
155°	547	567	611	672	693	252
165°	594	600	613	638	641	167
175°	617	616	614	622	621	59
180°	616	616	616	616	616	



TEST NUMBER: P563022

CATALOG NUMBER: SQ4-PC3-125U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	845.7	845.7	845.7	845.7	845.7
2.5°	850.7	843.4	845.7	843.8	840.7
5°	848.9	840.4	843.4	841.0	840.2
7.5°	842.7	834.3	838.2	836.6	835.9
10°	837.1	828.7	833.2	831.6	830.8
12.5°	829.6	821.8	826.9	825.4	825.2
15°	816.7	809.9	816.7	816.7	816.0
17.5°	800.6	794.3	801.7	802.2	801.7
20°	789.3	782.4	791.7	790.9	791.7
22.5°	775.6	769.9	779.8	777.8	778.5
25°	754.1	748.7	759.6	757.2	757.2
27.5°	728.7	724.9	736.7	734.2	734.2
30°	711.8	708.0	720.4	717.3	717.3
32.5°	693.0	690.4	702.3	698.5	698.5
35°	663.3	661.7	673.4	668.7	668.7
37.5°	632.6	631.2	641.8	636.1	634.3
40°	610.0	609.2	618.6	612.4	612.4
42.5°	587.5	586.7	594.8	587.3	587.3
45°	552.8	551.3	556.8	549.7	548.2
47.5°	515.1	513.6	517.0	509.3	508.5
50°	489.4	487.9	489.4	482.4	481.6
52.5°	463.1	460.4	460.6	453.6	453.4
55°	422.9	417.5	417.4	411.1	411.1
57.5°	380.3	373.2	373.8	368.5	367.7
60°	350.8	343.2	343.8	339.1	338.3
62.5°	322.0	313.1	315.0	309.6	309.5
65°	274.1	267.9	268.6	266.2	266.2
67.5°	228.0	222.4	226.5	224.6	224.4
70°	194.2	190.4	195.8	195.8	195.0
72.5°	162.9	162.7	169.5	169.5	169.9
75°	118.2	123.6	130.8	131.6	131.6
77.5°	78.9	88.4	96.3	96.6	96.5
80°	56.4	67.1	74.4	75.9	75.2
82.5°	38.2	49.5	55.6	57.1	56.4
85°	17.2	26.4	31.3	32.1	31.3
87.5°	5.3	11.5	14.4	14.5	13.3
90°	1.6	4.6	9.4	10.2	10.2
92.5°	19.2	67.7	133.8	64.4	44.7
95°	44.0	156.8	472.6	241.7	167.2
97.5°	70.2	179.5	741.2	619.2	466.9
100°	90.3	188.5	826.6	864.9	717.5
102.5°	109.7	201.2	854.9	1048.9	927.9
105°	143.7	223.5	858.8	1284.9	1205.8
107.5°	175.7	246.9	822.2	1406.1	1426.6
110°	197.0	264.6	789.0	1443.8	1518.2



TEST NUMBER: P563022

CATALOG NUMBER: SQ4-PC3-125U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	219.7	282.3	756.9	1435.5	1557.8
115°	253.6	310.4	715.2	1381.8	1563.0
117.5°	284.5	337.8	682.8	1296.3	1498.0
120°	304.6	356.0	666.5	1234.8	1442.1
122.5°	322.2	373.0	654.6	1172.0	1378.7
125°	346.2	397.6	642.2	1085.3	1277.2
127.5°	369.3	419.9	634.3	1008.9	1180.2
130°	383.1	433.8	631.2	965.1	1115.5
132.5°	396.9	447.0	628.0	926.5	1064.7
135°	416.9	465.2	624.1	875.6	991.5
137.5°	435.8	482.2	622.1	832.4	927.6
140°	449.0	493.6	620.2	805.8	891.8
142.5°	462.9	504.3	618.9	781.0	853.5
145°	482.0	519.6	616.2	748.6	803.9
147.5°	502.7	535.4	613.6	721.3	764.8
150°	516.5	544.9	612.3	704.2	740.3
152.5°	529.1	553.8	611.7	690.2	719.6
155°	547.2	567.1	610.8	671.7	693.2
157.5°	563.0	578.5	610.9	658.7	673.1
160°	573.1	586.1	611.5	651.0	661.8
162.5°	581.9	592.5	612.2	644.7	652.4
165°	593.5	600.4	613.1	637.5	640.6
167.5°	602.9	606.9	613.9	632.0	633.2
170°	609.2	610.7	613.9	628.8	628.8
172.5°	613.0	613.3	614.5	625.7	625.7
175°	617.0	616.3	613.9	622.5	621.0
177.5°	618.8	617.5	614.4	619.4	618.1
180°	616.2	616.2	616.2	616.2	616.2

(END OF REPORT)