

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563286

Luminaire Tested: **SQ4-PP3-050U-050D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563286
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3137.2 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 28.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563286
CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563286

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	36
3	82	72	65	59	75	67	61	55	57	52	48	48	44	41	39	36	34	30
4	75	64	56	50	69	59	52	47	51	45	41	42	38	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5592	5592	5592
5°	5633	5599	5578
10°	5623	5584	5558
15°	5586	5555	5525
20°	5549	5518	5476
25°	5483	5445	5391
30°	5381	5353	5285
35°	5241	5205	5139
40°	5073	5042	4984
45°	4935	4899	4851
50°	4758	4727	4681
55°	4512	4451	4417
60°	4108	3989	3969
65°	3617	3467	3456
70°	3124	2994	2994
75°	2688	2652	2613
80°	2370	2396	2343
85°	1853	2022	2022



TEST NUMBER: P563286

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.3	1.8
10°-20°	163.6	5.2
20°-30°	245.1	7.8
30°-40°	287.5	9.2
40°-50°	288.4	9.2
50°-60°	246.0	7.8
60°-70°	160.4	5.1
70°-80°	80.5	2.6
80°-90°	23.2	0.7
90°-100°	116.5	3.7
100°-110°	316.6	10.1
110°-120°	325.5	10.4
120°-130°	260.2	8.3
130°-140°	204.5	6.5
140°-150°	156.8	5.0
150°-160°	112.8	3.6
160°-170°	69.0	2.2
170°-180°	23.2	0.7
0°-30°	466.1	14.9
0°-40°	753.5	24.0
0°-60°	1288.0	41.1
0°-90°	1552.1	49.5
90°-120°	758.6	24.2
90°-150°	1380.1	44.0
90°-180°	1585.0	50.5
0°-180°	3137.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	606	606	606	606	606	
5°	608	602	604	602	602	58
15°	585	579	582	580	578	165
25°	539	532	535	530	530	248
35°	465	461	462	457	456	291
45°	378	376	376	372	372	291
55°	280	279	277	275	275	249
65°	166	163	159	158	158	165
75°	75	75	74	74	73	82
85°	18	19	19	19	19	21
90°	1	3	6	7	7	2
95°	17	64	203	88	59	18
105°	56	88	348	530	499	60
115°	100	121	279	554	632	99
125°	137	156	252	425	501	122
135°	166	184	245	346	390	128
145°	191	205	242	294	316	120
155°	216	224	240	264	272	100
165°	234	237	241	251	252	66
175°	243	244	242	245	244	23
180°	243	243	243	243	243	



TEST NUMBER: P563286

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	606.1	606.1	606.1	606.1	606.1
2.5°	609.9	604.9	606.1	605.2	602.7
5°	608.2	602.5	604.5	602.3	602.3
7.5°	604.0	597.8	599.8	597.7	597.6
10°	600.2	594.0	596.0	593.8	593.3
12.5°	594.7	588.5	590.9	588.3	588.2
15°	584.8	579.1	581.6	579.5	578.4
17.5°	573.7	567.4	570.5	567.5	567.1
20°	565.2	558.9	562.0	557.7	557.7
22.5°	555.0	548.7	552.2	546.7	546.7
25°	538.6	532.4	534.9	530.1	529.6
27.5°	519.2	513.0	515.7	510.2	510.1
30°	505.1	499.4	502.5	496.6	496.1
32.5°	489.8	484.5	486.8	480.9	480.4
35°	465.3	460.6	462.1	456.8	456.3
37.5°	439.5	434.7	436.4	431.8	431.6
40°	421.2	418.1	418.6	414.8	413.8
42.5°	404.2	400.7	401.1	397.4	397.2
45°	378.2	375.6	375.5	371.8	371.8
47.5°	350.6	348.6	348.0	344.9	344.8
50°	331.5	329.9	329.3	326.7	326.1
52.5°	311.5	310.8	308.9	306.7	306.6
55°	280.5	279.4	276.7	275.1	274.6
57.5°	246.8	244.7	241.7	239.4	239.8
60°	222.6	220.5	216.2	215.1	215.1
62.5°	199.2	196.7	192.4	190.9	191.8
65°	165.7	162.6	158.8	157.8	158.3
67.5°	135.3	132.5	128.4	128.4	128.0
70°	115.8	114.2	111.0	111.0	111.0
72.5°	98.4	97.6	95.3	95.3	94.9
75°	75.4	75.4	74.4	73.8	73.3
77.5°	56.5	56.7	56.2	55.6	54.7
80°	44.6	45.7	45.1	44.6	44.1
82.5°	33.6	34.6	34.5	33.6	33.5
85°	17.5	19.1	19.1	19.1	19.1
87.5°	4.8	7.0	7.9	8.2	8.6
90°	0.8	3.1	5.5	7.0	7.0
92.5°	7.0	31.9	55.4	23.8	20.1
95°	17.2	63.7	203.0	88.3	59.3
97.5°	28.4	70.4	311.1	242.1	170.0
100°	35.9	74.8	344.2	349.0	281.8
102.5°	43.4	79.3	353.0	431.6	372.3
105°	56.2	87.5	348.1	530.1	498.8
107.5°	69.5	97.1	328.0	581.0	589.7
110°	78.8	104.0	313.0	591.0	628.4



TEST NUMBER: P563286

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	87.0	110.9	298.0	582.7	639.0
115°	99.9	121.3	278.7	554.4	631.5
117.5°	112.1	132.5	266.3	514.4	601.2
120°	120.2	140.1	260.7	487.5	573.7
122.5°	127.1	146.9	257.0	460.6	543.8
125°	137.4	156.5	252.1	424.8	501.1
127.5°	146.6	165.5	249.5	397.7	463.2
130°	152.2	170.5	248.2	380.7	439.5
132.5°	157.8	176.2	247.0	366.2	418.2
135°	165.5	183.8	245.1	346.0	390.3
137.5°	173.8	190.4	244.2	328.2	365.5
140°	178.8	194.8	243.5	316.9	350.5
142.5°	183.8	198.6	242.9	308.0	336.1
145°	191.2	205.0	242.0	294.0	316.1
147.5°	199.7	211.4	241.2	283.0	300.4
150°	205.3	215.2	241.2	276.6	290.4
152.5°	209.7	218.4	240.6	271.0	282.3
155°	216.2	223.9	240.4	264.0	271.6
157.5°	222.6	228.6	240.4	259.3	265.1
160°	226.4	231.7	240.4	256.1	260.7
162.5°	230.1	234.2	241.0	253.6	257.0
165°	234.2	237.2	241.2	251.4	252.1
167.5°	238.4	239.9	242.0	248.7	249.3
170°	239.6	241.2	242.0	247.4	247.4
172.5°	240.9	241.8	242.0	246.2	246.2
175°	242.8	243.5	242.0	245.1	244.3
177.5°	243.4	243.4	241.5	244.0	242.8
180°	242.8	242.8	242.8	242.8	242.8

(END OF REPORT)