

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564967

Luminaire Tested: **SQ4-PW1-100U-100D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564967
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-100D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9302.5 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 92.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564967
CATALOG NUMBER: SQ4-PW1-100U-100D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564967

CATALOG NUMBER: SQ4-PW1-100U-100D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	39	35
3	81	72	64	59	74	66	60	55	56	51	47	47	43	40	38	36	33	29
4	74	63	56	50	68	59	52	47	50	45	40	42	38	35	34	31	29	25
5	68	57	48	43	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	35	30	36	31	27	31	26	23	25	22	20	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16	14
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10896	10896	10896
5°	10966	10879	10831
10°	10878	10791	10732
15°	10763	10644	10604
20°	10635	10471	10451
25°	10486	10295	10263
30°	10264	10109	10043
35°	9973	9832	9773
40°	9662	9512	9474
45°	9286	9164	9123
50°	8901	8826	8766
55°	8486	8486	8352
60°	7968	8122	7834
65°	7292	7655	7110
70°	6427	7044	6258
75°	5490	6305	5340
80°	4258	5306	4311
85°	2752	4072	3634



TEST NUMBER: P564967

CATALOG NUMBER: SQ4-PW1-100U-100D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.8	1.8
10°-20°	470.9	5.1
20°-30°	698.6	7.5
30°-40°	817.4	8.8
40°-50°	813.7	8.7
50°-60°	702.7	7.6
60°-70°	505.8	5.4
70°-80°	265.2	2.9
80°-90°	67.3	0.7
90°-100°	345.5	3.7
100°-110°	953.9	10.3
110°-120°	983.8	10.6
120°-130°	790.5	8.5
130°-140°	621.3	6.7
140°-150°	476.5	5.1
150°-160°	342.5	3.7
160°-170°	209.4	2.3
170°-180°	70.6	0.8
0°-30°	1336.3	14.4
0°-40°	2153.7	23.2
0°-60°	3670.1	39.5
0°-90°	4508.4	48.5
90°-120°	2283.2	24.5
90°-150°	4171.5	44.8
90°-180°	4794.0	51.5
0°-180°	9302.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1771	1771	1771	1771	1771	
5°	1776	1756	1762	1757	1754	168
15°	1690	1669	1672	1668	1665	476
25°	1545	1519	1517	1508	1512	710
35°	1328	1310	1309	1297	1302	830
45°	1068	1058	1054	1050	1049	824
55°	791	790	791	780	779	706
65°	501	516	526	505	488	496
75°	231	252	265	248	225	248
85°	39	51	58	55	52	52
90°	2	5	9	11	12	5
95°	51	187	627	258	168	54
105°	170	262	1050	1602	1509	181
115°	305	368	845	1673	1903	299
125°	418	476	766	1297	1522	372
135°	503	557	745	1050	1184	389
145°	583	624	736	894	962	365
155°	658	680	730	802	828	303
165°	712	721	733	762	767	201
175°	738	739	734	745	742	70
180°	738	738	738	738	738	



TEST NUMBER: P564967

CATALOG NUMBER: SQ4-PW1-100U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1771.4	1771.4	1771.4	1771.4	1771.4
2.5°	1781.4	1766.7	1771.4	1767.5	1758.9
5°	1776.1	1756.2	1762.0	1757.3	1754.2
7.5°	1758.0	1739.7	1743.9	1738.9	1737.1
10°	1741.7	1723.4	1727.7	1721.4	1718.3
12.5°	1723.0	1703.5	1707.7	1701.4	1699.6
15°	1690.2	1668.9	1671.5	1668.3	1665.3
17.5°	1652.2	1630.5	1630.9	1625.9	1625.3
20°	1624.7	1601.8	1599.7	1593.6	1596.6
22.5°	1594.7	1570.6	1568.5	1559.9	1564.1
25°	1545.1	1519.2	1517.0	1507.7	1512.3
27.5°	1487.7	1462.0	1462.1	1449.1	1454.0
30°	1445.2	1420.8	1423.4	1407.9	1414.0
32.5°	1400.3	1378.3	1379.7	1364.2	1370.3
35°	1328.2	1309.8	1309.4	1297.1	1301.6
37.5°	1254.5	1238.3	1235.8	1228.6	1229.8
40°	1203.3	1189.6	1184.6	1179.9	1179.9
42.5°	1149.6	1137.1	1132.1	1128.7	1127.5
45°	1067.5	1058.4	1053.5	1050.3	1048.8
47.5°	986.4	977.8	973.6	971.3	969.8
50°	930.2	924.1	922.4	917.7	916.1
52.5°	874.0	870.3	868.7	862.7	861.2
55°	791.3	789.8	791.3	780.3	778.8
57.5°	705.1	707.6	712.6	697.9	694.2
60°	647.7	653.8	660.2	642.9	636.8
62.5°	589.0	598.8	607.7	587.9	579.3
65°	501.0	516.2	526.0	505.3	488.5
67.5°	416.1	435.0	446.7	424.4	405.5
70°	357.4	378.8	391.7	369.4	348.0
72.5°	306.2	330.0	340.5	319.5	298.1
75°	231.0	252.3	265.3	247.6	224.7
77.5°	163.9	184.0	194.8	179.4	160.4
80°	120.2	141.5	149.8	137.0	121.7
82.5°	85.2	102.9	108.6	100.9	90.5
85°	39.0	51.2	57.7	54.6	51.5
87.5°	10.5	19.5	25.6	25.9	27.3
90°	2.4	4.7	9.4	10.7	11.8
92.5°	21.2	88.2	157.7	57.6	44.9
95°	50.8	187.0	626.9	257.7	167.6
97.5°	84.1	209.4	928.6	714.9	517.8
100°	108.6	222.9	1040.0	1047.4	851.2
102.5°	132.2	238.2	1061.8	1294.1	1108.0
105°	170.0	262.3	1049.5	1602.2	1508.7
107.5°	210.1	292.3	990.9	1750.8	1784.9
110°	238.5	312.3	945.6	1782.7	1893.6

TEST NUMBER: P564967

CATALOG NUMBER: SQ4-PW1-100U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	264.0	335.1	903.1	1757.5	1920.9
115°	304.6	368.1	845.3	1673.3	1903.0
117.5°	340.0	403.2	807.2	1554.8	1816.1
120°	363.6	425.9	792.1	1474.6	1737.7
122.5°	386.3	445.8	779.9	1399.6	1649.0
125°	417.9	475.6	766.2	1296.6	1521.7
127.5°	444.8	502.5	758.1	1209.5	1403.6
130°	462.8	520.5	754.4	1156.2	1332.8
132.5°	479.8	534.7	750.6	1111.4	1271.4
135°	502.9	557.2	744.9	1050.2	1184.1
137.5°	528.9	578.3	742.1	998.7	1113.0
140°	543.0	591.5	740.2	964.4	1064.8
142.5°	559.1	603.9	738.3	933.9	1022.3
145°	583.2	623.6	735.5	894.0	962.1
147.5°	606.3	641.6	732.9	860.4	913.3
150°	623.3	652.2	731.9	840.3	883.0
152.5°	636.5	663.5	731.0	823.2	858.5
155°	657.6	679.5	729.6	802.2	827.5
157.5°	676.9	693.8	729.8	786.9	804.2
160°	688.2	703.2	730.7	778.3	790.9
162.5°	697.7	710.8	731.7	770.6	780.6
165°	711.9	721.1	733.1	761.6	767.3
167.5°	722.7	728.3	734.3	756.0	757.9
170°	728.4	733.0	734.3	753.2	753.2
172.5°	733.1	735.9	734.3	749.4	748.5
175°	737.8	739.0	734.3	744.9	742.5
177.5°	739.7	738.8	734.0	740.6	738.8
180°	737.8	737.8	737.8	737.8	737.8

(END OF REPORT)