

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564006

Luminaire Tested: **SQ4-PR1-050U-100D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564006
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4605.8 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564006
CATALOG NUMBER: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564006

CATALOG NUMBER: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66
1	102	97	94	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56
2	93	85	79	74	87	81	75	71	72	68	64	63	60	57	56	53	51	48
3	85	76	68	62	80	71	65	60	64	58	54	56	52	49	50	47	44	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	42	45	41	38	35
5	72	60	52	46	67	57	50	44	51	45	40	46	41	37	40	37	34	31
6	66	54	46	40	62	51	44	38	46	40	35	41	36	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	26	24
8	57	45	37	31	54	42	35	30	38	32	28	34	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	24	21	19
10	50	37	30	25	47	36	29	24	33	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11145	11145	11145
5°	11245	11159	11101
10°	11209	11132	11074
15°	11160	11091	11031
20°	11105	11033	10951
25°	11026	10952	10825
30°	10907	10829	10675
35°	10746	10653	10501
40°	10501	10388	10200
45°	10073	9897	9693
50°	9320	9094	8916
55°	8134	7949	7782
60°	6853	6796	6661
65°	5929	5951	5905
70°	5446	5473	5473
75°	5229	5229	5265
80°	4920	4973	4920
85°	3970	4404	4404



TEST NUMBER: P564006

CATALOG NUMBER: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.2	2.5
10°-20°	326.8	7.1
20°-30°	493.0	10.7
30°-40°	587.4	12.8
40°-50°	579.1	12.6
50°-60°	442.6	9.6
60°-70°	273.9	5.9
70°-80°	155.5	3.4
80°-90°	48.3	1.0
90°-100°	116.5	2.5
100°-110°	316.6	6.9
110°-120°	325.5	7.1
120°-130°	260.2	5.7
130°-140°	204.5	4.4
140°-150°	156.8	3.4
150°-160°	112.8	2.4
160°-170°	69.0	1.5
170°-180°	23.2	0.5
0°-30°	934.0	20.3
0°-40°	1521.4	33.0
0°-60°	2543.1	55.2
0°-90°	3020.7	65.6
90°-120°	758.6	16.5
90°-150°	1380.1	30.0
90°-180°	1585.0	34.4
0°-180°	4605.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1208	1208	1208	1208	1208	
5°	1214	1201	1205	1201	1199	115
15°	1168	1156	1161	1157	1155	330
25°	1083	1070	1076	1064	1063	498
35°	954	943	946	933	932	595
45°	772	762	758	745	743	591
55°	506	498	494	486	484	453
65°	272	270	273	270	270	275
75°	147	147	147	148	148	155
85°	38	40	42	42	42	44
90°	1	3	6	7	7	3
95°	17	64	203	88	59	18
105°	56	88	348	530	499	60
115°	100	121	279	554	632	99
125°	137	156	252	425	501	122
135°	166	184	245	346	390	128
145°	191	205	242	294	316	120
155°	216	224	240	264	272	100
165°	234	237	241	251	252	66
175°	243	244	242	245	244	23
180°	243	243	243	243	243	



TEST NUMBER: P564006

CATALOG NUMBER: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1208.0	1208.0	1208.0	1208.0	1208.0
2.5°	1215.5	1204.9	1208.0	1205.4	1199.7
5°	1214.2	1201.0	1204.9	1200.7	1198.6
7.5°	1204.9	1191.8	1195.7	1191.5	1190.3
10°	1196.5	1184.3	1188.2	1184.0	1182.0
12.5°	1187.4	1174.4	1179.1	1174.0	1172.0
15°	1168.4	1156.2	1161.2	1157.0	1154.9
17.5°	1147.6	1134.6	1139.5	1134.7	1132.0
20°	1131.0	1118.8	1123.7	1116.4	1115.4
22.5°	1112.7	1100.5	1105.4	1095.6	1095.4
25°	1083.1	1069.9	1075.8	1064.4	1063.4
27.5°	1048.0	1035.8	1040.7	1029.0	1027.8
30°	1023.8	1011.6	1016.5	1004.0	1002.0
32.5°	996.4	985.0	989.1	976.6	975.3
35°	954.1	942.9	945.8	933.3	932.3
37.5°	906.0	895.9	897.5	883.8	882.7
40°	871.9	861.7	862.5	848.0	846.9
42.5°	834.5	824.3	823.4	808.8	807.8
45°	772.0	761.9	758.5	744.9	742.9
47.5°	700.9	690.7	684.4	673.4	671.9
50°	649.3	639.1	633.6	624.2	621.2
52.5°	593.5	583.3	578.7	570.1	567.1
55°	505.7	497.5	494.2	485.9	483.8
57.5°	422.2	416.7	415.8	407.6	406.8
60°	371.4	368.4	368.3	361.0	361.0
62.5°	328.2	325.9	327.5	322.7	321.9
65°	271.6	269.5	272.6	270.5	270.5
67.5°	226.8	226.8	228.7	227.9	227.9
70°	201.9	201.9	202.9	202.9	202.9
72.5°	179.4	178.6	181.2	181.2	180.4
75°	146.7	146.7	146.7	147.7	147.7
77.5°	114.2	114.4	115.3	115.1	114.2
80°	92.6	93.6	93.6	92.6	92.6
82.5°	71.0	72.0	72.0	71.8	71.0
85°	37.5	39.5	41.6	41.6	41.6
87.5°	11.0	14.7	17.7	18.0	17.2
90°	0.8	3.1	5.5	7.0	7.0
92.5°	7.0	31.9	55.4	23.8	20.1
95°	17.2	63.7	203.0	88.3	59.3
97.5°	28.4	70.4	311.1	242.1	170.0
100°	35.9	74.8	344.2	349.0	281.8
102.5°	43.4	79.3	353.0	431.6	372.3
105°	56.2	87.5	348.1	530.1	498.8
107.5°	69.5	97.1	328.0	581.0	589.7
110°	78.8	104.0	313.0	591.0	628.4

TEST NUMBER: P564006

CATALOG NUMBER: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	<i>87.0</i>	110.9	298.0	582.7	639.0
115°	<i>99.9</i>	121.3	278.7	554.4	631.5
117.5°	<i>112.1</i>	132.5	266.3	514.4	601.2
120°	<i>120.2</i>	140.1	260.7	487.5	573.7
122.5°	<i>127.1</i>	146.9	257.0	460.6	543.8
125°	<i>137.4</i>	156.5	252.1	424.8	501.1
127.5°	<i>146.6</i>	165.5	249.5	397.7	463.2
130°	<i>152.2</i>	170.5	248.2	380.7	439.5
132.5°	<i>157.8</i>	176.2	247.0	366.2	418.2
135°	<i>165.5</i>	183.8	245.1	346.0	390.3
137.5°	<i>173.8</i>	190.4	244.2	328.2	365.5
140°	<i>178.8</i>	194.8	243.5	316.9	350.5
142.5°	<i>183.8</i>	198.6	242.9	308.0	336.1
145°	<i>191.2</i>	205.0	242.0	294.0	316.1
147.5°	<i>199.7</i>	211.4	241.2	283.0	300.4
150°	<i>205.3</i>	215.2	241.2	276.6	290.4
152.5°	<i>209.7</i>	218.4	240.6	271.0	282.3
155°	<i>216.2</i>	223.9	240.4	264.0	271.6
157.5°	<i>222.6</i>	228.6	240.4	259.3	265.1
160°	<i>226.4</i>	231.7	240.4	256.1	260.7
162.5°	<i>230.1</i>	234.2	241.0	253.6	257.0
165°	<i>234.2</i>	237.2	241.2	251.4	252.1
167.5°	<i>238.4</i>	239.9	242.0	248.7	249.3
170°	<i>239.6</i>	241.2	242.0	247.4	247.4
172.5°	<i>240.9</i>	241.8	242.0	246.2	246.2
175°	<i>242.8</i>	243.5	242.0	245.1	244.3
177.5°	<i>243.4</i>	243.4	241.5	244.0	242.8
180°	<i>242.8</i>	242.8	242.8	242.8	242.8

(END OF REPORT)