

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564174

Luminaire Tested: **SQ4-PR1-0U-075D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564174
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-0U-075D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2272.8 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564174
CATALOG NUMBER: SQ4-PR1-0U-075D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564174

CATALOG NUMBER: SQ4-PR1-0U-075D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8388	8388	8388
5°	8463	8398	8355
10°	8436	8378	8334
15°	8400	8347	8302
20°	8357	8303	8242
25°	8299	8243	8147
30°	8209	8151	8034
35°	8088	8017	7902
40°	7903	7819	7677
45°	7581	7449	7295
50°	7013	6845	6710
55°	6122	5984	5857
60°	5159	5115	5014
65°	4462	4480	4445
70°	4098	4119	4119
75°	3935	3935	3964
80°	3703	3746	3703
85°	2985	3313	3313



TEST NUMBER: P564174

CATALOG NUMBER: SQ4-PR1-0U-075D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.0	3.8
10°-20°	246.0	10.8
20°-30°	371.0	16.3
30°-40°	442.1	19.5
40°-50°	435.8	19.2
50°-60°	333.1	14.7
60°-70°	206.1	9.1
70°-80°	117.1	5.2
80°-90°	35.6	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	703.0	30.9
0°-40°	1145.0	50.4
0°-60°	1914.0	84.2
0°-90°	2272.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2272.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	909	909	909	909	909	
5°	914	904	907	904	902	87
15°	879	870	874	871	869	248
25°	815	805	810	801	800	375
35°	718	710	712	702	702	448
45°	581	573	571	561	559	445
55°	381	374	372	366	364	341
65°	204	203	205	204	204	207
75°	110	110	110	111	111	117
85°	28	30	31	31	31	34
90°	0	0	0	0	0	



TEST NUMBER: P564174

CATALOG NUMBER: SQ4-PR1-0U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	909.1	909.1	909.1	909.1	909.1
2.5°	914.8	906.8	909.1	907.2	902.9
5°	913.8	903.9	906.8	903.6	902.1
7.5°	906.8	897.0	899.9	896.8	895.8
10°	900.5	891.3	894.3	891.1	889.6
12.5°	893.6	883.8	887.4	883.6	882.1
15°	879.4	870.2	873.9	870.7	869.2
17.5°	863.7	853.9	857.6	854.0	852.0
20°	851.2	842.0	845.7	840.2	839.5
22.5°	837.4	828.2	831.9	824.6	824.4
25°	815.2	805.2	809.7	801.1	800.3
27.5°	788.7	779.5	783.2	774.4	773.5
30°	770.5	761.4	765.1	755.6	754.1
32.5°	749.9	741.3	744.4	735.0	734.1
35°	718.1	709.7	711.8	702.4	701.6
37.5°	681.9	674.2	675.5	665.1	664.4
40°	656.2	648.6	649.2	638.2	637.4
42.5°	628.0	620.4	619.7	608.7	608.0
45°	581.0	573.4	570.9	560.6	559.1
47.5°	527.5	519.8	515.1	506.8	505.7
50°	488.6	481.0	476.9	469.8	467.5
52.5°	446.7	439.0	435.5	429.1	426.8
55°	380.6	374.4	372.0	365.7	364.1
57.5°	317.8	313.6	312.9	306.8	306.2
60°	279.6	277.3	277.2	271.7	271.7
62.5°	247.0	245.3	246.5	242.9	242.3
65°	204.4	202.9	205.2	203.6	203.6
67.5°	170.7	170.7	172.1	171.5	171.5
70°	151.9	151.9	152.7	152.7	152.7
72.5°	135.0	134.4	136.4	136.4	135.8
75°	110.4	110.4	110.4	111.2	111.2
77.5°	86.0	86.1	86.8	86.6	86.0
80°	69.7	70.5	70.5	69.7	69.7
82.5°	53.4	54.2	54.2	54.0	53.4
85°	28.2	29.7	31.3	31.3	31.3
87.5°	8.1	10.6	12.5	12.5	11.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)