

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565087

Luminaire Tested: **SQ4-PW1-125U-125D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P565087  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-125U-125D-930-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11720.9 lumens  
Efficiency: N/A  
Efficacy: 100.0 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 117.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P565087  
CATALOG NUMBER: SQ4-PW1-125U-125D-930-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P565087

CATALOG NUMBER: SQ4-PW1-125U-125D-930-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42
2	89	82	76	70	82	75	70	66	64	60	57	53	50	48	43	41	40	35
3	81	72	65	59	75	66	60	55	56	52	48	47	44	41	38	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	32	53	43	36	31	37	31	27	31	27	23	26	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	15
9	50	38	31	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13904	13904	13904
5°	13994	13884	13822
10°	13882	13770	13696
15°	13735	13583	13532
20°	13571	13363	13337
25°	13382	13138	13098
30°	13099	12901	12816
35°	12727	12547	12473
40°	12330	12138	12090
45°	11850	11694	11642
50°	11358	11264	11187
55°	10829	10829	10657
60°	10167	10364	9996
65°	9304	9769	9073
70°	8202	8990	7987
75°	7006	8047	6816
80°	5434	6773	5504
85°	3515	5201	4637



TEST NUMBER: P565087

CATALOG NUMBER: SQ4-PW1-125U-125D-930-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	212.9	1.8
10°-20°	601.0	5.1
20°-30°	891.4	7.6
30°-40°	1043.1	8.9
40°-50°	1038.4	8.9
50°-60°	896.7	7.7
60°-70°	645.5	5.5
70°-80°	338.5	2.9
80°-90°	86.1	0.7
90°-100°	432.4	3.7
100°-110°	1164.8	9.9
110°-120°	1222.5	10.4
120°-130°	992.0	8.5
130°-140°	778.0	6.6
140°-150°	597.3	5.1
150°-160°	429.5	3.7
160°-170°	262.4	2.2
170°-180°	88.5	0.8
0°-30°	1705.3	14.5
0°-40°	2748.4	23.4
0°-60°	4683.5	40.0
0°-90°	5753.6	49.1
90°-120°	2819.7	24.1
90°-150°	5187.0	44.3
90°-180°	5967.0	50.9
0°-180°	11720.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2260	2260	2260	2260	2260	
5°	2266	2241	2249	2242	2239	215
15°	2157	2130	2133	2129	2125	608
25°	1972	1939	1936	1924	1930	907
35°	1695	1672	1671	1655	1661	1060
45°	1362	1351	1344	1340	1338	1051
55°	1010	1008	1010	996	994	901
65°	639	659	671	645	623	634
75°	295	322	339	316	287	316
85°	50	65	74	70	66	66
90°	2	7	14	15	15	6
95°	66	235	709	362	251	69
105°	216	335	1288	1927	1809	227
115°	380	466	1073	2073	2344	374
125°	519	596	963	1628	1916	464
135°	625	698	936	1313	1487	483
145°	723	779	924	1123	1206	453
155°	821	851	916	1008	1040	378
165°	890	901	920	956	961	251
175°	926	924	921	934	931	88
180°	924	924	924	924	924	

TEST NUMBER: P565087

CATALOG NUMBER: SQ4-PW1-125U-125D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2260.5	2260.5	2260.5	2260.5	2260.5
2.5°	2273.3	2254.6	2260.5	2255.5	2244.6
5°	2266.5	2241.2	2248.6	2242.5	2238.6
7.5°	2243.4	2220.0	2225.5	2219.1	2216.7
10°	2222.7	2199.3	2204.8	2196.7	2192.8
12.5°	2198.8	2173.9	2179.3	2171.3	2168.9
15°	2157.0	2129.7	2133.1	2129.0	2125.1
17.5°	2108.4	2080.7	2081.3	2074.9	2074.1
20°	2073.3	2044.1	2041.5	2033.6	2037.5
22.5°	2035.1	2004.3	2001.6	1990.6	1996.1
25°	1971.8	1938.6	1935.9	1924.1	1929.9
27.5°	1898.5	1865.7	1865.8	1849.2	1855.4
30°	1844.3	1813.1	1816.4	1796.7	1804.5
32.5°	1786.9	1758.9	1760.6	1740.9	1748.7
35°	1694.9	1671.5	1671.0	1655.2	1661.1
37.5°	1600.9	1580.3	1577.0	1567.9	1569.4
40°	1535.6	1518.1	1511.7	1505.7	1505.7
42.5°	1467.1	1451.1	1444.8	1440.3	1438.8
45°	1362.3	1350.6	1344.4	1340.4	1338.4
47.5°	1258.7	1247.8	1242.4	1239.6	1237.6
50°	1187.0	1179.2	1177.1	1171.1	1169.1
52.5°	1115.3	1110.7	1108.6	1101.0	1099.0
55°	1009.8	1007.8	1009.8	995.8	993.8
57.5°	899.8	903.0	909.4	890.6	885.9
60°	826.5	834.3	842.5	820.4	812.6
62.5°	751.7	764.1	775.6	750.2	739.3
65°	639.3	658.8	671.2	644.8	623.4
67.5°	531.0	555.1	570.0	541.6	517.4
70°	456.1	483.4	499.9	471.4	444.1
72.5°	390.8	421.1	434.6	407.7	380.4
75°	294.8	322.0	338.6	316.0	286.8
77.5°	209.1	234.8	248.6	228.9	204.7
80°	153.4	180.6	191.2	174.8	155.4
82.5°	108.7	131.3	138.6	128.8	115.5
85°	49.8	65.4	73.7	69.6	65.7
87.5°	13.2	25.0	33.1	33.4	34.9
90°	2.4	7.0	14.1	15.3	15.3
92.5°	28.7	101.5	200.7	96.6	67.1
95°	65.9	235.2	708.9	362.5	250.8
97.5°	105.3	269.2	1111.8	928.8	700.4
100°	135.4	282.8	1240.0	1297.3	1076.3
102.5°	164.6	301.9	1282.3	1573.3	1391.9
105°	215.5	335.2	1288.2	1927.3	1808.7
107.5°	263.5	370.4	1233.4	2109.2	2139.8
110°	295.6	396.9	1183.4	2165.7	2277.4



TEST NUMBER: P565087

CATALOG NUMBER: SQ4-PW1-125U-125D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	329.5	423.4	1135.4	2153.2	2336.7
115°	380.3	465.5	1072.7	2072.8	2344.5
117.5°	426.7	506.6	1024.2	1944.4	2247.0
120°	456.9	534.0	999.7	1852.3	2163.1
122.5°	483.3	559.5	981.8	1758.0	2068.0
125°	519.3	596.4	963.2	1628.0	1915.9
127.5°	553.9	629.9	951.5	1513.3	1770.3
130°	574.6	650.6	946.7	1447.6	1673.3
132.5°	595.4	670.4	942.0	1389.7	1597.0
135°	625.3	697.8	936.1	1313.4	1487.2
137.5°	653.8	723.3	933.1	1248.6	1391.4
140°	673.6	740.3	930.3	1208.7	1337.7
142.5°	694.3	756.5	928.4	1171.5	1280.2
145°	723.0	779.4	924.4	1122.9	1205.8
147.5°	754.1	803.1	920.4	1082.0	1147.2
150°	774.8	817.4	918.5	1056.3	1110.4
152.5°	793.7	830.7	917.5	1035.4	1079.3
155°	820.7	850.7	916.1	1007.5	1039.8
157.5°	844.5	867.8	916.4	988.0	1009.6
160°	859.6	879.2	917.3	976.5	992.7
162.5°	872.8	888.7	918.2	967.0	978.5
165°	890.2	900.6	919.7	956.3	960.9
167.5°	904.4	910.3	920.8	948.0	949.8
170°	913.8	916.1	920.8	943.2	943.2
172.5°	919.4	919.9	921.8	938.5	938.5
175°	925.5	924.4	920.8	933.7	931.4
177.5°	928.1	926.3	921.5	929.0	927.2
180°	924.4	924.4	924.4	924.4	924.4

(END OF REPORT)