

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519033

Luminaire Tested: **SQ4-WB-025U-100D-930-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519033  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-025U-100D-930-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5081.4 lumens  
Efficiency: N/A  
Efficacy: 80.0 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 63.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519033  
CATALOG NUMBER: SQ4-WB-025U-100D-930-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P519033

CATALOG NUMBER: SQ4-WB-025U-100D-930-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	114	114	114	114	108	108	108	108	99	99	99	89	89	89	81	81	81	77		
1	106	102	98	95	101	97	94	92	89	87	85	82	80	78	75	73	72	69		
2	98	91	86	81	93	87	82	78	80	76	73	74	71	68	68	66	64	60		
3	90	82	75	70	86	79	73	68	73	68	64	67	63	60	62	59	56	53		
4	84	74	67	61	80	71	65	59	66	61	56	61	57	53	57	53	50	48		
5	78	67	60	54	74	65	58	53	60	54	50	56	51	48	52	48	45	43		
6	73	61	54	48	69	59	52	47	55	49	45	51	47	43	48	44	41	39		
7	68	56	49	43	65	54	47	42	51	45	41	48	43	39	45	40	37	35		
8	63	52	44	39	61	50	43	38	47	41	37	44	39	35	41	37	34	32		
9	60	48	41	36	57	46	40	35	44	38	34	41	36	33	39	34	31	29		
10	56	44	37	33	54	43	37	32	41	35	31	38	33	30	36	32	29	27		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16578	16578	16578
5°	16371	16313	16408
10°	15467	15608	15970
15°	14278	14610	15265
20°	12967	13454	14345
25°	11630	12264	13364
30°	10399	11079	12347
35°	9093	9751	11144
40°	7654	8261	9648
45°	6317	6861	8055
50°	5273	5749	6711
55°	4477	4934	5542
60°	3826	4277	4422
65°	3046	3598	2857
70°	2701	2807	1744
75°	2502	2277	1067
80°	2302	2093	921
85°	2089	1920	748



TEST NUMBER: P519033

CATALOG NUMBER: SQ4-WB-025U-100D-930-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	247.2	4.9
10°-20°	643.0	12.7
20°-30°	832.9	16.4
30°-40°	815.6	16.1
40°-50°	624.3	12.3
50°-60°	416.0	8.2
60°-70°	227.0	4.5
70°-80°	94.6	1.9
80°-90°	27.7	0.5
90°-100°	86.7	1.7
100°-110°	227.9	4.5
110°-120°	236.3	4.7
120°-130°	189.6	3.7
130°-140°	148.7	2.9
140°-150°	114.2	2.2
150°-160°	82.2	1.6
160°-170°	50.3	1.0
170°-180°	17.0	0.3
0°-30°	1723.2	33.9
0°-40°	2538.8	50.0
0°-60°	3579.1	70.4
0°-90°	3928.5	77.3
90°-120°	551.0	10.8
90°-150°	1003.4	19.7
90°-180°	1153.0	22.7
0°-180°	5081.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2695	2695	2695	2695	2695	
5°	2652	2625	2642	2648	2657	247
15°	2242	2234	2294	2357	2397	626
25°	1714	1718	1807	1886	1969	788
35°	1211	1217	1299	1386	1484	753
45°	726	740	789	848	926	566
55°	418	435	460	478	517	379
65°	209	227	247	216	196	218
75°	105	105	96	66	45	112
85°	30	30	27	18	11	32
90°	1	3	9	5	5	2
95°	11	45	149	77	52	13
105°	41	62	252	382	357	43
115°	73	89	202	403	460	72
125°	102	114	184	310	366	90
135°	121	133	178	250	284	94
145°	140	149	176	214	230	88
155°	158	163	176	193	198	73
165°	171	173	176	182	185	48
175°	178	178	177	179	179	17
180°	178	178	178	178	178	

TEST NUMBER: P519033

CATALOG NUMBER: SQ4-WB-025U-100D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2695.3	2695.3	2695.3	2695.3	2695.3
2.5°	2701.9	2677.9	2683.9	2683.8	2676.4
5°	2651.5	2624.9	2642.1	2648.2	2657.4
7.5°	2553.1	2533.0	2564.2	2587.4	2606.1
10°	2476.5	2459.1	2499.0	2532.6	2556.9
12.5°	2387.6	2373.0	2422.3	2467.5	2499.2
15°	2242.3	2234.2	2294.4	2356.8	2397.2
17.5°	2086.9	2083.0	2152.0	2224.8	2276.6
20°	1981.0	1979.8	2055.5	2131.3	2191.5
22.5°	1874.0	1876.6	1956.1	2035.0	2103.5
25°	1713.7	1718.3	1807.1	1885.9	1969.1
27.5°	1565.4	1567.4	1659.3	1742.4	1831.2
30°	1464.1	1469.9	1559.9	1646.0	1738.5
32.5°	1362.9	1369.6	1457.7	1546.7	1641.1
35°	1211.0	1216.8	1298.6	1385.9	1484.2
37.5°	1054.5	1062.3	1134.9	1217.5	1314.2
40°	953.2	964.8	1028.9	1106.8	1201.6
42.5°	855.8	870.1	929.6	1003.4	1089.0
45°	726.2	740.0	788.8	848.5	926.0
47.5°	614.5	630.5	668.0	719.4	785.5
50°	551.1	566.2	600.8	638.9	701.3
52.5°	495.3	510.3	541.2	570.5	623.7
55°	417.5	434.8	460.1	477.5	516.8
57.5°	353.6	370.3	390.3	398.2	422.0
60°	311.0	329.5	347.7	346.8	359.5
62.5°	272.2	288.0	306.1	293.6	294.2
65°	209.3	226.7	247.2	216.0	196.3
67.5°	169.1	172.8	194.0	150.6	127.3
70°	150.2	150.2	156.1	116.6	97.0
72.5°	132.2	132.2	126.8	94.9	74.3
75°	105.3	105.3	95.8	65.8	44.9
77.5°	81.1	80.2	73.3	49.1	32.6
80°	65.0	65.0	59.1	38.7	26.0
82.5°	50.9	50.9	45.9	30.3	19.4
85°	29.6	29.6	27.2	17.6	10.6
87.5°	10.6	11.1	11.3	6.6	5.6
90°	1.1	3.4	9.1	4.6	4.6
92.5°	4.8	23.1	51.1	22.6	14.6
95°	11.4	44.9	149.4	77.0	52.5
97.5°	19.8	49.3	223.5	177.7	130.9
100°	26.2	53.0	246.3	249.6	193.8
102.5°	31.7	56.7	252.7	310.9	263.2
105°	41.0	62.2	252.0	382.5	356.9
107.5°	50.6	70.3	237.6	419.8	426.0
110°	57.0	74.9	225.8	429.3	456.1



TEST NUMBER: P519033

CATALOG NUMBER: SQ4-WB-025U-100D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	63.4	80.3	214.8	423.3	464.3
115°	73.0	88.6	201.8	402.7	459.5
117.5°	82.3	96.6	192.9	374.1	437.2
120°	87.8	101.2	189.3	354.9	416.2
122.5°	93.3	106.7	186.5	335.7	396.1
125°	101.5	113.7	183.6	310.3	366.0
127.5°	108.1	120.6	181.1	289.8	336.8
130°	111.7	125.1	180.2	276.9	320.4
132.5°	115.4	128.8	179.2	265.9	304.9
135°	120.9	133.1	177.9	250.5	283.9
137.5°	126.6	138.6	177.7	238.9	266.4
140°	131.1	142.3	176.7	229.8	255.4
142.5°	134.8	145.0	176.7	223.3	245.4
145°	140.3	149.2	175.6	213.6	230.3
147.5°	145.7	154.4	175.6	205.6	219.4
150°	149.4	157.2	175.6	200.9	212.1
152.5°	153.0	159.0	175.6	197.2	205.7
155°	158.5	163.0	175.6	192.8	198.4
157.5°	162.6	166.8	175.6	188.9	192.9
160°	165.3	168.7	175.6	187.1	189.3
162.5°	168.1	170.5	175.6	185.2	187.5
165°	171.0	173.3	175.6	182.5	184.7
167.5°	173.8	174.9	176.7	181.3	182.2
170°	175.6	176.7	176.7	181.3	181.3
172.5°	176.5	176.7	176.7	180.4	179.5
175°	177.9	177.9	176.7	179.0	179.0
177.5°	177.9	177.9	177.0	178.8	177.9
180°	177.9	177.9	177.9	177.9	177.9

(END OF REPORT)