

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519081

Luminaire Tested: **SQ4-WB-050U-050D-930-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519081
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-050U-050D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4394.2 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 44.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519081
CATALOG NUMBER: SQ4-WB-050U-050D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519081

CATALOG NUMBER: SQ4-WB-050U-050D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	98	94	91	87	90	87	84	81	73	70	69	60	58	57	48	47	46	41
2	90	83	78	73	83	77	72	68	65	61	59	54	51	49	43	42	41	36
3	83	74	68	62	76	69	63	58	58	54	51	49	46	43	40	38	36	32
4	76	66	59	54	70	62	55	50	52	48	44	44	41	38	36	34	32	28
5	71	60	52	47	65	56	49	44	48	43	39	40	36	34	33	31	29	25
6	65	54	47	41	60	50	44	39	43	38	34	37	33	30	30	28	26	23
7	61	49	42	37	56	46	39	35	40	35	31	34	30	27	28	25	23	21
8	57	45	38	33	52	42	36	31	36	31	28	31	27	25	26	23	21	19
9	53	41	34	30	49	39	32	28	34	29	25	29	25	22	24	22	20	17
10	50	38	31	27	46	36	30	26	31	26	23	27	23	21	23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8507	8507	8507
5°	8400	8370	8419
10°	7936	8008	8194
15°	7326	7496	7832
20°	6653	6904	7360
25°	5968	6293	6857
30°	5335	5685	6335
35°	4666	5003	5719
40°	3927	4239	4950
45°	3241	3521	4133
50°	2706	2950	3443
55°	2297	2532	2844
60°	1963	2195	2270
65°	1563	1845	1466
70°	1387	1440	896
75°	1283	1169	549
80°	1183	1073	475
85°	1073	988	388



TEST NUMBER: P519081

CATALOG NUMBER: SQ4-WB-050U-050D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.9	2.9
10°-20°	329.9	7.5
20°-30°	427.4	9.7
30°-40°	418.5	9.5
40°-50°	320.3	7.3
50°-60°	213.5	4.9
60°-70°	116.5	2.7
70°-80°	48.5	1.1
80°-90°	15.1	0.3
90°-100°	174.8	4.0
100°-110°	474.9	10.8
110°-120°	488.2	11.1
120°-130°	390.4	8.9
130°-140°	306.7	7.0
140°-150°	235.2	5.4
150°-160°	169.1	3.8
160°-170°	103.4	2.4
170°-180°	34.8	0.8
0°-30°	884.2	20.1
0°-40°	1302.7	29.6
0°-60°	1836.5	41.8
0°-90°	2016.6	45.9
90°-120°	1137.9	25.9
90°-150°	2070.2	47.1
90°-180°	2378.0	54.1
0°-180°	4394.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1383	1383	1383	1383	1383	
5°	1360	1347	1356	1359	1364	127
15°	1150	1146	1177	1209	1230	321
25°	879	882	927	968	1010	404
35°	621	624	666	711	762	386
45°	373	380	405	435	475	291
55°	214	223	236	245	265	194
65°	107	116	127	111	101	112
75°	54	54	49	34	23	58
85°	15	15	14	9	6	17
90°	1	5	8	10	10	3
95°	26	96	304	132	89	27
105°	84	131	522	795	748	90
115°	150	182	418	832	947	148
125°	206	235	378	637	752	184
135°	248	276	368	519	585	192
145°	287	308	363	441	474	180
155°	324	336	361	396	408	150
165°	351	356	362	377	378	99
175°	364	365	363	368	366	35
180°	364	364	364	364	364	

TEST NUMBER: P519081

CATALOG NUMBER: SQ4-WB-050U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1383.0	1383.0	1383.0	1383.0	1383.0
2.5°	1386.3	1374.0	1377.1	1377.0	1373.2
5°	1360.5	1346.9	1355.6	1358.8	1363.5
7.5°	1310.0	1299.7	1315.7	1327.6	1337.2
10°	1270.7	1261.8	1282.2	1299.5	1312.0
12.5°	1225.1	1217.6	1242.9	1266.1	1282.3
15°	1150.5	1146.4	1177.2	1209.3	1230.0
17.5°	1070.8	1068.8	1104.2	1141.6	1168.1
20°	1016.4	1015.8	1054.7	1093.6	1124.4
22.5°	961.6	962.9	1003.7	1044.2	1079.3
25°	879.3	881.7	927.2	967.6	1010.4
27.5°	803.2	804.3	851.4	894.0	939.6
30°	751.2	754.2	800.4	844.6	892.0
32.5°	699.3	702.7	748.0	793.6	842.0
35°	621.4	624.4	666.3	711.1	761.6
37.5°	541.0	545.1	582.3	624.7	674.3
40°	489.1	495.0	527.9	567.9	616.5
42.5°	439.1	446.5	477.0	514.9	558.8
45°	372.6	379.7	404.8	435.4	475.1
47.5°	315.3	323.5	342.7	369.1	403.1
50°	282.8	290.5	308.3	327.8	359.8
52.5°	254.1	261.9	277.7	292.7	320.0
55°	214.2	223.1	236.1	245.0	265.2
57.5°	181.4	190.0	200.3	204.3	216.5
60°	159.6	169.1	178.4	177.9	184.5
62.5°	139.7	147.8	157.0	150.6	151.0
65°	107.4	116.3	126.8	110.8	100.7
67.5°	86.8	88.7	99.5	77.3	65.3
70°	77.1	77.1	80.1	59.8	49.8
72.5°	67.8	67.8	65.1	48.7	38.1
75°	54.0	54.0	49.2	33.7	23.1
77.5°	41.6	41.2	37.6	25.2	16.7
80°	33.4	33.4	30.3	19.9	13.4
82.5°	26.1	26.1	23.5	15.5	10.0
85°	15.2	15.2	14.0	9.0	5.5
87.5°	5.6	6.3	6.5	5.0	4.5
90°	1.2	4.6	8.2	10.5	10.5
92.5°	10.5	47.9	83.1	35.7	30.2
95°	25.8	95.6	304.4	132.5	89.0
97.5°	42.6	105.6	466.7	363.1	255.0
100°	53.9	112.2	516.4	523.4	422.7
102.5°	65.1	118.9	529.5	647.4	558.5
105°	84.3	131.2	522.2	795.1	748.2
107.5°	104.2	145.7	492.0	871.4	884.5
110°	118.3	156.0	469.5	886.5	942.6

TEST NUMBER: P519081

CATALOG NUMBER: SQ4-WB-050U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	130.4	166.4	447.0	874.0	958.5
115°	149.9	181.9	418.0	831.6	947.2
117.5°	168.1	198.8	399.5	771.5	901.8
120°	180.3	210.1	391.1	731.2	860.6
122.5°	190.6	220.4	385.5	690.9	815.6
125°	206.1	234.7	378.2	637.2	751.7
127.5°	219.9	248.3	374.2	596.6	694.8
130°	228.3	255.8	372.3	571.1	659.2
132.5°	236.8	264.2	370.5	549.3	627.4
135°	248.2	275.7	367.7	519.0	585.4
137.5°	260.6	285.6	366.3	492.3	548.2
140°	268.1	292.2	365.3	475.4	525.7
142.5°	275.6	297.8	364.4	462.1	504.2
145°	286.9	307.5	363.0	441.0	474.2
147.5°	299.5	317.1	361.8	424.5	450.6
150°	307.9	322.8	361.8	415.0	435.6
152.5°	314.5	327.6	360.9	406.4	423.4
155°	324.3	335.8	360.6	396.0	407.5
157.5°	333.9	342.9	360.6	388.9	397.6
160°	339.6	347.6	360.6	384.2	391.1
162.5°	345.2	351.4	361.6	380.4	385.5
165°	351.3	355.8	361.8	377.1	378.2
167.5°	357.6	359.9	363.0	373.1	374.0
170°	359.5	361.8	363.0	371.2	371.2
172.5°	361.3	362.7	363.0	369.3	369.3
175°	364.1	365.3	363.0	367.6	366.5
177.5°	365.1	365.1	362.3	366.0	364.1
180°	364.1	364.1	364.1	364.1	364.1

(END OF REPORT)