

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519345

Luminaire Tested: **SQ4-WB-0U-125D-930-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519345
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-125D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4899.8 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519345
CATALOG NUMBER: SQ4-WB-0U-125D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519345

CATALOG NUMBER: SQ4-WB-OU-125D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89	
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78			78	
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			69	
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62			62	
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55			55	
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50			50	
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45			45	
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41			41	
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38			38	
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35			35	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20682	20682	20682
5°	20424	20351	20470
10°	19297	19472	19923
15°	17813	18226	19044
20°	16177	16785	17896
25°	14509	15301	16672
30°	12973	13822	15404
35°	11344	12164	13904
40°	9548	10306	12036
45°	7880	8560	10049
50°	6580	7172	8372
55°	5585	6154	6915
60°	4773	5336	5517
65°	3802	4488	3564
70°	3370	3503	2176
75°	3120	2840	1333
80°	2873	2614	1151
85°	2604	2392	939



TEST NUMBER: P519345

CATALOG NUMBER: SQ4-WB-OU-125D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	308.4	6.3
10°-20°	802.2	16.4
20°-30°	1039.1	21.2
30°-40°	1017.5	20.8
40°-50°	778.9	15.9
50°-60°	519.0	10.6
60°-70°	283.2	5.8
70°-80°	118.0	2.4
80°-90°	33.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2149.7	43.9
0°-40°	3167.3	64.6
0°-60°	4465.1	91.1
0°-90°	4899.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4899.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3362	3362	3362	3362	3362	
5°	3308	3275	3296	3304	3315	308
15°	2797	2787	2862	2940	2991	781
25°	2138	2144	2254	2353	2457	983
35°	1511	1518	1620	1729	1852	939
45°	906	923	984	1059	1155	706
55°	521	542	574	596	645	472
65°	261	283	308	269	245	271
75°	131	131	120	82	56	140
85°	37	37	34	22	13	42
90°	0	0	0	0	0	



TEST NUMBER: P519345

CATALOG NUMBER: SQ4-WB-OU-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3362.5	3362.5	3362.5	3362.5	3362.5
2.5°	3370.8	3340.8	3348.4	3348.1	3338.9
5°	3307.9	3274.7	3296.1	3303.8	3315.3
7.5°	3185.2	3160.1	3199.0	3227.9	3251.3
10°	3089.6	3067.9	3117.6	3159.6	3189.9
12.5°	2978.6	2960.4	3022.0	3078.4	3117.9
15°	2797.4	2787.3	2862.3	2940.2	2990.7
17.5°	2603.6	2598.6	2684.7	2775.6	2840.2
20°	2471.4	2469.9	2564.3	2659.0	2734.0
22.5°	2338.0	2341.1	2440.4	2538.8	2624.2
25°	2137.9	2143.7	2254.5	2352.7	2456.6
27.5°	1952.9	1955.5	2070.0	2173.8	2284.6
30°	1826.6	1833.8	1946.1	2053.5	2168.9
32.5°	1700.3	1708.7	1818.6	1929.6	2047.3
35°	1510.8	1518.1	1620.0	1729.0	1851.7
37.5°	1315.5	1325.3	1415.8	1518.9	1639.5
40°	1189.2	1203.6	1283.6	1380.7	1499.0
42.5°	1067.6	1085.5	1159.7	1251.8	1358.6
45°	905.9	923.2	984.1	1058.6	1155.3
47.5°	766.6	786.5	833.3	897.5	980.0
50°	687.6	706.3	749.5	797.0	874.9
52.5°	617.9	636.7	675.2	711.8	778.1
55°	520.8	542.5	573.9	595.7	644.8
57.5°	441.2	461.9	486.9	496.7	526.4
60°	388.0	411.1	433.8	432.7	448.5
62.5°	339.6	359.3	381.8	366.2	367.1
65°	261.2	282.8	308.4	269.4	244.9
67.5°	211.0	215.6	242.0	187.9	158.8
70°	187.4	187.4	194.8	145.5	121.0
72.5°	165.0	165.0	158.2	118.3	92.7
75°	131.3	131.3	119.5	82.0	56.1
77.5°	101.2	100.1	91.5	61.2	40.7
80°	81.1	81.1	73.8	48.3	32.5
82.5°	63.4	63.4	57.2	37.8	24.2
85°	36.9	36.9	33.9	21.9	13.3
87.5°	13.0	13.0	11.8	7.1	5.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)