

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564510

Luminaire Tested: **SQ4-PR1-150U-125D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564510  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8648.8 lumens  
Efficiency: N/A  
Efficacy: 104.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 83.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564510  
CATALOG NUMBER: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564510

CATALOG NUMBER: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38				
2	88	81	75	70	81	75	69	65	62	59	55	51	48	46	40	39	37	32				
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	63	56	50	68	58	52	47	49	44	40	40	37	34	32	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18				
7	58	46	38	33	53	42	35	31	36	31	27	30	26	23	24	21	19	16				
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14222	14222	14222
5°	14351	14240	14166
10°	14305	14206	14131
15°	14242	14154	14077
20°	14171	14079	13975
25°	14071	13976	13814
30°	13919	13820	13622
35°	13714	13593	13400
40°	13401	13257	13017
45°	12855	12629	12369
50°	11892	11606	11378
55°	10380	10145	9931
60°	8746	8673	8501
65°	7564	7595	7536
70°	6949	6984	6984
75°	6673	6673	6720
80°	6280	6349	6280
85°	5060	5621	5621



TEST NUMBER: P564510

CATALOG NUMBER: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	145.8	1.7
10°-20°	417.1	4.8
20°-30°	629.1	7.3
30°-40°	749.6	8.7
40°-50°	739.0	8.5
50°-60°	564.8	6.5
60°-70°	349.5	4.0
70°-80°	198.5	2.3
80°-90°	61.9	0.7
90°-100°	345.5	4.0
100°-110°	934.2	10.8
110°-120°	982.2	11.4
120°-130°	797.8	9.2
130°-140°	625.8	7.2
140°-150°	480.3	5.6
150°-160°	345.4	4.0
160°-170°	211.0	2.4
170°-180°	71.1	0.8
0°-30°	1191.9	13.8
0°-40°	1941.5	22.4
0°-60°	3245.3	37.5
0°-90°	3855.2	44.6
90°-120°	2262.0	26.2
90°-150°	4166.0	48.2
90°-180°	4794.0	55.4
0°-180°	8648.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1542	1542	1542	1542	1542	
5°	1550	1533	1538	1532	1530	147
15°	1491	1476	1482	1476	1474	421
25°	1382	1365	1373	1358	1357	636
35°	1218	1203	1207	1191	1190	760
45°	985	972	968	951	948	755
55°	645	635	631	620	617	578
65°	346	344	348	345	345	351
75°	187	187	187	188	188	198
85°	48	50	53	53	53	56
90°	2	5	10	11	10	5
95°	54	188	575	297	177	56
105°	174	268	1036	1529	1466	183
115°	306	374	860	1664	1878	302
125°	419	480	775	1307	1536	373
135°	502	561	754	1056	1195	388
145°	583	627	744	904	972	365
155°	659	684	737	810	837	304
165°	717	724	740	769	773	202
175°	744	744	741	751	749	71
180°	744	744	744	744	744	

TEST NUMBER: P564510

CATALOG NUMBER: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1541.5	1541.5	1541.5	1541.5	1541.5
2.5°	1551.1	1537.6	1541.5	1538.2	1530.9
5°	1549.5	1532.6	1537.6	1532.2	1529.6
7.5°	1537.6	1520.9	1525.9	1520.5	1519.0
10°	1526.9	1511.4	1516.3	1511.0	1508.4
12.5°	1515.3	1498.6	1504.6	1498.2	1495.6
15°	1491.1	1475.5	1481.8	1476.4	1473.8
17.5°	1464.5	1447.9	1454.2	1448.0	1444.6
20°	1443.3	1427.7	1434.0	1424.7	1423.4
22.5°	1419.9	1404.3	1410.6	1398.1	1397.9
25°	1382.2	1365.3	1372.9	1358.3	1357.0
27.5°	1337.3	1321.8	1328.0	1313.1	1311.6
30°	1306.5	1291.0	1297.2	1281.2	1278.6
32.5°	1271.5	1256.9	1262.2	1246.2	1244.7
35°	1217.6	1203.3	1206.9	1191.0	1189.7
37.5°	1156.2	1143.2	1145.3	1127.8	1126.5
40°	1112.7	1099.7	1100.7	1082.1	1080.8
42.5°	1064.9	1051.9	1050.8	1032.2	1030.9
45°	985.2	972.2	967.9	950.6	948.0
47.5°	894.4	881.4	873.4	859.3	857.5
50°	828.5	815.5	808.6	796.6	792.7
52.5°	757.4	744.4	738.5	727.5	723.6
55°	645.3	634.9	630.7	620.0	617.4
57.5°	538.8	531.8	530.6	520.2	519.2
60°	474.0	470.1	470.0	460.7	460.7
62.5°	418.8	415.9	418.0	411.9	410.8
65°	346.5	344.0	347.9	345.2	345.2
67.5°	289.5	289.5	291.8	290.8	290.8
70°	257.6	257.6	258.9	258.9	258.9
72.5°	228.9	227.9	231.3	231.3	230.2
75°	187.2	187.2	187.2	188.5	188.5
77.5°	145.8	146.0	147.1	146.8	145.8
80°	118.2	119.5	119.5	118.2	118.2
82.5°	90.6	91.9	91.9	91.6	90.6
85°	47.8	50.4	53.1	53.1	53.1
87.5°	14.1	18.9	23.3	23.5	22.3
90°	1.6	4.7	10.4	11.2	10.4
92.5°	22.7	82.8	163.4	70.9	51.4
95°	53.6	188.2	574.6	297.4	176.9
97.5°	86.1	215.9	895.7	741.3	544.4
100°	110.4	227.0	995.6	1038.3	839.5
102.5°	132.9	242.6	1030.8	1263.5	1114.8
105°	173.7	268.4	1036.4	1528.8	1466.2
107.5°	211.4	297.8	991.1	1694.3	1715.1
110°	240.9	319.1	950.8	1738.7	1827.1

TEST NUMBER: P564510

CATALOG NUMBER: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	267.1	340.4	913.6	1729.8	1878.3
115°	305.7	373.8	859.5	1663.9	1878.3
117.5°	343.5	407.4	823.8	1563.3	1806.3
120°	366.5	429.1	802.7	1491.0	1739.1
122.5°	388.3	449.7	789.9	1413.6	1663.5
125°	418.6	479.6	774.7	1307.3	1535.8
127.5°	446.4	506.4	765.7	1220.6	1421.5
130°	461.8	523.6	761.9	1167.0	1348.5
132.5°	477.8	539.0	758.1	1118.6	1285.8
135°	501.8	561.3	753.9	1055.6	1194.9
137.5°	526.0	582.2	750.4	1004.4	1117.9
140°	542.6	595.0	749.1	971.5	1072.4
142.5°	558.6	607.9	746.5	941.7	1030.2
145°	583.4	627.3	743.5	903.5	972.4
147.5°	606.0	644.8	740.0	868.9	921.8
150°	622.6	657.1	738.7	850.1	892.4
152.5°	638.0	668.1	738.1	832.6	867.4
155°	658.7	684.5	737.1	810.5	837.1
157.5°	680.1	698.1	737.3	795.1	812.6
160°	692.3	707.1	737.9	785.4	797.9
162.5°	701.9	714.2	738.5	777.6	787.0
165°	717.1	724.1	740.3	769.2	773.1
167.5°	727.5	732.3	740.5	761.9	763.8
170°	733.9	736.2	741.1	758.7	758.7
172.5°	739.0	739.5	741.1	754.8	754.2
175°	744.3	743.5	741.1	750.7	749.1
177.5°	746.1	744.2	740.9	747.3	745.4
180°	743.5	743.5	743.5	743.5	743.5

(END OF REPORT)