

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564990

Luminaire Tested: **SQ4-PW1-100U-125D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564990
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-125D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7031.3 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 68.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564990
CATALOG NUMBER: SQ4-PW1-100U-125D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564990

CATALOG NUMBER: SQ4-PW1-100U-125D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55		
1	99	95	91	87	92	88	85	82	76	73	71	64	62	61	53	52	51	46		
2	90	83	77	71	83	77	72	67	66	62	59	56	53	51	47	45	43	39		
3	82	73	65	60	76	68	61	56	59	54	49	50	46	43	42	39	37	33		
4	75	64	57	50	70	60	53	48	52	47	42	44	40	37	37	34	32	28		
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	30	28	25		
6	64	52	43	38	59	48	41	36	42	36	32	36	32	28	31	27	24	22		
7	59	47	39	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19		
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	22	19	17		
9	51	39	31	26	47	36	30	25	32	26	22	28	23	20	24	20	18	15		
10	48	36	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13904	13904	13904
5°	13994	13884	13822
10°	13882	13771	13696
15°	13735	13583	13532
20°	13571	13363	13336
25°	13382	13138	13098
30°	13098	12900	12816
35°	12726	12547	12473
40°	12329	12138	12090
45°	11850	11695	11643
50°	11359	11263	11187
55°	10829	10829	10658
60°	10167	10365	9996
65°	9304	9769	9073
70°	8203	8991	7987
75°	7005	8046	6816
80°	5430	6774	5504
85°	3515	5198	4637



TEST NUMBER: P564990

CATALOG NUMBER: SQ4-PW1-100U-125D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.9	2.0
10°-20°	400.7	5.7
20°-30°	594.3	8.5
30°-40°	695.4	9.9
40°-50°	692.3	9.8
50°-60°	597.8	8.5
60°-70°	430.3	6.1
70°-80°	225.7	3.2
80°-90°	57.0	0.8
90°-100°	230.4	3.3
100°-110°	635.9	9.0
110°-120°	655.9	9.3
120°-130°	527.0	7.5
130°-140°	414.2	5.9
140°-150°	317.7	4.5
150°-160°	228.3	3.2
160°-170°	139.6	2.0
170°-180°	47.1	0.7
0°-30°	1136.9	16.2
0°-40°	1832.3	26.1
0°-60°	3122.4	44.4
0°-90°	3835.3	54.5
90°-120°	1522.1	21.6
90°-150°	2781.0	39.6
90°-180°	3196.0	45.5
0°-180°	7031.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1507	1507	1507	1507	1507	
5°	1511	1494	1499	1495	1492	143
15°	1438	1420	1422	1419	1417	405
25°	1314	1292	1291	1283	1287	604
35°	1130	1114	1114	1104	1107	706
45°	908	900	896	894	892	701
55°	673	672	673	664	663	601
65°	426	439	448	430	416	422
75°	196	215	226	211	191	211
85°	33	44	49	46	44	44
90°	2	3	6	7	8	4
95°	34	125	418	172	112	36
105°	113	175	700	1068	1006	121
115°	203	245	564	1116	1269	200
125°	279	317	511	864	1014	248
135°	335	371	497	700	789	259
145°	389	416	490	596	641	243
155°	438	453	486	535	552	202
165°	475	481	489	508	512	134
175°	492	493	490	497	495	47
180°	492	492	492	492	492	

TEST NUMBER: P564990

CATALOG NUMBER: SQ4-PW1-100U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1507.0	1507.0	1507.0	1507.0	1507.0
2.5°	1515.5	1503.1	1507.0	1503.7	1496.4
5°	1511.0	1494.1	1499.1	1495.0	1492.4
7.5°	1495.6	1480.0	1483.7	1479.4	1477.8
10°	1481.8	1466.2	1469.9	1464.5	1461.9
12.5°	1465.9	1449.3	1452.9	1447.5	1446.0
15°	1438.0	1419.8	1422.1	1419.3	1416.7
17.5°	1405.6	1387.2	1387.5	1383.3	1382.8
20°	1382.2	1362.7	1361.0	1355.7	1358.3
22.5°	1356.7	1336.2	1334.4	1327.1	1330.7
25°	1314.5	1292.4	1290.6	1282.7	1286.6
27.5°	1265.6	1243.8	1243.9	1232.8	1237.0
30°	1229.5	1208.8	1210.9	1197.8	1203.0
32.5°	1191.3	1172.6	1173.8	1160.6	1165.8
35°	1129.9	1114.4	1114.0	1103.5	1107.4
37.5°	1067.3	1053.5	1051.3	1045.3	1046.3
40°	1023.7	1012.0	1007.8	1003.8	1003.8
42.5°	978.0	967.4	963.2	960.2	959.2
45°	908.2	900.4	896.3	893.6	892.3
47.5°	839.2	831.9	828.3	826.4	825.1
50°	791.4	786.2	784.7	780.7	779.4
52.5°	743.6	740.4	739.0	734.0	732.7
55°	673.2	671.9	673.2	663.9	662.6
57.5°	599.9	602.0	606.3	593.7	590.6
60°	551.0	556.2	561.7	546.9	541.7
62.5°	501.1	509.4	517.0	500.1	492.9
65°	426.2	439.2	447.5	429.9	415.6
67.5°	354.0	370.1	380.0	361.1	345.0
70°	304.1	322.2	333.3	314.3	296.1
72.5°	260.5	280.8	289.7	271.8	253.6
75°	196.5	214.7	225.7	210.7	191.2
77.5°	139.4	156.6	165.7	152.6	136.5
80°	102.2	120.4	127.5	116.5	103.6
82.5°	72.5	87.6	92.4	85.8	77.0
85°	33.2	43.6	49.1	46.4	43.8
87.5°	8.8	16.4	21.4	21.6	22.8
90°	1.6	3.1	6.3	7.1	7.9
92.5°	14.2	58.8	105.1	38.4	29.9
95°	33.8	124.6	417.9	171.8	111.8
97.5°	56.0	139.6	619.1	476.6	345.2
100°	72.4	148.6	693.4	698.3	567.4
102.5°	88.1	158.8	707.8	862.7	738.7
105°	113.3	174.9	699.7	1068.1	1005.8
107.5°	140.1	194.9	660.6	1167.2	1190.0
110°	159.0	208.2	630.4	1188.5	1262.4

TEST NUMBER: P564990

CATALOG NUMBER: SQ4-PW1-100U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.0	223.4	602.1	1171.7	1280.6
115°	203.0	245.4	563.5	1115.5	1268.7
117.5°	226.7	268.8	538.2	1036.5	1210.7
120°	242.4	284.0	528.1	983.0	1158.5
122.5°	257.5	297.2	519.9	933.1	1099.3
125°	278.6	317.1	510.8	864.4	1014.5
127.5°	296.5	335.0	505.4	806.3	935.8
130°	308.5	347.0	502.9	770.8	888.5
132.5°	319.8	356.5	500.4	741.0	847.6
135°	335.3	371.4	496.6	700.1	789.4
137.5°	352.6	385.5	494.7	665.8	742.0
140°	362.0	394.3	493.5	642.9	709.9
142.5°	372.7	402.6	492.2	622.6	681.6
145°	388.8	415.7	490.3	596.0	641.4
147.5°	404.2	427.8	488.6	573.6	608.8
150°	415.5	434.8	487.9	560.2	588.7
152.5°	424.4	442.4	487.3	548.8	572.3
155°	438.4	453.0	486.4	534.8	551.7
157.5°	451.3	462.5	486.5	524.6	536.1
160°	458.8	468.8	487.2	518.8	527.3
162.5°	465.1	473.9	487.8	513.8	520.4
165°	474.6	480.7	488.7	507.7	511.6
167.5°	481.8	485.5	489.5	504.0	505.3
170°	485.6	488.7	489.5	502.1	502.1
172.5°	488.7	490.6	489.5	499.6	499.0
175°	491.9	492.7	489.5	496.6	495.0
177.5°	493.1	492.5	489.4	493.7	492.5
180°	491.9	491.9	491.9	491.9	491.9

(END OF REPORT)