

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P565110

Luminaire Tested: **SQ4-PW1-150U-050D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P565110  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-150U-050D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6329.4 lumens  
Efficiency: N/A  
Efficacy: 113.6 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 55.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P565110  
CATALOG NUMBER: SQ4-PW1-150U-050D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P565110

CATALOG NUMBER: SQ4-PW1-150U-050D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	57	44	43	42	29	28	27	21
2	84	77	71	66	74	68	64	59	53	50	47	39	37	35	25	24	23	17
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	22	21	20	15
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	9
8	50	38	31	26	45	35	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5563	5563	5563
5°	5599	5555	5531
10°	5555	5510	5481
15°	5496	5435	5415
20°	5431	5347	5336
25°	5355	5257	5241
30°	5242	5162	5129
35°	5092	5021	4991
40°	4933	4857	4838
45°	4742	4679	4658
50°	4546	4507	4477
55°	4333	4333	4264
60°	4069	4146	4000
65°	3722	3908	3631
70°	3283	3599	3197
75°	2802	3219	2727
80°	2173	2710	2200
85°	1408	2085	1853



TEST NUMBER: P565110

CATALOG NUMBER: SQ4-PW1-150U-050D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.8	0.9
10°-20°	160.3	2.5
20°-30°	237.8	3.8
30°-40°	278.3	4.4
40°-50°	277.0	4.4
50°-60°	239.2	3.8
60°-70°	172.2	2.7
70°-80°	90.3	1.4
80°-90°	23.9	0.4
90°-100°	345.5	5.5
100°-110°	934.2	14.8
110°-120°	982.2	15.5
120°-130°	797.8	12.6
130°-140°	625.8	9.9
140°-150°	480.3	7.6
150°-160°	345.4	5.5
160°-170°	211.0	3.3
170°-180°	71.1	1.1
0°-30°	454.9	7.2
0°-40°	733.2	11.6
0°-60°	1249.4	19.7
0°-90°	1535.8	24.3
90°-120°	2262.0	35.7
90°-150°	4166.0	65.8
90°-180°	4794.0	75.7
0°-180°	6329.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	603	603	603	603	603	
5°	605	598	600	598	597	57
15°	575	568	569	568	567	162
25°	526	517	516	513	515	242
35°	452	446	446	442	443	283
45°	363	360	359	358	357	280
55°	269	269	269	266	265	240
65°	170	176	179	172	166	169
75°	79	86	90	84	76	84
85°	13	17	20	19	18	18
90°	2	5	10	11	10	4
95°	54	188	575	297	177	56
105°	174	268	1036	1529	1466	183
115°	306	374	860	1664	1878	302
125°	419	480	775	1307	1536	373
135°	502	561	754	1056	1195	388
145°	583	627	744	904	972	365
155°	659	684	737	810	837	304
165°	717	724	740	769	773	202
175°	744	744	741	751	749	71
180°	744	744	744	744	744	

TEST NUMBER: P565110

CATALOG NUMBER: SQ4-PW1-150U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	603.0	603.0	603.0	603.0	603.0
2.5°	606.4	601.4	603.0	601.7	598.8
5°	604.6	597.9	599.8	598.2	597.2
7.5°	598.5	592.2	593.7	592.0	591.3
10°	592.9	586.7	588.1	586.0	585.0
12.5°	586.6	579.9	581.3	579.2	578.6
15°	575.4	568.1	569.0	567.9	566.9
17.5°	562.4	555.1	555.2	553.5	553.3
20°	553.1	545.3	544.6	542.5	543.5
22.5°	542.9	534.7	534.0	531.0	532.5
25°	526.0	517.2	516.4	513.3	514.8
27.5°	506.4	497.7	497.7	493.3	495.0
30°	492.0	483.7	484.5	479.3	481.4
32.5°	476.7	469.2	469.7	464.4	466.5
35°	452.1	445.9	445.8	441.5	443.1
37.5°	427.1	421.6	420.7	418.2	418.7
40°	409.6	405.0	403.3	401.7	401.7
42.5°	391.4	387.1	385.4	384.2	383.8
45°	363.4	360.3	358.6	357.6	357.0
47.5°	335.8	332.9	331.4	330.7	330.1
50°	316.7	314.6	314.0	312.4	311.9
52.5°	297.5	296.3	295.7	293.7	293.2
55°	269.4	268.8	269.4	265.6	265.1
57.5°	240.0	240.9	242.6	237.6	236.3
60°	220.5	222.6	224.7	218.8	216.8
62.5°	200.5	203.8	206.9	200.1	197.2
65°	170.5	175.7	179.0	172.0	166.3
67.5°	141.6	148.1	152.1	144.5	138.0
70°	121.7	128.9	133.4	125.8	118.5
72.5°	104.2	112.3	115.9	108.8	101.5
75°	78.6	85.9	90.3	84.3	76.5
77.5°	55.8	62.6	66.3	61.1	54.6
80°	40.9	48.2	51.0	46.6	41.4
82.5°	29.0	35.0	37.0	34.3	30.8
85°	13.3	17.4	19.7	18.6	17.5
87.5°	3.7	7.3	10.2	10.3	10.6
90°	1.6	4.7	10.4	11.2	10.4
92.5°	22.7	82.8	163.4	70.9	51.4
95°	53.6	188.2	574.6	297.4	176.9
97.5°	86.1	215.9	895.7	741.3	544.4
100°	110.4	227.0	995.6	1038.3	839.5
102.5°	132.9	242.6	1030.8	1263.5	1114.8
105°	173.7	268.4	1036.4	1528.8	1466.2
107.5°	211.4	297.8	991.1	1694.3	1715.1
110°	240.9	319.1	950.8	1738.7	1827.1



TEST NUMBER: P565110

CATALOG NUMBER: SQ4-PW1-150U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	267.1	340.4	913.6	1729.8	1878.3
115°	305.7	373.8	859.5	1663.9	1878.3
117.5°	343.5	407.4	823.8	1563.3	1806.3
120°	366.5	429.1	802.7	1491.0	1739.1
122.5°	388.3	449.7	789.9	1413.6	1663.5
125°	418.6	479.6	774.7	1307.3	1535.8
127.5°	446.4	506.4	765.7	1220.6	1421.5
130°	461.8	523.6	761.9	1167.0	1348.5
132.5°	477.8	539.0	758.1	1118.6	1285.8
135°	501.8	561.3	753.9	1055.6	1194.9
137.5°	526.0	582.2	750.4	1004.4	1117.9
140°	542.6	595.0	749.1	971.5	1072.4
142.5°	558.6	607.9	746.5	941.7	1030.2
145°	583.4	627.3	743.5	903.5	972.4
147.5°	606.0	644.8	740.0	868.9	921.8
150°	622.6	657.1	738.7	850.1	892.4
152.5°	638.0	668.1	738.1	832.6	867.4
155°	658.7	684.5	737.1	810.5	837.1
157.5°	680.1	698.1	737.3	795.1	812.6
160°	692.3	707.1	737.9	785.4	797.9
162.5°	701.9	714.2	738.5	777.6	787.0
165°	717.1	724.1	740.3	769.2	773.1
167.5°	727.5	732.3	740.5	761.9	763.8
170°	733.9	736.2	741.1	758.7	758.7
172.5°	739.0	739.5	741.1	754.8	754.2
175°	744.3	743.5	741.1	750.7	749.1
177.5°	746.1	744.2	740.9	747.3	745.4
180°	743.5	743.5	743.5	743.5	743.5

(END OF REPORT)