

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936252

Luminaire Tested: SQ4-FB-025U-050D-930-1D-UNV-STD-W-8

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P936252  
REPORT IS A COMBINATION OF REPORTS P933453 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-025U-050D-930-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4145.9 lumens  
Efficiency: N/A  
Efficacy: 94.2 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P936252  
CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P936252

CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	68	68	68	63
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56	59	57	56	51
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46	51	48	46	42
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38	44	41	38	34
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32	39	35	32	29
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	35	31	28	35	31	28	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24	31	27	24	21
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21	28	24	21	18
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18	26	22	18	16
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16	24	19	16	14
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15	22	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1554	1554	1554
5°	1518	1796	2089
10°	1377	2619	3463
15°	1170	3421	4182
20°	953	3964	4262
25°	795	4148	4175
30°	670	4175	4168
35°	592	4105	4275
40°	517	4015	4386
45°	468	3949	4404
50°	429	3890	4331
55°	411	3803	4139
60°	421	3636	3835
65°	438	3382	3419
70°	467	2949	2889
75°	517	2405	2254
80°	564	1667	1519
85°	503	884	778

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 4404 cd/sqm



TEST NUMBER: P936252

CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	43.3	1.0
10°-20°	192.0	4.6
20°-30°	335.9	8.1
30°-40°	432.4	10.4
40°-50°	483.0	11.6
50°-60°	462.6	11.2
60°-70°	366.6	8.8
70°-80°	215.6	5.2
80°-90°	60.8	1.5
90°-100°	116.8	2.8
100°-110°	307.2	7.4
110°-120°	318.5	7.7
120°-130°	255.5	6.2
130°-140°	200.4	4.8
140°-150°	153.9	3.7
150°-160°	110.8	2.7
160°-170°	67.8	1.6
170°-180°	22.9	0.6
0°-30°	571.3	13.8
0°-40°	1003.7	24.2
0°-60°	1949.2	47.0
0°-90°	2592.2	62.5
90°-120°	742.5	17.9
90°-150°	1352.2	32.6
90°-180°	1554.0	37.5
0°-180°	4145.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	335	335	335	335	335	
5°	326	350	394	446	462	30
15°	244	451	760	922	951	68
25°	156	512	906	946	947	72
35°	106	489	853	902	937	66
45°	72	390	754	864	903	56
55°	52	248	640	743	764	47
65°	41	131	475	534	542	41
75°	30	81	261	286	288	32
85°	11	25	65	71	72	11
90°	2	4	12	6	6	2
95°	15	60	201	104	71	17
105°	55	84	340	516	481	59
115°	98	119	272	543	619	97
125°	137	153	247	418	493	121
135°	163	179	240	338	383	126
145°	189	201	237	288	310	118
155°	214	220	237	260	267	98
165°	230	234	237	246	249	65
175°	240	240	238	241	241	23
180°	240	240	240	240	240	



TEST NUMBER: P936252

CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	334.9	334.9	334.9	334.9	334.9	334.9	334.9	334.9	334.9	334.9	334.9
2.5°	334.9	334.9	337.1	338.2	340.3	341.4	343.6	345.8	352.2	353.2	355.4
5°	326.3	330.7	344.6	350.0	365.1	385.6	394.2	408.2	437.3	445.9	451.3
7.5°	313.4	323.1	357.6	366.2	403.9	457.7	480.4	510.5	556.8	579.4	597.8
10°	292.9	313.4	374.8	395.3	456.7	538.5	580.6	622.6	692.5	723.7	735.6
12.5°	270.4	303.7	393.1	421.1	509.4	629.0	679.7	725.9	805.6	847.6	854.1
15°	244.5	289.7	410.3	451.3	565.5	704.4	760.4	817.5	891.8	921.9	929.5
17.5°	221.9	279.0	426.6	469.6	608.5	772.2	829.3	876.7	937.0	957.5	962.9
20°	193.8	261.7	437.3	493.3	653.8	821.8	876.7	913.3	954.3	967.2	969.4
22.5°	173.4	243.4	443.7	501.9	683.9	852.0	898.2	927.4	955.3	959.7	960.7
25°	156.2	222.9	442.7	511.6	709.8	870.3	905.8	927.4	943.5	945.7	945.7
27.5°	140.0	200.3	438.4	513.8	729.2	874.5	902.6	917.7	925.2	929.5	929.5
30°	126.0	178.8	427.6	509.4	737.8	870.3	892.9	900.4	908.0	914.5	917.7
32.5°	115.2	158.4	411.5	500.8	738.8	859.5	875.7	879.9	890.7	905.8	911.2
35°	105.5	137.9	393.1	488.9	732.4	842.3	853.0	857.4	878.9	901.5	909.0
37.5°	95.9	122.8	369.5	468.6	722.7	821.8	829.3	836.9	870.3	897.2	905.8
40°	86.2	109.9	341.4	445.9	707.6	797.1	803.5	815.4	859.5	890.7	899.4
42.5°	78.6	99.1	311.2	422.2	688.3	769.0	778.7	795.9	846.6	879.9	889.6
45°	72.2	88.3	279.0	389.9	663.4	740.0	753.9	777.6	831.5	863.8	872.4
47.5°	65.7	80.8	245.6	356.5	636.5	710.9	729.2	756.1	811.0	842.3	849.8
50°	60.3	73.2	212.2	321.0	607.5	679.7	701.2	729.2	785.2	814.2	824.0
52.5°	56.0	66.8	180.9	285.4	574.1	647.3	672.1	701.2	753.9	782.0	788.4
55°	51.7	61.4	154.0	247.7	539.6	612.8	639.8	667.8	719.5	743.2	747.5
57.5°	49.5	57.1	131.4	212.2	503.0	574.1	604.3	630.1	678.5	696.8	701.2
60°	46.3	53.9	114.2	182.0	463.2	537.4	563.3	589.2	630.1	645.1	648.4
62.5°	43.1	51.7	101.3	153.0	422.2	494.4	520.2	544.0	578.4	589.2	593.5
65°	41.0	49.5	91.5	131.4	380.2	449.1	475.0	495.5	523.5	534.2	536.4
67.5°	38.8	47.4	84.0	113.1	338.2	403.9	423.3	442.7	464.2	475.0	476.0
70°	35.6	45.2	77.6	100.1	295.1	352.2	368.3	388.8	406.1	411.5	414.7
72.5°	33.4	42.0	73.2	90.5	250.9	302.7	317.7	329.6	344.6	350.0	350.0
75°	30.2	37.7	68.9	80.8	205.7	247.7	260.7	272.5	284.3	286.5	283.3
77.5°	26.9	33.4	59.3	67.9	160.5	196.0	206.8	213.3	222.9	225.1	226.2
80°	22.6	29.1	46.3	52.8	116.4	144.3	151.8	157.2	165.9	165.9	168.0
82.5°	17.3	22.6	33.4	37.7	78.6	99.1	105.5	108.8	114.2	114.2	114.2
85°	10.8	14.0	21.5	24.7	47.4	60.3	64.6	65.7	70.0	71.1	71.1
87.5°	5.4	7.5	14.0	15.1	24.7	31.2	31.2	33.4	33.4	32.3	31.2
90°	1.6	2.9	4.2	4.5	7.1	10.5	12.2	10.8	8.1	6.1	6.1
92.5°	6.4	17.3	28.3	31.1	43.7	60.5	68.8	60.3	43.4	30.6	29.4
95°	15.4	35.4	55.5	60.5	107.4	169.9	201.2	179.6	136.3	103.7	100.1
97.5°	26.7	44.4	62.0	66.4	144.6	248.9	301.1	287.5	260.1	239.5	232.5
100°	35.4	51.4	67.4	71.4	158.2	273.9	331.8	332.8	334.9	336.4	328.0
102.5°	42.8	57.7	72.7	76.4	164.5	281.9	340.6	358.0	392.8	419.0	411.9
105°	55.3	68.0	80.7	83.8	169.1	282.7	339.6	378.7	456.9	515.5	511.7
107.5°	68.2	80.0	91.8	94.8	169.9	270.1	320.2	374.8	483.9	565.7	566.7
110°	76.9	87.5	98.2	100.9	168.6	259.0	304.2	365.1	487.1	578.6	582.6



TEST NUMBER: P936252

CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	85.4	95.6	105.7	108.2	168.7	249.3	289.6	352.0	476.7	570.4	576.6
115°	98.3	107.6	117.0	119.3	170.2	238.1	272.0	332.1	452.4	542.6	551.1
117.5°	111.0	119.5	128.0	130.2	173.4	231.1	259.9	314.2	422.7	504.1	513.6
120°	118.4	126.4	134.4	136.4	176.0	228.8	255.1	304.7	403.8	478.2	487.3
122.5°	125.6	133.7	141.8	143.8	179.7	227.5	251.4	296.1	385.4	452.3	461.4
125°	136.8	144.1	151.4	153.3	184.7	226.5	247.4	285.3	361.2	418.0	426.4
127.5°	145.7	153.1	160.6	162.4	189.7	225.9	244.0	276.6	341.8	390.6	397.6
130°	150.6	158.6	166.5	168.5	193.3	226.3	242.7	271.7	329.7	373.2	379.7
132.5°	155.5	163.6	171.5	173.5	196.3	226.5	241.6	267.6	319.4	358.4	364.2
135°	162.9	170.2	177.5	179.4	199.5	226.3	239.7	261.5	304.9	337.5	342.5
137.5°	170.5	177.7	184.9	186.8	204.3	227.7	239.4	257.8	294.5	322.0	326.1
140°	176.7	183.4	190.1	191.8	207.3	227.9	238.3	254.1	285.9	309.6	313.5
142.5°	181.6	187.7	193.9	195.5	209.7	228.8	238.3	252.2	280.1	301.0	304.3
145°	189.0	194.4	199.7	201.1	213.0	228.8	236.6	248.0	270.9	288.0	290.4
147.5°	196.4	201.6	206.9	208.1	217.6	230.3	236.6	245.6	263.5	277.0	279.0
150°	201.2	206.0	210.6	211.8	220.1	231.1	236.6	244.2	259.4	270.7	272.4
152.5°	206.2	209.7	213.4	214.2	221.7	231.7	236.6	243.1	256.0	265.7	267.0
155°	213.6	216.2	218.9	219.5	225.2	232.9	236.6	241.8	252.1	259.8	260.6
157.5°	219.1	221.6	224.2	224.8	228.8	234.0	236.6	240.7	248.6	254.6	255.2
160°	222.8	224.8	226.8	227.2	230.4	234.6	236.6	240.1	246.9	252.1	252.4
162.5°	226.4	228.0	229.4	229.8	232.1	235.1	236.6	239.5	245.3	249.7	250.0
165°	230.5	231.9	233.3	233.6	234.6	236.0	236.6	238.7	242.8	246.0	246.3
167.5°	234.2	234.9	235.5	235.7	236.6	237.7	238.3	239.6	242.3	244.4	244.5
170°	236.6	237.3	237.9	238.1	238.2	238.3	238.3	239.6	242.3	244.4	244.4
172.5°	237.9	238.1	238.3	238.3	238.3	238.3	238.3	239.3	241.5	243.1	242.9
175°	239.7	239.7	239.7	239.7	239.2	238.6	238.3	238.9	240.3	241.3	241.3
177.5°	239.7	239.7	239.7	239.7	239.3	238.8	238.6	239.1	240.2	241.0	240.8
180°	239.7	239.7	239.7	239.7	239.7	239.7	239.7	239.7	239.7	239.7	239.7



TEST NUMBER: P936252

CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	334.9	334.9
2.5°	357.6	355.4
5°	459.9	462.0
7.5°	619.3	618.2
10°	770.1	779.8
12.5°	879.9	882.1
15°	946.7	951.1
17.5°	972.6	973.6
20°	973.6	971.5
22.5°	961.8	959.7
25°	947.8	946.7
27.5°	934.9	936.0
30°	929.5	932.8
32.5°	929.5	934.9
35°	931.6	937.0
37.5°	930.6	937.0
40°	926.3	933.8
42.5°	914.5	919.8
45°	896.1	902.6
47.5°	872.4	876.7
50°	842.3	846.6
52.5°	804.5	805.6
55°	759.3	763.7
57.5°	710.9	711.9
60°	657.0	660.2
62.5°	599.9	599.9
65°	539.6	541.8
67.5°	477.1	482.5
70°	413.6	414.7
72.5°	351.2	351.2
75°	286.5	287.6
77.5°	225.1	225.1
80°	166.9	168.0
82.5°	115.2	117.4
85°	72.2	72.2
87.5°	33.4	30.2
90°	6.1	6.1
92.5°	24.5	19.6
95°	85.4	70.6
97.5°	204.4	176.4
100°	294.6	261.2
102.5°	383.3	354.7
105°	496.3	480.9
107.5°	570.4	574.1
110°	598.6	614.6





TEST NUMBER: P936252

CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	601.1	625.7
115°	585.2	619.3
117.5°	551.4	589.2
120°	524.1	560.9
122.5°	497.6	533.8
125°	459.8	493.2
127.5°	425.8	453.9
130°	405.7	431.7
132.5°	387.5	410.8
135°	362.6	382.6
137.5°	342.6	359.0
140°	328.8	344.2
142.5°	317.5	330.7
145°	300.5	310.4
147.5°	287.3	295.7
150°	279.1	285.9
152.5°	272.1	277.1
155°	263.9	267.3
157.5°	257.6	259.9
160°	253.7	255.1
162.5°	251.3	252.5
165°	247.6	249.0
167.5°	245.1	245.6
170°	244.4	244.4
172.5°	242.4	241.9
175°	241.3	241.3
177.5°	240.3	239.7
180°	239.7	239.7



TEST NUMBER: P936252  
 CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-8

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.60	4.64	4.44	5.50	6.58	16.78	17.82	17.61	18.68	19.76
	3H	4.32	5.26	5.17	6.13	7.23	18.63	19.57	19.48	20.44	21.54
	4H	4.63	5.51	5.49	6.39	7.50	19.29	20.17	20.15	21.05	22.16
	6H	4.89	5.70	5.76	6.59	7.72	19.73	20.54	20.60	21.43	22.56
	8H	4.96	5.74	5.84	6.64	7.77	19.85	20.63	20.74	21.54	22.66
	12H	4.98	5.73	5.87	6.63	7.78	19.93	20.67	20.82	21.57	22.72
4H	2H	10.84	11.72	11.70	12.60	13.72	17.08	17.96	17.94	18.84	19.95
	3H	12.42	13.16	13.30	14.07	15.20	19.14	19.88	20.02	20.79	21.92
	4H	12.52	13.20	13.42	14.11	15.26	19.91	20.59	20.80	21.50	22.65
	6H	12.55	13.13	13.45	14.06	15.22	20.46	21.05	21.37	21.98	23.14
	8H	12.53	13.08	13.44	14.00	15.17	20.63	21.18	21.54	22.10	23.27
	12H	12.49	12.99	13.42	13.93	15.11	20.73	21.23	21.66	22.17	23.35
8H	4H	13.99	14.53	14.89	15.46	16.63	19.99	20.54	20.90	21.46	22.63
	6H	14.24	14.69	15.17	15.66	16.83	20.63	21.08	21.56	22.05	23.22
	8H	14.26	14.66	15.20	15.62	16.81	20.85	21.25	21.79	22.21	23.40
	12H	14.23	14.59	15.18	15.54	16.78	21.00	21.36	21.95	22.31	23.55
12H	4H	14.14	14.63	15.07	15.58	16.75	19.95	20.45	20.88	21.39	22.57
	6H	14.50	14.90	15.44	15.86	17.05	20.61	21.02	21.56	21.97	23.16
	8H	14.57	14.93	15.52	15.88	17.12	20.85	21.21	21.80	22.16	23.39