

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519512

Luminaire Tested: **SQ4-WB-125U-100D-930-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519512
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-100D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6598.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 64.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519512
CATALOG NUMBER: SQ4-WB-125U-100D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519512

CATALOG NUMBER: SQ4-WB-125U-100D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	89	86	88	84	81	79	69	67	65	55	54	53	43	42	41	35
2	88	82	76	72	80	75	70	66	62	59	56	50	48	46	39	37	36	31
3	81	73	66	61	74	67	61	56	55	51	48	45	42	40	35	33	32	27
4	75	65	58	52	68	60	54	49	50	45	42	41	37	35	32	30	28	24
5	69	58	51	45	63	54	47	42	45	40	37	37	34	31	29	27	25	22
6	64	53	45	40	58	49	42	37	41	36	32	34	30	28	27	25	23	20
7	59	48	40	35	54	44	38	33	37	33	29	31	27	25	25	23	21	18
8	55	44	36	32	50	40	34	30	34	29	26	29	25	22	23	21	19	16
9	52	40	33	28	47	37	31	27	32	27	24	26	23	20	22	19	17	15
10	48	37	30	26	44	34	28	24	29	25	21	25	21	19	20	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16579	16579	16579
5°	16371	16313	16408
10°	15467	15608	15970
15°	14279	14610	15265
20°	12966	13454	14345
25°	11630	12264	13364
30°	10399	11080	12347
35°	9094	9750	11145
40°	7654	8261	9648
45°	6316	6862	8054
50°	5273	5749	6710
55°	4477	4933	5541
60°	3827	4277	4423
65°	3048	3598	2858
70°	2700	2808	1745
75°	2502	2278	1069
80°	2306	2093	919
85°	2085	1916	752



TEST NUMBER: P519512

CATALOG NUMBER: SQ4-WB-125U-100D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.8	2.5
10°-20°	428.7	6.5
20°-30°	555.3	8.4
30°-40°	543.8	8.2
40°-50°	416.2	6.3
50°-60°	277.3	4.2
60°-70°	151.3	2.3
70°-80°	63.1	1.0
80°-90°	19.3	0.3
90°-100°	288.3	4.4
100°-110°	776.6	11.8
110°-120°	815.0	12.4
120°-130°	661.3	10.0
130°-140°	518.7	7.9
140°-150°	398.2	6.0
150°-160°	286.3	4.3
160°-170°	174.9	2.7
170°-180°	59.0	0.9
0°-30°	1148.8	17.4
0°-40°	1692.5	25.7
0°-60°	2386.1	36.2
0°-90°	2619.8	39.7
90°-120°	1879.8	28.5
90°-150°	3458.0	52.4
90°-180°	3978.0	60.3
0°-180°	6598.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1797	1797	1797	1797	1797	
5°	1768	1750	1761	1766	1772	164
15°	1495	1490	1530	1571	1598	417
25°	1142	1146	1205	1257	1313	525
35°	807	811	866	924	990	502
45°	484	493	526	566	617	378
55°	278	290	307	318	344	252
65°	140	151	165	144	131	145
75°	70	70	64	44	30	75
85°	20	20	18	12	7	21
90°	2	5	9	10	10	4
95°	44	157	473	242	167	46
105°	144	224	859	1285	1206	151
115°	254	310	715	1382	1563	250
125°	346	398	642	1085	1277	309
135°	417	465	624	876	992	322
145°	482	520	616	749	804	302
155°	547	567	611	672	693	252
165°	594	600	613	638	641	167
175°	617	616	614	622	621	59
180°	616	616	616	616	616	

TEST NUMBER: P519512

CATALOG NUMBER: SQ4-WB-125U-100D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1796.9	1796.9	1796.9	1796.9	1796.9
2.5°	1801.3	1785.2	1789.3	1789.2	1784.2
5°	1767.7	1749.9	1761.4	1765.5	1771.6
7.5°	1702.1	1688.7	1709.5	1724.9	1737.4
10°	1651.0	1639.4	1666.0	1688.4	1704.6
12.5°	1591.7	1582.0	1614.9	1645.0	1666.1
15°	1494.9	1489.5	1529.6	1571.2	1598.2
17.5°	1391.3	1388.7	1434.6	1483.2	1517.7
20°	1320.6	1319.9	1370.3	1420.9	1461.0
22.5°	1249.4	1251.1	1304.1	1356.7	1402.3
25°	1142.4	1145.5	1204.7	1257.2	1312.8
27.5°	1043.6	1045.0	1106.2	1161.6	1220.8
30°	976.1	979.9	1040.0	1097.3	1159.0
32.5°	908.6	913.1	971.8	1031.1	1094.0
35°	807.4	811.2	865.7	924.0	989.5
37.5°	703.0	708.2	756.6	811.7	876.1
40°	635.5	643.2	685.9	737.8	801.1
42.5°	570.5	580.1	619.7	668.9	726.0
45°	484.1	493.4	525.9	565.7	617.3
47.5°	409.7	420.3	445.3	479.6	523.7
50°	367.4	377.4	400.5	425.9	467.5
52.5°	330.2	340.2	360.8	380.4	415.8
55°	278.3	289.9	306.7	318.3	344.5
57.5°	235.7	246.8	260.2	265.4	281.3
60°	207.4	219.7	231.8	231.2	239.7
62.5°	181.5	192.0	204.0	195.7	196.2
65°	139.6	151.1	164.8	144.0	130.9
67.5°	112.7	115.2	129.3	100.4	84.8
70°	100.1	100.1	104.1	77.8	64.7
72.5°	88.1	88.1	84.5	63.2	49.5
75°	70.2	70.2	63.9	43.8	30.0
77.5°	54.1	53.5	48.9	32.7	21.8
80°	43.4	43.4	39.4	25.8	17.3
82.5°	33.9	33.9	30.6	20.2	12.9
85°	19.7	19.7	18.1	11.7	7.1
87.5°	7.3	7.9	8.2	5.8	5.2
90°	1.6	4.6	9.4	10.2	10.2
92.5°	19.2	67.7	133.8	64.4	44.7
95°	44.0	156.8	472.6	241.7	167.2
97.5°	70.2	179.5	741.2	619.2	466.9
100°	90.3	188.5	826.6	864.9	717.5
102.5°	109.7	201.2	854.9	1048.9	927.9
105°	143.7	223.5	858.8	1284.9	1205.8
107.5°	175.7	246.9	822.2	1406.1	1426.6
110°	197.0	264.6	789.0	1443.8	1518.2



TEST NUMBER: P519512

CATALOG NUMBER: SQ4-WB-125U-100D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	219.7	282.3	756.9	1435.5	1557.8
115°	253.6	310.4	715.2	1381.8	1563.0
117.5°	284.5	337.8	682.8	1296.3	1498.0
120°	304.6	356.0	666.5	1234.8	1442.1
122.5°	322.2	373.0	654.6	1172.0	1378.7
125°	346.2	397.6	642.2	1085.3	1277.2
127.5°	369.3	419.9	634.3	1008.9	1180.2
130°	383.1	433.8	631.2	965.1	1115.5
132.5°	396.9	447.0	628.0	926.5	1064.7
135°	416.9	465.2	624.1	875.6	991.5
137.5°	435.8	482.2	622.1	832.4	927.6
140°	449.0	493.6	620.2	805.8	891.8
142.5°	462.9	504.3	618.9	781.0	853.5
145°	482.0	519.6	616.2	748.6	803.9
147.5°	502.7	535.4	613.6	721.3	764.8
150°	516.5	544.9	612.3	704.2	740.3
152.5°	529.1	553.8	611.7	690.2	719.6
155°	547.2	567.1	610.8	671.7	693.2
157.5°	563.0	578.5	610.9	658.7	673.1
160°	573.1	586.1	611.5	651.0	661.8
162.5°	581.9	592.5	612.2	644.7	652.4
165°	593.5	600.4	613.1	637.5	640.6
167.5°	602.9	606.9	613.9	632.0	633.2
170°	609.2	610.7	613.9	628.8	628.8
172.5°	613.0	613.3	614.5	625.7	625.7
175°	617.0	616.3	613.9	622.5	621.0
177.5°	618.8	617.5	614.4	619.4	618.1
180°	616.2	616.2	616.2	616.2	616.2

(END OF REPORT)