

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937552

Luminaire Tested: SQ4-FB-100U-075D-930-1D-UNV-STD-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937552
REPORT IS A COMBINATION OF REPORTS P933582 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-075D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10320.2 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 98.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937552
CATALOG NUMBER: SQ4-FB-100U-075D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P937552

CATALOG NUMBER: SQ4-FB-100U-075D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37				37
1	95	90	86	83	86	82	78	75	66	64	62	52	50	49	39	38	37	31				31
2	86	78	72	67	77	71	66	61	58	54	50	45	42	40	34	32	30	25				25
3	78	68	61	55	70	62	56	50	50	46	42	39	36	33	29	27	25	21				21
4	71	60	52	46	64	55	48	42	44	39	35	35	31	28	26	23	21	17				17
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18	15				15
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13				13
7	55	42	34	29	49	39	32	27	32	26	22	25	21	18	19	16	14	11				11
8	51	38	31	25	46	35	28	23	29	23	20	23	19	16	17	14	12	10				10
9	47	35	27	22	42	32	25	21	26	21	17	21	17	14	16	13	11	9				9
10	44	32	24	20	40	29	23	18	24	19	15	19	15	12	14	12	10	8				8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2317	2317	2317
5°	2264	2678	3115
10°	2053	3904	5164
15°	1745	5101	6236
20°	1421	5911	6355
25°	1185	6186	6226
30°	999	6225	6214
35°	884	6121	6375
40°	770	5988	6541
45°	697	5889	6567
50°	639	5800	6458
55°	613	5671	6172
60°	628	5421	5720
65°	652	5043	5098
70°	695	4398	4307
75°	771	3586	3361
80°	841	2486	2264
85°	750	1320	1159

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 6567 cd/sqm



TEST NUMBER: P937552

CATALOG NUMBER: SQ4-FB-100U-075D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.6	0.6
10°-20°	286.4	2.8
20°-30°	500.9	4.9
30°-40°	644.8	6.2
40°-50°	720.2	7.0
50°-60°	689.8	6.7
60°-70°	546.6	5.3
70°-80°	321.4	3.1
80°-90°	93.1	0.9
90°-100°	485.2	4.7
100°-110°	1275.5	12.4
110°-120°	1322.6	12.8
120°-130°	1060.9	10.3
130°-140°	832.4	8.1
140°-150°	638.9	6.2
150°-160°	460.1	4.5
160°-170°	281.5	2.7
170°-180°	95.1	0.9
0°-30°	851.9	8.3
0°-40°	1496.7	14.5
0°-60°	2906.7	28.2
0°-90°	3867.8	37.5
90°-120°	3083.3	29.9
90°-150°	5615.6	54.4
90°-180°	6452.0	62.5
0°-180°	10320.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	500	500	500	500	500	
5°	487	522	588	665	689	45
15°	365	673	1134	1375	1418	101
25°	233	763	1351	1410	1412	107
35°	157	729	1272	1344	1397	98
45°	108	581	1124	1288	1346	83
55°	77	369	954	1108	1139	70
65°	61	196	708	797	808	60
75°	45	120	389	427	429	47
85°	16	37	96	106	108	17
90°	7	19	51	25	25	7
95°	64	251	836	431	293	71
105°	230	348	1410	2141	1997	244
115°	408	496	1130	2253	2572	403
125°	568	637	1027	1736	2048	504
135°	677	745	995	1402	1589	524
145°	785	835	983	1196	1289	492
155°	887	912	983	1079	1110	408
165°	957	970	983	1021	1034	270
175°	995	995	989	1002	1002	94
180°	995	995	995	995	995	



TEST NUMBER: P937552

CATALOG NUMBER: SQ4-FB-100U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	499.5	499.5	499.5	499.5	499.5	499.5	499.5	499.5	499.5	499.5	499.5
2.5°	499.5	499.5	502.7	504.3	507.5	509.1	512.3	515.5	525.2	526.8	530.0
5°	486.6	493.0	513.9	522.0	544.4	574.9	587.8	608.7	652.0	664.9	672.9
7.5°	467.3	481.8	533.2	546.0	602.2	682.6	716.3	761.2	830.3	864.0	891.3
10°	436.8	467.3	558.9	589.4	680.9	803.0	865.6	928.3	1032.7	1079.3	1097.0
12.5°	403.1	452.9	586.2	627.9	759.6	938.0	1013.5	1082.5	1201.4	1264.0	1273.6
15°	364.6	432.0	611.9	672.9	843.2	1050.4	1133.9	1219.0	1329.8	1374.8	1386.1
17.5°	330.8	416.0	636.0	700.2	907.4	1151.6	1236.7	1307.4	1397.3	1427.8	1435.8
20°	289.1	390.3	652.0	735.5	974.9	1225.5	1307.4	1362.0	1423.0	1442.3	1445.5
22.5°	258.6	363.0	661.7	748.4	1019.9	1270.4	1339.5	1382.8	1424.6	1431.0	1432.6
25°	232.9	332.4	660.1	762.8	1058.4	1297.7	1350.7	1382.8	1406.9	1410.1	1410.1
27.5°	208.8	298.7	653.6	766.1	1087.3	1304.2	1345.9	1368.4	1379.6	1386.1	1386.1
30°	187.9	266.6	637.6	759.6	1100.2	1297.7	1331.5	1342.7	1353.9	1363.6	1368.4
32.5°	171.8	236.1	613.5	746.8	1101.8	1281.7	1305.8	1312.2	1328.2	1350.7	1358.8
35°	157.4	205.6	586.2	729.1	1092.2	1256.0	1272.0	1278.5	1310.6	1344.3	1355.5
37.5°	142.9	183.1	550.9	698.6	1077.7	1225.5	1236.7	1247.9	1297.7	1337.9	1350.7
40°	128.5	163.8	509.1	664.9	1055.2	1188.5	1198.2	1215.8	1281.7	1328.2	1341.1
42.5°	117.2	147.8	464.1	629.6	1026.3	1146.8	1161.2	1186.9	1262.4	1312.2	1326.6
45°	107.6	131.7	416.0	581.4	989.4	1103.4	1124.3	1159.6	1239.9	1288.1	1300.9
47.5°	98.0	120.4	366.2	531.6	949.2	1060.0	1087.3	1127.5	1209.4	1256.0	1267.2
50°	89.9	109.2	316.4	478.6	905.8	1013.5	1045.6	1087.3	1170.9	1214.2	1228.7
52.5°	83.5	99.6	269.8	425.6	856.0	965.3	1002.2	1045.6	1124.3	1166.0	1175.7
55°	77.1	91.5	229.7	369.4	804.6	913.9	954.0	995.8	1072.9	1108.2	1114.6
57.5°	73.9	85.1	195.9	316.4	750.0	856.0	901.0	939.6	1011.9	1039.2	1045.6
60°	69.1	80.3	170.2	271.4	690.6	801.4	839.9	878.5	939.6	962.1	966.9
62.5°	64.2	77.1	151.0	228.1	629.6	737.2	775.7	811.0	862.4	878.5	884.9
65°	61.0	73.9	136.5	195.9	566.9	669.7	708.2	738.8	780.5	796.6	799.8
67.5°	57.8	70.7	125.3	168.6	504.3	602.2	631.2	660.1	692.2	708.2	709.9
70°	53.0	67.5	115.6	149.4	440.0	525.2	549.3	579.8	605.5	613.5	618.3
72.5°	49.8	62.6	109.2	134.9	374.2	451.3	473.8	491.4	513.9	522.0	522.0
75°	45.0	56.2	102.8	120.4	306.7	369.4	388.7	406.3	424.0	427.2	422.4
77.5°	40.2	49.8	88.3	101.2	239.3	292.3	308.4	318.0	332.4	335.7	337.3
80°	33.7	43.4	69.1	78.7	173.4	215.2	226.4	234.5	247.3	247.3	250.5
82.5°	25.7	33.7	49.8	56.2	117.2	147.8	157.4	162.2	170.2	170.2	170.2
85°	16.1	20.9	32.1	36.9	70.7	89.9	96.4	98.0	104.4	106.0	106.0
87.5°	8.0	11.2	20.9	22.5	36.9	46.6	46.6	49.8	49.8	48.2	46.6
90°	6.7	12.0	17.3	18.7	29.4	43.6	50.7	45.1	33.8	25.4	25.4
92.5°	26.7	72.2	117.6	129.0	181.2	251.0	285.9	250.5	180.0	127.0	121.9
95°	64.2	147.3	230.4	251.2	446.0	705.8	835.7	745.7	565.8	430.9	415.6
97.5°	110.9	184.2	257.6	275.9	600.8	1033.9	1250.5	1193.7	1080.0	994.7	965.6
100°	146.9	213.4	280.0	296.6	657.1	1137.8	1378.1	1382.3	1390.6	1396.8	1362.1
102.5°	177.7	239.7	301.8	317.3	682.9	1170.4	1414.2	1486.6	1631.5	1740.2	1710.5
105°	229.8	282.3	334.9	348.0	702.1	1174.1	1410.1	1572.5	1897.3	2141.0	2125.0
107.5°	283.2	332.2	381.2	393.5	705.7	1121.9	1330.0	1556.5	2009.6	2349.3	2353.2
110°	319.3	363.5	407.8	418.8	700.3	1075.5	1263.2	1516.5	2022.9	2402.8	2419.4



TEST NUMBER: P937552

CATALOG NUMBER: SQ4-FB-100U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	354.7	396.8	439.1	449.6	700.5	1035.1	1202.4	1461.6	1980.0	2368.8	2394.3
115°	408.2	447.0	486.0	495.7	707.0	988.7	1129.6	1379.3	1878.7	2253.2	2288.6
117.5°	460.9	496.3	531.6	540.4	720.1	959.7	1079.5	1304.8	1755.5	2093.5	2132.8
120°	491.7	524.9	558.2	566.4	730.8	949.9	1059.5	1265.4	1677.1	1986.0	2024.1
122.5°	521.7	555.3	588.8	597.2	746.1	944.7	1044.1	1229.5	1600.3	1878.5	1916.1
125°	567.8	598.4	629.0	636.6	766.9	940.6	1027.4	1184.9	1499.9	1736.2	1770.9
127.5°	605.2	636.1	667.0	674.7	787.6	938.1	1013.4	1148.6	1419.1	1621.9	1651.1
130°	625.2	658.5	691.7	700.1	802.7	939.6	1008.0	1128.4	1369.2	1549.8	1576.8
132.5°	645.9	679.2	712.4	720.8	815.0	940.6	1003.3	1111.1	1326.6	1488.3	1512.5
135°	676.7	707.0	737.3	744.9	828.4	939.7	995.3	1085.6	1266.1	1401.5	1422.4
137.5°	708.1	738.0	768.1	775.5	848.4	945.5	994.0	1070.2	1222.9	1337.3	1354.4
140°	734.1	761.7	789.3	796.3	860.6	946.4	989.3	1055.2	1187.1	1285.9	1301.9
142.5°	754.2	779.7	805.2	811.6	870.9	949.8	989.3	1047.2	1163.0	1249.9	1263.6
145°	784.9	807.2	829.5	835.0	884.3	949.9	982.6	1030.0	1124.7	1195.7	1206.1
147.5°	815.6	837.3	859.0	864.4	903.9	956.4	982.6	1019.9	1094.4	1150.3	1158.9
150°	835.7	855.3	874.9	879.8	914.1	959.7	982.6	1014.1	1077.1	1124.3	1131.3
152.5°	856.4	871.3	886.1	889.8	920.7	962.0	982.6	1009.5	1063.3	1103.6	1108.9
155°	887.1	898.1	909.1	911.8	935.4	966.9	982.6	1004.0	1046.8	1078.8	1082.3
157.5°	909.8	920.5	931.2	933.9	950.1	971.8	982.6	999.3	1032.5	1057.5	1059.9
160°	925.2	933.6	941.8	943.9	956.9	974.0	982.6	996.9	1025.4	1046.8	1048.2
162.5°	940.6	946.8	953.1	954.6	963.9	976.4	982.6	994.7	1018.7	1036.8	1038.1
165°	957.3	962.9	968.5	969.9	974.2	979.8	982.6	991.2	1008.5	1021.4	1022.9
167.5°	972.6	975.2	978.0	978.6	982.1	986.9	989.3	994.9	1006.2	1014.7	1015.2
170°	982.6	985.3	988.0	988.7	988.9	989.1	989.3	994.9	1006.2	1014.7	1014.7
172.5°	988.0	988.6	989.1	989.3	989.3	989.3	989.3	993.8	1002.7	1009.4	1008.9
175°	995.3	995.3	995.3	995.3	993.3	990.7	989.3	992.1	997.7	1002.0	1002.0
177.5°	995.3	995.3	995.3	995.3	993.8	991.7	990.7	992.9	997.3	1000.7	1000.1
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P937552

CATALOG NUMBER: SQ4-FB-100U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	499.5	499.5
2.5°	533.2	530.0
5°	685.8	689.0
7.5°	923.5	921.9
10°	1148.4	1162.8
12.5°	1312.2	1315.4
15°	1411.8	1418.2
17.5°	1450.3	1451.9
20°	1451.9	1448.7
22.5°	1434.2	1431.0
25°	1413.4	1411.8
27.5°	1394.1	1395.7
30°	1386.1	1390.9
32.5°	1386.1	1394.1
35°	1389.3	1397.3
37.5°	1387.7	1397.3
40°	1381.2	1392.5
42.5°	1363.6	1371.6
45°	1336.3	1345.9
47.5°	1300.9	1307.4
50°	1256.0	1262.4
52.5°	1199.8	1201.4
55°	1132.3	1138.7
57.5°	1060.0	1061.6
60°	979.7	984.6
62.5°	894.5	894.5
65°	804.6	807.8
67.5°	711.5	719.5
70°	616.7	618.3
72.5°	523.6	523.6
75°	427.2	428.8
77.5°	335.7	335.7
80°	248.9	250.5
82.5°	171.8	175.1
85°	107.6	107.6
87.5°	49.8	45.0
90°	25.4	25.4
92.5°	101.7	81.5
95°	354.4	293.3
97.5°	849.2	732.8
100°	1223.5	1084.9
102.5°	1591.7	1472.9
105°	2061.1	1997.3
107.5°	2368.7	2384.1
110°	2485.9	2552.4



TEST NUMBER: P937552

CATALOG NUMBER: SQ4-FB-100U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2496.4	2598.5
115°	2430.2	2571.8
117.5°	2289.8	2446.9
120°	2176.8	2329.3
122.5°	2066.6	2217.1
125°	1909.5	2048.1
127.5°	1768.1	1885.1
130°	1684.9	1792.9
132.5°	1609.3	1706.1
135°	1505.8	1589.2
137.5°	1422.7	1491.0
140°	1365.7	1429.5
142.5°	1318.5	1373.5
145°	1247.7	1289.2
147.5°	1193.3	1227.8
150°	1159.1	1187.1
152.5°	1129.9	1150.9
155°	1096.3	1110.2
157.5°	1069.7	1079.5
160°	1053.9	1059.5
162.5°	1043.4	1048.8
165°	1028.5	1034.1
167.5°	1017.6	1020.1
170°	1014.7	1014.7
172.5°	1006.8	1004.7
175°	1002.0	1002.0
177.5°	997.7	995.3
180°	995.3	995.3



TEST NUMBER: P937552
 CATALOG NUMBER: SQ4-FB-100U-075D-930-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.66	3.44	3.71	4.50	5.94	15.84	16.62	16.89	17.68	19.12
	3H	3.36	4.06	4.42	5.13	6.59	17.67	18.38	18.73	19.44	20.90
	4H	3.65	4.32	4.72	5.39	6.85	18.31	18.98	19.38	20.05	21.51
	6H	3.90	4.52	4.98	5.59	7.06	18.74	19.36	19.82	20.43	21.90
	8H	3.96	4.55	5.05	5.64	7.11	18.86	19.44	19.94	20.53	22.00
	12H	3.98	4.54	5.07	5.62	7.11	18.92	19.48	20.01	20.56	22.06
4H	2H	9.86	10.53	10.94	11.60	13.06	16.10	16.77	17.18	17.84	19.30
	3H	11.42	11.98	12.51	13.08	14.56	18.14	18.70	19.23	19.80	21.27
	4H	11.51	12.03	12.61	13.12	14.61	18.90	19.42	20.00	20.51	22.00
	6H	11.52	11.96	12.62	13.07	14.56	19.44	19.88	20.54	20.99	22.48
	8H	11.50	11.91	12.60	13.01	14.52	19.60	20.01	20.70	21.11	22.62
	12H	11.45	11.82	12.57	12.94	14.45	19.69	20.06	20.81	21.18	22.69
8H	4H	12.95	13.37	14.05	14.47	15.98	18.96	19.37	20.06	20.47	21.98
	6H	13.19	13.53	14.31	14.68	16.18	19.58	19.92	20.71	21.07	22.57
	8H	13.21	13.51	14.34	14.63	16.16	19.80	20.10	20.93	21.23	22.75
	12H	13.17	13.44	14.31	14.56	16.12	19.94	20.21	21.08	21.33	22.89
12H	4H	13.09	13.47	14.21	14.58	16.09	18.91	19.28	20.02	20.40	21.91
	6H	13.45	13.75	14.58	14.88	16.40	19.56	19.87	20.69	20.99	22.51
	8H	13.52	13.78	14.65	14.90	16.46	19.79	20.05	20.93	21.18	22.74