

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519584

Luminaire Tested: **SQ4-WB-150U-075D-930-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519584
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-150U-075D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6779.3 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 63.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519584
CATALOG NUMBER: SQ4-WB-150U-075D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519584

CATALOG NUMBER: SQ4-WB-150U-075D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33	26
2	86	79	74	69	77	71	67	63	57	54	51	43	41	39	31	29	28	23
3	79	70	64	58	71	63	58	53	51	47	44	39	36	34	28	26	25	20
4	72	63	55	50	65	57	50	46	45	41	38	35	32	30	25	24	22	18
5	67	56	49	43	60	51	44	40	41	36	33	32	29	26	23	21	20	16
6	62	50	43	38	55	46	39	35	37	32	29	29	26	23	21	19	18	15
7	57	46	38	33	51	42	35	31	34	29	26	26	23	21	20	18	16	13
8	53	41	34	29	48	38	32	27	31	26	23	24	21	19	18	16	15	12
9	49	38	31	26	44	35	29	24	28	24	21	22	19	17	17	15	13	11
10	46	35	28	24	42	32	26	22	26	22	19	21	18	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12562	12562	12562
5°	12406	12361	12433
10°	11721	11827	12101
15°	10820	11071	11568
20°	9826	10195	10870
25°	8813	9293	10127
30°	7880	8396	9357
35°	6891	7389	8445
40°	5800	6260	7311
45°	4786	5200	6104
50°	3996	4356	5085
55°	3392	3738	4200
60°	2899	3242	3351
65°	2310	2727	2166
70°	2047	2128	1322
75°	1896	1725	809
80°	1748	1589	696
85°	1577	1450	572



TEST NUMBER: P519584

CATALOG NUMBER: SQ4-WB-150U-075D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.9	1.8
10°-20°	324.9	4.8
20°-30°	420.8	6.2
30°-40°	412.0	6.1
40°-50°	315.4	4.7
50°-60°	210.2	3.1
60°-70°	114.7	1.7
70°-80°	47.8	0.7
80°-90°	15.1	0.2
90°-100°	345.5	5.1
100°-110°	934.2	13.8
110°-120°	982.2	14.5
120°-130°	797.8	11.8
130°-140°	625.8	9.2
140°-150°	480.3	7.1
150°-160°	345.4	5.1
160°-170°	211.0	3.1
170°-180°	71.1	1.0
0°-30°	870.5	12.8
0°-40°	1282.6	18.9
0°-60°	1808.1	26.7
0°-90°	1985.7	29.3
90°-120°	2262.0	33.4
90°-150°	4166.0	61.5
90°-180°	4794.0	70.7
0°-180°	6779.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1362	1362	1362	1362	1362	
5°	1340	1326	1335	1338	1342	125
15°	1133	1129	1159	1191	1211	316
25°	866	868	913	953	995	398
35°	612	615	656	700	750	380
45°	367	374	398	429	468	286
55°	211	220	232	241	261	191
65°	106	114	125	109	99	110
75°	53	53	48	33	23	57
85°	15	15	14	9	5	16
90°	2	5	10	11	10	4
95°	54	188	575	297	177	56
105°	174	268	1036	1529	1466	183
115°	306	374	860	1664	1878	302
125°	419	480	775	1307	1536	373
135°	502	561	754	1056	1195	388
145°	583	627	744	904	972	365
155°	659	684	737	810	837	304
165°	717	724	740	769	773	202
175°	744	744	741	751	749	71
180°	744	744	744	744	744	



TEST NUMBER: P519584

CATALOG NUMBER: SQ4-WB-150U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1361.6	1361.6	1361.6	1361.6	1361.6
2.5°	1365.0	1352.8	1355.9	1355.8	1352.1
5°	1339.5	1326.1	1334.7	1337.8	1342.5
7.5°	1289.8	1279.6	1295.4	1307.1	1316.6
10°	1251.1	1242.3	1262.4	1279.5	1291.7
12.5°	1206.2	1198.8	1223.7	1246.6	1262.6
15°	1132.8	1128.7	1159.1	1190.6	1211.1
17.5°	1054.3	1052.3	1087.2	1124.0	1150.1
20°	1000.8	1000.2	1038.4	1076.7	1107.1
22.5°	946.7	948.0	988.2	1028.1	1062.7
25°	865.7	868.1	912.9	952.7	994.8
27.5°	790.8	791.9	838.2	880.3	925.1
30°	739.7	742.6	788.1	831.5	878.3
32.5°	688.5	691.9	736.4	781.4	829.0
35°	611.8	614.7	656.0	700.2	749.8
37.5°	532.7	536.7	573.3	615.1	663.9
40°	481.6	487.4	519.8	559.1	607.0
42.5°	432.3	439.6	469.6	506.9	550.1
45°	366.8	373.9	398.5	428.7	467.8
47.5°	310.4	318.5	337.4	363.4	396.8
50°	278.4	286.0	303.5	322.8	354.3
52.5°	250.2	257.8	273.4	288.2	315.1
55°	210.9	219.7	232.4	241.2	261.1
57.5°	178.6	187.1	197.2	201.1	213.2
60°	157.1	166.5	175.7	175.2	181.6
62.5°	137.5	145.5	154.6	148.3	148.6
65°	105.8	114.5	124.9	109.1	99.2
67.5°	85.4	87.3	98.0	76.1	64.3
70°	75.9	75.9	78.9	58.9	49.0
72.5°	66.8	66.8	64.0	47.9	37.5
75°	53.2	53.2	48.4	33.2	22.7
77.5°	41.0	40.5	37.0	24.8	16.5
80°	32.9	32.9	29.9	19.6	13.1
82.5°	25.7	25.7	23.2	15.3	9.8
85°	14.9	14.9	13.7	8.9	5.4
87.5°	5.6	6.2	6.9	5.1	4.5
90°	1.6	4.7	10.4	11.2	10.4
92.5°	22.7	82.8	163.4	70.9	51.4
95°	53.6	188.2	574.6	297.4	176.9
97.5°	86.1	215.9	895.7	741.3	544.4
100°	110.4	227.0	995.6	1038.3	839.5
102.5°	132.9	242.6	1030.8	1263.5	1114.8
105°	173.7	268.4	1036.4	1528.8	1466.2
107.5°	211.4	297.8	991.1	1694.3	1715.1
110°	240.9	319.1	950.8	1738.7	1827.1



TEST NUMBER: P519584

CATALOG NUMBER: SQ4-WB-150U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	267.1	340.4	913.6	1729.8	1878.3
115°	305.7	373.8	859.5	1663.9	1878.3
117.5°	343.5	407.4	823.8	1563.3	1806.3
120°	366.5	429.1	802.7	1491.0	1739.1
122.5°	388.3	449.7	789.9	1413.6	1663.5
125°	418.6	479.6	774.7	1307.3	1535.8
127.5°	446.4	506.4	765.7	1220.6	1421.5
130°	461.8	523.6	761.9	1167.0	1348.5
132.5°	477.8	539.0	758.1	1118.6	1285.8
135°	501.8	561.3	753.9	1055.6	1194.9
137.5°	526.0	582.2	750.4	1004.4	1117.9
140°	542.6	595.0	749.1	971.5	1072.4
142.5°	558.6	607.9	746.5	941.7	1030.2
145°	583.4	627.3	743.5	903.5	972.4
147.5°	606.0	644.8	740.0	868.9	921.8
150°	622.6	657.1	738.7	850.1	892.4
152.5°	638.0	668.1	738.1	832.6	867.4
155°	658.7	684.5	737.1	810.5	837.1
157.5°	680.1	698.1	737.3	795.1	812.6
160°	692.3	707.1	737.9	785.4	797.9
162.5°	701.9	714.2	738.5	777.6	787.0
165°	717.1	724.1	740.3	769.2	773.1
167.5°	727.5	732.3	740.5	761.9	763.8
170°	733.9	736.2	741.1	758.7	758.7
172.5°	739.0	739.5	741.1	754.8	754.2
175°	744.3	743.5	741.1	750.7	749.1
177.5°	746.1	744.2	740.9	747.3	745.4
180°	743.5	743.5	743.5	743.5	743.5

(END OF REPORT)