

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562544

Luminaire Tested: **SQ4-PC3-025U-075D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562544
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6154.8 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 64.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562544
CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562544

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75				
1	103	99	95	91	98	94	91	88	86	83	80	78	75	73	70	69	67	63				
2	94	87	80	75	89	83	77	72	75	70	67	68	65	61	62	59	57	53				
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48	45				
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	41	38				
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	33				
6	67	54	46	39	63	52	44	38	48	41	36	44	38	34	40	35	32	29				
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	36	32	28	26				
8	57	45	36	31	55	43	35	30	39	33	28	36	31	27	33	29	25	23				
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	31	26	23	21				
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	29	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7803	7803	7803
5°	7862	7811	7782
10°	7842	7806	7784
15°	7801	7801	7794
20°	7750	7773	7773
25°	7677	7733	7709
30°	7583	7675	7642
35°	7470	7585	7532
40°	7347	7451	7375
45°	7213	7264	7152
50°	7025	7025	6913
55°	6802	6714	6613
60°	6473	6343	6242
65°	5984	5864	5813
70°	5239	5280	5260
75°	4215	4661	4689
80°	2997	3953	3993
85°	1826	3313	3313



TEST NUMBER: P562544

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	2.6
10°-20°	459.4	7.5
20°-30°	695.7	11.3
30°-40°	834.0	13.6
40°-50°	850.4	13.8
50°-60°	742.3	12.1
60°-70°	531.4	8.6
70°-80°	273.7	4.4
80°-90°	70.5	1.1
90°-100°	115.6	1.9
100°-110°	303.9	4.9
110°-120°	315.1	5.1
120°-130°	252.8	4.1
130°-140°	198.3	3.2
140°-150°	152.2	2.5
150°-160°	109.6	1.8
160°-170°	67.1	1.1
170°-180°	22.7	0.4
0°-30°	1315.1	21.4
0°-40°	2149.1	34.9
0°-60°	3741.9	60.8
0°-90°	4617.5	75.0
90°-120°	734.6	11.9
90°-150°	1337.9	21.7
90°-180°	1537.0	25.0
0°-180°	6154.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1691	1691	1691	1691	1691	
5°	1698	1681	1687	1682	1680	161
15°	1634	1620	1634	1634	1632	461
25°	1508	1498	1519	1514	1514	694
35°	1326	1324	1347	1338	1338	830
45°	1106	1103	1114	1099	1096	851
55°	846	835	835	822	822	754
65°	548	536	537	532	532	542
75°	236	247	262	263	263	256
85°	34	53	63	64	63	47
90°	2	4	12	6	6	3
95°	15	60	199	103	70	17
105°	55	83	336	510	476	58
115°	97	118	269	537	613	96
125°	135	152	245	414	488	120
135°	161	178	237	334	379	125
145°	187	199	234	285	307	117
155°	211	217	234	257	264	97
165°	228	231	234	243	246	64
175°	237	237	236	239	239	23
180°	237	237	237	237	237	



TEST NUMBER: P562544

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1691.4	1691.4	1691.4	1691.4	1691.4
2.5°	1701.5	1686.8	1691.4	1687.5	1681.4
5°	1697.7	1680.9	1686.7	1682.0	1680.5
7.5°	1685.5	1668.6	1676.4	1673.2	1671.7
10°	1674.2	1657.4	1666.4	1663.2	1661.7
12.5°	1659.2	1643.6	1653.8	1650.7	1650.4
15°	1633.5	1619.7	1633.5	1633.5	1631.9
17.5°	1601.2	1588.7	1603.4	1604.3	1603.4
20°	1578.7	1564.9	1583.4	1581.8	1583.4
22.5°	1551.1	1539.8	1559.6	1555.5	1557.1
25°	1508.2	1497.5	1519.2	1514.5	1514.5
27.5°	1457.5	1449.8	1473.4	1468.4	1468.4
30°	1423.6	1416.0	1440.9	1434.6	1434.6
32.5°	1386.0	1380.8	1404.5	1397.0	1397.0
35°	1326.5	1323.5	1346.9	1337.5	1337.5
37.5°	1265.1	1262.4	1283.6	1272.3	1268.6
40°	1220.0	1218.5	1237.3	1224.7	1224.7
42.5°	1174.9	1173.4	1189.6	1174.6	1174.6
45°	1105.7	1102.6	1113.5	1099.4	1096.3
47.5°	1030.2	1027.1	1034.0	1018.6	1017.1
50°	978.8	975.8	978.8	964.7	963.2
52.5°	926.2	920.7	921.2	907.1	906.8
55°	845.7	835.0	834.8	822.2	822.2
57.5°	760.5	746.4	747.7	737.0	735.5
60°	701.6	686.3	687.5	678.1	676.6
62.5°	644.0	626.2	629.9	619.2	618.9
65°	548.2	535.9	537.2	532.5	532.5
67.5°	456.1	444.7	452.9	449.2	448.9
70°	388.4	380.7	391.5	391.5	390.0
72.5°	325.8	325.5	338.9	338.9	339.9
75°	236.5	247.2	261.5	263.1	263.1
77.5°	157.9	176.9	192.6	193.3	192.9
80°	112.8	134.2	148.8	151.9	150.3
82.5°	76.4	99.1	111.2	114.3	112.8
85°	34.5	52.8	62.6	64.2	62.6
87.5°	10.3	21.9	27.5	26.2	23.8
90°	1.5	4.5	12.2	6.1	6.1
92.5°	6.4	30.8	68.1	30.2	19.5
95°	15.2	59.8	199.2	102.6	69.9
97.5°	26.5	65.7	298.0	237.0	174.5
100°	35.0	70.6	328.4	332.8	258.5
102.5°	42.3	75.6	336.9	414.5	350.9
105°	54.7	83.0	336.0	510.1	475.9
107.5°	67.5	93.7	316.8	559.7	568.0
110°	76.0	99.8	301.0	572.5	608.1

TEST NUMBER: P562544

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	84.5	107.1	286.4	564.4	619.1
115°	97.3	118.1	269.1	536.9	612.7
117.5°	109.8	128.8	257.2	498.8	582.9
120°	117.1	134.9	252.4	473.2	554.9
122.5°	124.4	142.2	248.7	447.6	528.2
125°	135.3	151.7	244.8	413.7	488.0
127.5°	144.1	160.8	241.4	386.4	449.1
130°	149.0	166.8	240.2	369.2	427.2
132.5°	153.9	171.7	239.0	354.5	406.5
135°	161.2	177.5	237.2	334.0	378.6
137.5°	168.8	184.8	236.9	318.6	355.2
140°	174.8	189.7	235.7	306.4	340.6
142.5°	179.7	193.4	235.7	297.7	327.2
145°	187.0	198.9	234.1	284.8	307.1
147.5°	194.3	205.9	234.1	274.1	292.5
150°	199.2	209.6	234.1	267.9	282.8
152.5°	204.0	212.1	234.1	263.0	274.3
155°	211.3	217.3	234.1	257.1	264.5
157.5°	216.8	222.5	234.1	251.9	257.2
160°	220.5	224.9	234.1	249.4	252.4
162.5°	224.1	227.4	234.1	247.0	249.9
165°	228.1	231.0	234.1	243.3	246.3
167.5°	231.7	233.2	235.7	241.8	243.0
170°	234.1	235.6	235.7	241.7	241.7
172.5°	235.3	235.6	235.7	240.5	239.3
175°	237.2	237.2	235.7	238.7	238.7
177.5°	237.2	237.2	236.0	238.4	237.2
180°	237.2	237.2	237.2	237.2	237.2

(END OF REPORT)