

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562688

Luminaire Tested: **SQ4-PC3-050U-125D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562688
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10999.4 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 114.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562688
CATALOG NUMBER: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562688

CATALOG NUMBER: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	91	97	93	90	86	84	81	79	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	43
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	34	30	28
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	35	30	27	25
8	57	44	36	30	54	42	35	30	39	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13230	13230	13230
5°	13330	13244	13195
10°	13298	13235	13198
15°	13228	13228	13215
20°	13141	13180	13180
25°	13017	13111	13071
30°	12858	13014	12957
35°	12667	12861	12771
40°	12458	12634	12505
45°	12231	12318	12127
50°	11911	11911	11721
55°	11533	11384	11213
60°	10976	10756	10584
65°	10145	9943	9856
70°	8883	8955	8918
75°	7147	7905	7951
80°	5079	6703	6772
85°	3091	5621	5621



TEST NUMBER: P562688

CATALOG NUMBER: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.4	2.5
10°-20°	778.9	7.1
20°-30°	1179.6	10.7
30°-40°	1414.1	12.9
40°-50°	1441.9	13.1
50°-60°	1258.7	11.4
60°-70°	901.1	8.2
70°-80°	464.1	4.2
80°-90°	119.2	1.1
90°-100°	233.1	2.1
100°-110°	633.2	5.8
110°-120°	651.0	5.9
120°-130°	520.5	4.7
130°-140°	409.0	3.7
140°-150°	313.6	2.9
150°-160°	225.5	2.1
160°-170°	137.9	1.3
170°-180°	46.5	0.4
0°-30°	2229.9	20.3
0°-40°	3644.0	33.1
0°-60°	6344.7	57.7
0°-90°	7829.2	71.2
90°-120°	1517.2	13.8
90°-150°	2760.3	25.1
90°-180°	3170.0	28.8
0°-180°	10999.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2868	2868	2868	2868	2868	
5°	2879	2850	2860	2852	2849	273
15°	2770	2746	2770	2770	2767	781
25°	2557	2539	2576	2568	2568	1177
35°	2249	2244	2284	2268	2268	1407
45°	1875	1870	1888	1864	1859	1443
55°	1434	1416	1415	1394	1394	1278
65°	929	909	911	903	903	919
75°	401	419	444	446	446	433
85°	58	90	106	109	106	79
90°	2	6	11	14	14	5
95°	34	128	406	177	119	36
105°	112	175	696	1060	998	119
115°	200	243	557	1109	1263	197
125°	275	313	504	850	1002	245
135°	331	368	490	692	781	256
145°	382	410	484	588	632	240
155°	432	448	481	528	543	199
165°	468	474	482	503	504	132
175°	486	487	484	490	489	46
180°	486	486	486	486	486	

TEST NUMBER: P562688

CATALOG NUMBER: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2868.0	2868.0	2868.0	2868.0	2868.0
2.5°	2885.0	2860.1	2868.0	2861.4	2851.0
5°	2878.6	2850.1	2860.0	2852.0	2849.4
7.5°	2857.9	2829.4	2842.5	2837.1	2834.5
10°	2838.8	2810.2	2825.5	2820.1	2817.5
12.5°	2813.3	2786.8	2804.3	2798.9	2798.4
15°	2769.7	2746.4	2769.7	2769.7	2767.1
17.5°	2715.0	2693.8	2718.8	2720.3	2718.8
20°	2676.8	2653.4	2684.8	2682.2	2684.8
22.5°	2630.1	2610.9	2644.4	2637.6	2640.2
25°	2557.3	2539.1	2575.9	2567.9	2567.9
27.5°	2471.3	2458.3	2498.3	2489.9	2489.9
30°	2413.9	2400.9	2443.1	2432.5	2432.5
32.5°	2350.2	2341.3	2381.5	2368.8	2368.8
35°	2249.3	2244.1	2283.8	2267.8	2267.8
37.5°	2145.2	2140.5	2176.5	2157.2	2151.0
40°	2068.7	2066.1	2097.9	2076.6	2076.6
42.5°	1992.2	1989.6	2017.2	1991.7	1991.7
45°	1874.8	1869.6	1888.1	1864.1	1858.9
47.5°	1746.8	1741.6	1753.2	1727.1	1724.5
50°	1659.7	1654.5	1659.7	1635.8	1633.2
52.5°	1570.5	1561.1	1562.0	1538.1	1537.6
55°	1434.0	1415.8	1415.4	1394.2	1394.2
57.5°	1289.5	1265.7	1267.8	1249.6	1247.1
60°	1189.7	1163.7	1165.8	1149.8	1147.2
62.5°	1092.0	1061.8	1068.1	1050.0	1049.5
65°	929.4	908.7	910.9	902.9	902.9
67.5°	773.3	754.1	768.0	761.6	761.1
70°	658.6	645.6	663.9	663.8	661.2
72.5°	552.4	551.8	574.7	574.7	576.3
75°	401.0	419.2	443.5	446.1	446.1
77.5°	267.7	299.9	326.6	327.7	327.2
80°	191.2	227.6	252.3	257.5	254.9
82.5°	129.6	168.0	188.5	193.8	191.2
85°	58.4	89.6	106.2	108.8	106.2
87.5°	17.3	36.9	44.7	45.2	41.1
90°	1.6	6.1	10.9	14.1	14.1
92.5°	14.1	63.8	110.8	47.6	40.3
95°	34.3	127.5	405.9	176.7	118.7
97.5°	56.8	140.8	622.3	484.1	340.0
100°	71.8	149.7	688.5	697.9	563.6
102.5°	86.8	158.5	706.0	863.1	744.7
105°	112.4	175.0	696.3	1060.2	997.6
107.5°	138.9	194.2	656.0	1161.9	1179.3
110°	157.7	208.1	626.0	1182.0	1256.8



TEST NUMBER: P562688

CATALOG NUMBER: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	173.9	221.8	596.1	1165.3	1278.0
115°	199.8	242.6	557.3	1108.8	1263.0
117.5°	224.2	265.1	532.7	1028.7	1202.4
120°	240.4	280.1	521.4	975.0	1147.5
122.5°	254.2	293.8	513.9	921.1	1087.5
125°	274.8	312.9	504.3	849.6	1002.3
127.5°	293.2	331.0	499.0	795.4	926.4
130°	304.4	341.1	496.5	761.4	878.9
132.5°	315.7	352.3	494.0	732.4	836.5
135°	331.0	367.6	490.2	692.1	780.6
137.5°	347.5	380.8	488.3	656.5	730.9
140°	357.5	389.6	487.1	633.8	701.0
142.5°	367.5	397.1	485.8	616.1	672.2
145°	382.5	410.0	484.0	588.0	632.3
147.5°	399.4	422.9	482.4	565.9	600.7
150°	410.6	430.4	482.4	553.3	580.8
152.5°	419.3	436.7	481.2	541.9	564.5
155°	432.4	447.7	480.8	528.0	543.3
157.5°	445.3	457.2	480.8	518.6	530.2
160°	452.7	463.4	480.8	512.3	521.4
162.5°	460.2	468.5	482.1	507.2	513.9
165°	468.4	474.5	482.4	502.7	504.3
167.5°	476.8	479.8	484.0	497.4	498.6
170°	479.3	482.3	484.0	494.9	494.9
172.5°	481.8	483.6	484.0	492.4	492.4
175°	485.5	487.1	484.0	490.2	488.7
177.5°	486.8	486.8	483.0	488.0	485.5
180°	485.5	485.5	485.5	485.5	485.5

(END OF REPORT)