

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562856

Luminaire Tested: **SQ4-PC3-0U-100D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562856  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-100D-930-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6133.6 lumens  
Efficiency: N/A  
Efficacy: 85.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Direct

Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562856  
CATALOG NUMBER: SQ4-PC3-0U-100D-930-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P562856

CATALOG NUMBER: SQ4-PC3-0U-100D-930-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10367	10367	10367
5°	10446	10378	10339
10°	10420	10371	10342
15°	10365	10365	10355
20°	10297	10328	10328
25°	10200	10274	10243
30°	10076	10198	10153
35°	9926	10078	10008
40°	9762	9900	9800
45°	9584	9652	9503
50°	9334	9334	9185
55°	9038	8920	8787
60°	8602	8428	8294
65°	7950	7792	7723
70°	6961	7016	6989
75°	5600	6194	6231
80°	3980	5252	5308
85°	2424	4404	4404



TEST NUMBER: P562856

CATALOG NUMBER: SQ4-PC3-0U-100D-930-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	212.7	3.5
10°-20°	610.4	10.0
20°-30°	924.3	15.1
30°-40°	1108.1	18.1
40°-50°	1129.9	18.4
50°-60°	986.3	16.1
60°-70°	706.2	11.5
70°-80°	363.7	5.9
80°-90°	92.0	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1747.4	28.5
0°-40°	2855.5	46.6
0°-60°	4971.8	81.1
0°-90°	6133.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6133.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2247	2247	2247	2247	2247	
5°	2256	2233	2241	2235	2233	214
15°	2170	2152	2170	2170	2168	612
25°	2004	1990	2018	2012	2012	922
35°	1763	1758	1790	1777	1777	1102
45°	1469	1465	1480	1461	1457	1131
55°	1124	1110	1109	1092	1092	1002
65°	728	712	714	708	708	720
75°	314	328	348	350	350	340
85°	46	70	83	85	83	64
90°	0	0	0	0	0	



TEST NUMBER: P562856

CATALOG NUMBER: SQ4-PC3-0U-100D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2247.4	2247.4	2247.4	2247.4	2247.4
2.5°	2260.7	2241.2	2247.4	2242.2	2234.1
5°	2255.7	2233.4	2241.2	2234.9	2232.8
7.5°	2239.5	2217.1	2227.4	2223.2	2221.2
10°	2224.5	2202.1	2214.1	2209.9	2207.9
12.5°	2204.5	2183.8	2197.5	2193.3	2192.9
15°	2170.4	2152.1	2170.4	2170.4	2168.3
17.5°	2127.6	2110.9	2130.5	2131.7	2130.5
20°	2097.6	2079.3	2103.8	2101.8	2103.8
22.5°	2061.0	2045.9	2072.2	2066.8	2068.9
25°	2003.9	1989.7	2018.5	2012.3	2012.3
27.5°	1936.5	1926.3	1957.7	1951.1	1951.1
30°	1891.6	1881.4	1914.5	1906.1	1906.1
32.5°	1841.6	1834.7	1866.2	1856.2	1856.2
35°	1762.6	1758.5	1789.6	1777.1	1777.1
37.5°	1681.0	1677.3	1705.5	1690.4	1685.6
40°	1621.1	1619.0	1643.9	1627.3	1627.3
42.5°	1561.1	1559.1	1580.7	1560.7	1560.7
45°	1469.1	1465.1	1479.5	1460.7	1456.7
47.5°	1368.8	1364.8	1373.8	1353.4	1351.4
50°	1300.6	1296.5	1300.6	1281.8	1279.8
52.5°	1230.7	1223.3	1224.0	1205.3	1204.9
55°	1123.7	1109.5	1109.1	1092.5	1092.5
57.5°	1010.5	991.8	993.4	979.2	977.2
60°	932.3	911.9	913.5	901.0	899.0
62.5°	855.7	832.1	837.0	822.8	822.4
65°	728.3	712.1	713.8	707.5	707.5
67.5°	606.0	590.9	601.8	596.8	596.4
70°	516.1	505.9	520.2	520.2	518.2
72.5°	432.8	432.4	450.3	450.3	451.6
75°	314.2	328.5	347.5	349.6	349.6
77.5°	209.8	235.0	256.0	256.8	256.4
80°	149.8	178.3	197.7	201.8	199.8
82.5°	101.5	131.7	147.7	151.9	149.8
85°	45.8	70.2	83.2	85.3	83.2
87.5°	13.3	28.0	33.3	33.2	30.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)