

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562976

Luminaire Tested: **SQ4-PC3-100U-125D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562976  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-100U-125D-930-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 14221.4 lumens  
Efficiency: N/A  
Efficacy: 101.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 140.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562976  
CATALOG NUMBER: SQ4-PC3-100U-125D-930-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P562976

CATALOG NUMBER: SQ4-PC3-100U-125D-930-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51	47
2	90	83	76	71	83	77	72	67	66	62	59	56	54	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	26	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13230	13230	13230
5°	13330	13244	13195
10°	13298	13235	13198
15°	13228	13228	13215
20°	13141	13180	13180
25°	13017	13111	13071
30°	12858	13014	12957
35°	12667	12861	12771
40°	12458	12634	12505
45°	12231	12318	12127
50°	11911	11911	11721
55°	11533	11384	11213
60°	10976	10756	10584
65°	10145	9943	9856
70°	8883	8955	8918
75°	7147	7905	7951
80°	5079	6703	6772
85°	3091	5621	5621



TEST NUMBER: P562976

CATALOG NUMBER: SQ4-PC3-100U-125D-930-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	271.4	1.9
10°-20°	778.9	5.5
20°-30°	1179.6	8.3
30°-40°	1414.1	9.9
40°-50°	1441.9	10.1
50°-60°	1258.7	8.9
60°-70°	901.1	6.3
70°-80°	464.1	3.3
80°-90°	119.4	0.8
90°-100°	460.7	3.2
100°-110°	1271.9	8.9
110°-120°	1311.7	9.2
120°-130°	1054.1	7.4
130°-140°	828.4	5.8
140°-150°	635.3	4.5
150°-160°	456.6	3.2
160°-170°	279.2	2.0
170°-180°	94.1	0.7
0°-30°	2229.9	15.7
0°-40°	3644.0	25.6
0°-60°	6344.7	44.6
0°-90°	7829.4	55.1
90°-120°	3044.3	21.4
90°-150°	5562.0	39.1
90°-180°	6392.0	44.9
0°-180°	14221.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2868	2868	2868	2868	2868	
5°	2879	2850	2860	2852	2849	273
15°	2770	2746	2770	2770	2767	781
25°	2557	2539	2576	2568	2568	1177
35°	2249	2244	2284	2268	2268	1407
45°	1875	1870	1888	1864	1859	1443
55°	1434	1416	1415	1394	1394	1278
65°	929	909	911	903	903	919
75°	401	419	444	446	446	433
85°	58	90	106	109	106	79
90°	3	6	13	14	16	7
95°	68	249	836	344	224	72
105°	227	350	1399	2136	2012	241
115°	406	491	1127	2231	2537	399
125°	557	634	1022	1729	2029	496
135°	670	743	993	1400	1579	519
145°	778	831	981	1192	1283	487
155°	877	906	973	1070	1103	404
165°	949	962	978	1015	1023	268
175°	984	985	979	993	990	93
180°	984	984	984	984	984	

TEST NUMBER: P562976

CATALOG NUMBER: SQ4-PC3-100U-125D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2868.0	2868.0	2868.0	2868.0	2868.0
2.5°	2885.0	2860.1	2868.0	2861.4	2851.0
5°	2878.6	2850.1	2860.0	2852.0	2849.4
7.5°	2857.9	2829.4	2842.5	2837.1	2834.5
10°	2838.8	2810.2	2825.5	2820.1	2817.5
12.5°	2813.3	2786.8	2804.3	2798.9	2798.4
15°	2769.7	2746.4	2769.7	2769.7	2767.1
17.5°	2715.0	2693.8	2718.8	2720.3	2718.8
20°	2676.8	2653.4	2684.8	2682.2	2684.8
22.5°	2630.1	2610.9	2644.4	2637.6	2640.2
25°	2557.3	2539.1	2575.9	2567.9	2567.9
27.5°	2471.3	2458.3	2498.3	2489.9	2489.9
30°	2413.9	2400.9	2443.1	2432.5	2432.5
32.5°	2350.2	2341.3	2381.5	2368.8	2368.8
35°	2249.3	2244.1	2283.8	2267.8	2267.8
37.5°	2145.2	2140.5	2176.5	2157.2	2151.0
40°	2068.7	2066.1	2097.9	2076.6	2076.6
42.5°	1992.2	1989.6	2017.2	1991.7	1991.7
45°	1874.8	1869.6	1888.1	1864.1	1858.9
47.5°	1746.8	1741.6	1753.2	1727.1	1724.5
50°	1659.7	1654.5	1659.7	1635.8	1633.2
52.5°	1570.5	1561.1	1562.0	1538.1	1537.6
55°	1434.0	1415.8	1415.4	1394.2	1394.2
57.5°	1289.5	1265.7	1267.8	1249.6	1247.1
60°	1189.7	1163.7	1165.8	1149.8	1147.2
62.5°	1092.0	1061.8	1068.1	1050.0	1049.5
65°	929.4	908.7	910.9	902.9	902.9
67.5°	773.3	754.1	768.0	761.6	761.1
70°	658.6	645.6	663.9	663.8	661.2
72.5°	552.4	551.8	574.7	574.7	576.3
75°	401.0	419.2	443.5	446.1	446.1
77.5°	267.7	299.9	326.6	327.7	327.2
80°	191.2	227.6	252.3	257.5	254.9
82.5°	129.6	168.0	188.5	193.8	191.2
85°	58.4	89.6	106.2	108.8	106.2
87.5°	17.6	36.9	45.0	45.2	41.4
90°	3.1	6.2	12.6	14.2	15.7
92.5°	28.3	117.6	210.3	76.7	59.8
95°	67.7	249.3	835.8	343.6	223.5
97.5°	112.1	279.2	1238.1	953.2	690.4
100°	144.8	297.2	1386.7	1396.5	1134.9
102.5°	176.3	317.6	1415.7	1725.5	1477.4
105°	226.7	349.8	1399.3	2136.3	2011.6
107.5°	280.2	389.8	1321.2	2334.4	2379.9
110°	318.0	416.5	1260.8	2377.0	2524.7

TEST NUMBER: P562976

CATALOG NUMBER: SQ4-PC3-100U-125D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	352.0	446.8	1204.1	2343.3	2561.3
115°	406.1	490.7	1127.0	2231.1	2537.3
117.5°	453.3	537.7	1076.3	2073.0	2421.5
120°	484.8	567.9	1056.2	1966.1	2317.0
122.5°	515.0	594.4	1039.8	1866.2	2198.6
125°	557.2	634.2	1021.5	1728.8	2028.9
127.5°	593.1	670.0	1010.8	1612.7	1871.5
130°	617.0	694.0	1005.8	1541.6	1777.1
132.5°	639.7	712.9	1000.8	1481.9	1695.2
135°	670.5	742.9	993.2	1400.2	1578.8
137.5°	705.2	771.0	989.4	1331.6	1484.0
140°	724.1	788.7	986.9	1285.9	1419.8
142.5°	745.5	805.2	984.4	1245.2	1363.1
145°	777.6	831.4	980.6	1192.0	1282.8
147.5°	808.4	855.5	977.2	1147.2	1217.7
150°	831.1	869.6	975.9	1120.4	1177.4
152.5°	848.7	884.7	974.6	1097.5	1144.6
155°	876.7	906.0	972.7	1069.5	1103.4
157.5°	902.5	925.0	973.1	1049.1	1072.2
160°	917.7	937.7	974.3	1037.7	1054.6
162.5°	930.3	947.8	975.6	1027.5	1040.7
165°	949.1	961.5	977.5	1015.4	1023.1
167.5°	963.6	971.0	979.0	1008.1	1010.5
170°	971.2	977.3	979.0	1004.2	1004.2
172.5°	977.5	981.2	979.0	999.2	997.9
175°	983.8	985.3	979.0	993.1	990.1
177.5°	986.3	985.1	978.7	987.5	985.0
180°	983.8	983.8	983.8	983.8	983.8

(END OF REPORT)