

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563096

Luminaire Tested: **SQ4-PC3-150U-050D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563096  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12722.3 lumens  
Efficiency: N/A  
Efficacy: 113.7 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 111.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563096  
CATALOG NUMBER: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563096

CATALOG NUMBER: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	24	23	17
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20	15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5294	5294	5294
5°	5334	5299	5280
10°	5321	5296	5281
15°	5293	5293	5288
20°	5258	5274	5274
25°	5209	5246	5230
30°	5145	5207	5185
35°	5068	5146	5111
40°	4985	5055	5004
45°	4894	4929	4852
50°	4766	4766	4690
55°	4615	4555	4487
60°	4392	4304	4235
65°	4059	3979	3944
70°	3554	3582	3569
75°	2861	3164	3182
80°	2032	2680	2710
85°	1239	2249	2249



TEST NUMBER: P563096

CATALOG NUMBER: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.6	0.9
10°-20°	311.7	2.4
20°-30°	472.0	3.7
30°-40°	565.9	4.4
40°-50°	577.0	4.5
50°-60°	503.7	4.0
60°-70°	360.6	2.8
70°-80°	185.7	1.5
80°-90°	50.1	0.4
90°-100°	691.1	5.4
100°-110°	1868.5	14.7
110°-120°	1964.4	15.4
120°-130°	1595.6	12.5
130°-140°	1251.7	9.8
140°-150°	960.7	7.6
150°-160°	690.9	5.4
160°-170°	422.1	3.3
170°-180°	142.3	1.1
0°-30°	892.3	7.0
0°-40°	1458.1	11.5
0°-60°	2538.8	20.0
0°-90°	3135.1	24.6
90°-120°	4524.0	35.6
90°-150°	8331.9	65.5
90°-180°	9587.0	75.4
0°-180°	12722.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1152	1140	1144	1141	1140	109
15°	1108	1099	1108	1108	1107	312
25°	1023	1016	1031	1028	1028	471
35°	900	898	914	908	908	563
45°	750	748	756	746	744	577
55°	574	566	566	558	558	511
65°	372	364	364	361	361	368
75°	160	168	178	178	178	173
85°	23	36	42	44	42	32
90°	3	10	21	22	21	8
95°	107	376	1149	595	354	112
105°	347	537	2073	3058	2932	366
115°	611	748	1719	3328	3757	604
125°	837	959	1549	2615	3072	746
135°	1004	1122	1508	2111	2390	776
145°	1167	1254	1487	1807	1945	730
155°	1317	1369	1474	1621	1674	608
165°	1434	1448	1481	1538	1546	404
175°	1489	1487	1482	1501	1498	141
180°	1487	1487	1487	1487	1487	



TEST NUMBER: P563096

CATALOG NUMBER: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1147.6	1147.6	1147.6	1147.6	1147.6
2.5°	1154.4	1144.4	1147.6	1145.0	1140.8
5°	1151.9	1140.4	1144.4	1141.2	1140.2
7.5°	1143.6	1132.1	1137.4	1135.3	1134.2
10°	1135.9	1124.5	1130.6	1128.5	1127.4
12.5°	1125.7	1115.1	1122.1	1120.0	1119.8
15°	1108.3	1098.9	1108.3	1108.3	1107.2
17.5°	1086.4	1077.9	1087.9	1088.5	1087.9
20°	1071.1	1061.7	1074.3	1073.2	1074.3
22.5°	1052.4	1044.7	1058.1	1055.4	1056.4
25°	1023.3	1016.0	1030.7	1027.5	1027.5
27.5°	988.9	983.7	999.7	996.3	996.3
30°	965.9	960.7	977.6	973.3	973.3
32.5°	940.4	936.9	952.9	947.8	947.8
35°	900.0	897.9	913.8	907.5	907.5
37.5°	858.4	856.5	870.9	863.2	860.7
40°	827.8	826.7	839.5	831.0	831.0
42.5°	797.2	796.1	807.1	796.9	796.9
45°	750.2	748.1	755.5	745.9	743.8
47.5°	699.0	696.9	701.5	691.1	690.1
50°	664.1	662.0	664.1	654.5	653.5
52.5°	628.4	624.7	625.0	615.5	615.2
55°	573.8	566.5	566.4	557.9	557.9
57.5°	516.0	506.4	507.3	500.0	499.0
60°	476.0	465.7	466.5	460.1	459.0
62.5°	436.9	424.9	427.4	420.1	419.9
65°	371.9	363.6	364.5	361.3	361.3
67.5°	309.4	301.7	307.3	304.7	304.5
70°	263.5	258.3	265.6	265.6	264.6
72.5°	221.0	220.8	229.9	230.0	230.6
75°	160.5	167.7	177.5	178.5	178.5
77.5°	107.1	120.0	130.7	131.1	130.9
80°	76.5	91.1	100.9	103.0	102.0
82.5°	51.9	67.2	75.4	77.5	76.5
85°	23.4	35.8	42.5	43.5	42.5
87.5°	7.4	16.2	21.2	21.4	19.5
90°	3.2	9.5	20.8	22.4	20.8
92.5°	45.5	165.7	326.8	141.9	102.8
95°	107.2	376.4	1149.3	594.8	353.7
97.5°	172.2	431.7	1791.4	1482.5	1088.8
100°	220.9	454.1	1991.2	2076.6	1679.1
102.5°	265.7	485.1	2061.6	2527.0	2229.7
105°	347.3	536.7	2072.8	3057.6	2932.4
107.5°	422.9	595.7	1982.2	3388.5	3430.2
110°	481.8	638.3	1901.6	3477.4	3654.3

TEST NUMBER: P563096

CATALOG NUMBER: SQ4-PC3-150U-050D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	534.3	680.8	1827.3	3459.6	3756.7
115°	611.4	747.6	1719.1	3327.9	3756.7
117.5°	687.0	814.7	1647.7	3126.5	3612.6
120°	733.1	858.3	1605.4	2982.1	3478.2
122.5°	776.6	899.3	1579.8	2827.2	3327.1
125°	837.1	959.2	1549.4	2614.6	3071.6
127.5°	892.8	1012.7	1531.5	2441.1	2843.0
130°	923.6	1047.2	1523.8	2334.0	2697.1
132.5°	955.6	1078.0	1516.1	2237.3	2571.6
135°	1003.6	1122.5	1507.8	2111.2	2389.7
137.5°	1051.9	1164.3	1500.8	2008.8	2235.8
140°	1085.2	1190.1	1498.2	1943.0	2144.9
142.5°	1117.2	1215.8	1493.1	1883.5	2060.3
145°	1166.9	1254.5	1487.0	1807.0	1944.8
147.5°	1212.0	1289.6	1479.9	1737.8	1843.6
150°	1245.3	1314.2	1477.4	1700.2	1784.7
152.5°	1276.0	1336.1	1476.1	1665.3	1734.8
155°	1317.3	1369.0	1474.2	1621.1	1674.3
157.5°	1360.2	1396.2	1474.5	1590.2	1625.3
160°	1384.5	1414.3	1475.8	1570.8	1595.8
162.5°	1403.8	1428.5	1477.1	1555.3	1574.1
165°	1434.2	1448.3	1480.6	1538.4	1546.2
167.5°	1455.0	1464.7	1480.9	1523.9	1527.6
170°	1467.8	1472.5	1482.2	1517.4	1517.4
172.5°	1478.0	1479.0	1482.2	1509.7	1508.4
175°	1488.6	1487.0	1482.2	1501.3	1498.2
177.5°	1492.1	1488.4	1481.9	1494.6	1490.8
180°	1487.0	1487.0	1487.0	1487.0	1487.0

(END OF REPORT)