

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937051

Luminaire Tested: SQ4-FB-075U-050D-930-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937051
REPORT IS A COMBINATION OF REPORTS P933509 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-050D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5551.9 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 51.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937051
CATALOG NUMBER: SQ4-FB-075U-050D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P937051

CATALOG NUMBER: SQ4-FB-075U-050D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				35
1	94	90	86	82	85	81	78	75	65	63	61	50	49	47	37	36	35	29				29
2	85	78	72	66	77	70	65	61	57	53	50	44	41	39	32	30	29	23				23
3	77	68	61	55	70	62	55	50	49	45	41	38	35	32	28	26	24	19				19
4	71	60	52	46	63	54	47	42	44	39	35	34	30	27	25	22	20	16				16
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17	14				14
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15	12				12
7	55	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13	10				10
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	14	12	9				9
9	47	35	27	22	42	32	25	20	26	21	17	20	16	14	15	12	10	8				8
10	44	32	24	20	39	29	22	18	23	18	15	18	15	12	14	11	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1554	1554	1554
5°	1518	1795	2089
10°	1376	2617	3462
15°	1169	3418	4181
20°	951	3960	4262
25°	794	4143	4175
30°	669	4168	4167
35°	591	4098	4275
40°	514	4007	4386
45°	466	3939	4403
50°	427	3879	4331
55°	409	3791	4139
60°	418	3623	3835
65°	434	3368	3418
70°	462	2935	2889
75°	509	2391	2254
80°	550	1656	1519
85°	483	878	777

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4403 cd/sqm



TEST NUMBER: P937051

CATALOG NUMBER: SQ4-FB-075U-050D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.5	0.6
10°-20°	144.0	2.6
20°-30°	251.9	4.5
30°-40°	324.3	5.8
40°-50°	362.2	6.5
50°-60°	346.9	6.2
60°-70°	274.9	5.0
70°-80°	161.7	2.9
80°-90°	47.0	0.8
90°-100°	271.2	4.9
100°-110°	713.0	12.8
110°-120°	739.3	13.3
120°-130°	593.0	10.7
130°-140°	465.3	8.4
140°-150°	357.1	6.4
150°-160°	257.2	4.6
160°-170°	157.4	2.8
170°-180°	53.2	1.0
0°-30°	428.4	7.7
0°-40°	752.7	13.6
0°-60°	1461.8	26.3
0°-90°	1945.4	35.0
90°-120°	1723.4	31.0
90°-150°	3138.8	56.5
90°-180°	3607.0	65.0
0°-180°	5551.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	251	251	251	251	251	
5°	245	262	296	334	346	23
15°	183	338	570	691	713	51
25°	117	384	679	709	710	54
35°	79	367	640	676	703	49
45°	54	292	565	648	677	42
55°	39	186	480	557	573	35
65°	31	98	356	401	406	30
75°	23	60	196	215	216	24
85°	8	18	48	53	54	9
90°	4	10	28	14	14	4
95°	36	140	467	241	164	40
105°	128	195	788	1197	1116	136
115°	228	277	631	1259	1438	225
125°	317	356	574	970	1145	282
135°	378	416	556	783	888	293
145°	439	467	549	668	721	275
155°	496	510	549	603	621	228
165°	535	542	549	571	578	151
175°	556	556	553	560	560	53
180°	556	556	556	556	556	



TEST NUMBER: P937051

CATALOG NUMBER: SQ4-FB-075U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	251.2	251.2	251.2	251.2	251.2	251.2	251.2	251.2	251.2	251.2	251.2
2.5°	251.2	251.2	252.8	253.6	255.3	256.1	257.7	259.3	264.1	264.9	266.5
5°	244.8	248.0	258.5	262.5	273.8	289.2	295.6	306.1	327.9	334.4	338.5
7.5°	235.0	242.3	268.1	274.6	302.9	343.3	360.2	382.9	417.6	434.6	448.3
10°	219.7	235.0	281.0	296.5	342.5	403.8	435.4	466.9	519.4	542.7	551.7
12.5°	202.8	227.8	294.8	315.8	382.1	471.7	509.7	544.4	604.2	635.7	640.5
15°	183.3	217.3	307.7	338.5	424.1	528.2	570.2	613.1	668.8	691.4	697.1
17.5°	166.4	209.2	319.8	352.2	456.3	579.1	621.9	657.5	702.7	718.0	722.1
20°	145.4	196.3	327.9	369.9	490.3	616.3	657.5	685.0	715.6	725.3	727.0
22.5°	130.0	182.5	332.8	376.4	512.9	638.9	673.6	695.4	716.4	719.6	720.5
25°	117.2	167.2	332.0	383.7	532.3	652.6	679.3	695.4	707.5	709.1	709.1
27.5°	105.0	150.2	328.7	385.3	546.8	655.9	676.8	688.2	693.8	697.1	697.1
30°	94.5	134.1	320.6	382.1	553.3	652.6	669.6	675.2	680.9	685.8	688.2
32.5°	86.4	118.8	308.5	375.6	554.1	644.6	656.7	659.9	667.9	679.3	683.4
35°	79.2	103.4	294.8	366.7	549.3	631.6	639.7	643.0	659.1	676.0	681.7
37.5°	71.9	92.1	277.0	351.4	541.9	616.3	621.9	627.6	652.6	672.8	679.3
40°	64.6	82.4	256.1	334.4	530.7	597.7	602.6	611.4	644.6	667.9	674.4
42.5°	58.9	74.3	233.4	316.6	516.1	576.7	583.9	596.9	634.9	659.9	667.1
45°	54.1	66.2	209.2	292.4	497.5	554.9	565.4	583.1	623.5	647.8	654.2
47.5°	49.3	60.5	184.1	267.3	477.4	533.1	546.8	567.0	608.2	631.6	637.3
50°	45.2	54.9	159.2	240.7	455.5	509.7	525.8	546.8	588.8	610.6	617.9
52.5°	42.0	50.1	135.7	214.1	430.5	485.4	504.0	525.8	565.4	586.4	591.2
55°	38.8	46.0	115.5	185.7	404.6	459.6	479.8	500.8	539.5	557.3	560.6
57.5°	37.2	42.8	98.5	159.2	377.2	430.5	453.1	472.5	508.9	522.6	525.8
60°	34.8	40.4	85.6	136.5	347.3	403.0	422.5	441.8	472.5	483.8	486.2
62.5°	32.3	38.8	76.0	114.7	316.6	370.7	390.1	407.9	433.7	441.8	445.0
65°	30.7	37.2	68.7	98.5	285.1	336.8	356.2	371.5	392.5	400.6	402.2
67.5°	29.1	35.6	63.0	84.8	253.6	302.9	317.4	332.0	348.1	356.2	357.0
70°	26.7	33.9	58.1	75.1	221.3	264.1	276.2	291.6	304.5	308.5	311.0
72.5°	25.1	31.5	54.9	67.9	188.2	226.9	238.3	247.2	258.5	262.5	262.5
75°	22.6	28.3	51.7	60.5	154.3	185.7	195.5	204.4	213.2	214.9	212.4
77.5°	20.2	25.1	44.4	50.9	120.4	147.0	155.1	160.0	167.2	168.8	169.6
80°	16.9	21.8	34.8	39.6	87.2	108.2	113.9	118.0	124.4	124.4	126.0
82.5°	12.9	16.9	25.1	28.3	58.9	74.3	79.2	81.6	85.6	85.6	85.6
85°	8.1	10.5	16.1	18.5	35.6	45.2	48.5	49.3	52.5	53.3	53.3
87.5°	4.0	5.6	10.5	11.3	18.5	23.4	23.4	25.1	25.1	24.3	23.4
90°	3.7	6.7	9.7	10.4	16.4	24.3	28.3	25.2	19.0	14.2	14.2
92.5°	14.9	40.3	65.7	72.0	101.3	140.3	159.8	140.0	100.5	70.9	68.1
95°	35.8	82.3	128.7	140.4	249.3	394.5	467.1	416.8	316.2	240.8	232.3
97.5°	62.0	102.9	143.9	154.2	335.8	577.9	699.0	667.2	603.7	556.0	539.7
100°	82.1	119.3	156.5	165.8	367.3	636.0	770.3	772.6	777.3	780.8	761.4
102.5°	99.3	134.0	168.7	177.4	381.7	654.2	790.5	830.9	912.0	972.7	956.1
105°	128.5	157.9	187.3	194.6	392.4	656.3	788.2	879.0	1060.5	1196.7	1187.8
107.5°	158.4	185.7	213.1	219.9	394.4	627.1	743.4	870.1	1123.3	1313.2	1315.4
110°	178.5	203.2	227.9	234.1	391.4	601.2	706.1	847.6	1130.8	1343.1	1352.4



TEST NUMBER: P937051

CATALOG NUMBER: SQ4-FB-075U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	198.3	221.8	245.4	251.3	391.5	578.6	672.1	817.0	1106.7	1324.0	1338.3
115°	228.1	249.9	271.6	277.0	395.2	552.6	631.4	771.0	1050.1	1259.4	1279.2
117.5°	257.6	277.4	297.1	302.1	402.5	536.4	603.4	729.4	981.3	1170.2	1192.1
120°	274.8	293.4	312.0	316.6	408.5	530.9	592.2	707.3	937.4	1110.1	1131.4
122.5°	291.6	310.4	329.1	333.8	417.1	528.1	583.6	687.2	894.5	1049.9	1071.0
125°	317.3	334.4	351.6	355.8	428.6	525.7	574.3	662.3	838.4	970.4	989.8
127.5°	338.3	355.6	372.8	377.1	440.2	524.4	566.4	642.0	793.2	906.6	923.0
130°	349.5	368.1	386.6	391.3	448.7	525.2	563.5	630.8	765.3	866.3	881.4
132.5°	361.0	379.7	398.2	402.9	455.5	525.7	560.8	621.0	741.6	831.9	845.4
135°	378.2	395.2	412.1	416.4	463.0	525.2	556.3	606.7	707.7	783.3	795.0
137.5°	395.8	412.5	429.3	433.5	474.2	528.5	555.6	598.2	683.5	747.5	757.1
140°	410.3	425.8	441.2	445.1	481.1	529.0	552.9	589.8	663.5	718.8	727.7
142.5°	421.6	435.9	450.2	453.7	486.8	530.9	552.9	585.3	650.0	698.6	706.3
145°	438.8	451.2	463.6	466.7	494.2	530.9	549.3	575.8	628.7	668.3	674.1
147.5°	455.9	468.0	480.1	483.2	505.2	534.6	549.3	570.0	611.7	643.0	647.8
150°	467.1	478.0	489.0	491.8	510.9	536.5	549.3	566.8	602.0	628.4	632.4
152.5°	478.7	487.0	495.3	497.4	514.6	537.7	549.3	564.3	594.3	616.9	619.8
155°	495.9	502.0	508.1	509.7	522.8	540.4	549.3	561.2	585.1	603.1	605.0
157.5°	508.5	514.6	520.5	522.0	531.1	543.2	549.3	558.6	577.1	591.1	592.5
160°	517.1	521.8	526.4	527.6	534.8	544.4	549.3	557.2	573.1	585.1	585.9
162.5°	525.7	529.3	532.7	533.6	538.8	545.8	549.3	556.0	569.4	579.5	580.2
165°	535.0	538.3	541.4	542.2	544.5	547.6	549.3	554.1	563.7	570.9	571.7
167.5°	543.6	545.2	546.6	547.0	549.0	551.7	552.9	556.1	562.4	567.2	567.5
170°	549.3	550.8	552.2	552.6	552.7	552.9	552.9	556.1	562.4	567.2	567.2
172.5°	552.2	552.5	552.9	552.9	552.9	552.9	552.9	555.4	560.4	564.2	563.9
175°	556.3	556.3	556.3	556.3	555.2	553.7	552.9	554.6	557.7	560.1	560.1
177.5°	556.3	556.3	556.3	556.3	555.4	554.3	553.7	555.0	557.5	559.4	559.0
180°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3



TEST NUMBER: P937051

CATALOG NUMBER: SQ4-FB-075U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	251.2	251.2
2.5°	268.1	266.5
5°	344.9	346.5
7.5°	464.5	463.7
10°	577.5	584.7
12.5°	659.9	661.5
15°	710.0	713.2
17.5°	729.4	730.2
20°	730.2	728.6
22.5°	721.3	719.6
25°	710.8	710.0
27.5°	701.1	701.9
30°	697.1	699.5
32.5°	697.1	701.1
35°	698.7	702.7
37.5°	697.9	702.7
40°	694.6	700.3
42.5°	685.8	689.8
45°	672.0	676.8
47.5°	654.2	657.5
50°	631.6	634.9
52.5°	603.4	604.2
55°	569.4	572.7
57.5°	533.1	533.9
60°	492.7	495.1
62.5°	449.9	449.9
65°	404.6	406.2
67.5°	357.8	361.8
70°	310.2	311.0
72.5°	263.3	263.3
75°	214.9	215.7
77.5°	168.8	168.8
80°	125.2	126.0
82.5°	86.4	88.0
85°	54.1	54.1
87.5°	25.1	22.6
90°	14.2	14.2
92.5°	56.8	45.5
95°	198.1	163.9
97.5°	474.7	409.6
100°	683.8	606.3
102.5°	889.7	823.3
105°	1152.1	1116.4
107.5°	1324.0	1332.6
110°	1389.5	1426.7



TEST NUMBER: P937051

CATALOG NUMBER: SQ4-FB-075U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1395.4	1452.5
115°	1358.4	1437.5
117.5°	1279.9	1367.7
120°	1216.7	1302.0
122.5°	1155.1	1239.3
125°	1067.3	1144.8
127.5°	988.3	1053.7
130°	941.8	1002.1
132.5°	899.5	953.6
135°	841.6	888.3
137.5°	795.2	833.4
140°	763.4	799.1
142.5°	737.0	767.7
145°	697.4	720.6
147.5°	667.0	686.2
150°	647.9	663.5
152.5°	631.6	643.4
155°	612.8	620.6
157.5°	597.9	603.4
160°	589.0	592.2
162.5°	583.2	586.2
165°	574.9	578.0
167.5°	568.8	570.1
170°	567.2	567.2
172.5°	562.7	561.5
175°	560.1	560.1
177.5°	557.7	556.3
180°	556.3	556.3



TEST NUMBER: P937051
 CATALOG NUMBER: SQ4-FB-075U-050D-930-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.98	1.74	2.05	2.82	4.29	14.15	14.91	15.22	15.99	17.45
	3H	1.68	2.37	2.76	3.45	4.93	15.97	16.66	17.05	17.74	19.23
	4H	1.97	2.63	3.06	3.71	5.20	16.61	17.26	17.70	18.35	19.84
	6H	2.22	2.82	3.32	3.91	5.41	17.03	17.63	18.13	18.72	20.23
	8H	2.28	2.86	3.39	3.96	5.46	17.15	17.72	18.25	18.82	20.32
	12H	2.30	2.84	3.41	3.94	5.46	17.21	17.75	18.32	18.85	20.37
4H	2H	8.18	8.83	9.27	9.91	11.41	14.41	15.06	15.51	16.15	17.64
	3H	9.74	10.28	10.84	11.39	12.90	16.44	16.99	17.54	18.10	19.60
	4H	9.83	10.33	10.93	11.43	12.95	17.20	17.70	18.31	18.80	20.33
	6H	9.83	10.26	10.95	11.39	12.90	17.73	18.16	18.85	19.29	20.80
	8H	9.81	10.21	10.92	11.33	12.86	17.89	18.29	19.00	19.41	20.94
	12H	9.76	10.12	10.89	11.25	12.79	17.97	18.34	19.11	19.47	21.01
8H	4H	11.26	11.66	12.38	12.78	14.31	17.25	17.66	18.37	18.77	20.31
	6H	11.50	11.83	12.64	12.99	14.52	17.87	18.21	19.01	19.37	20.90
	8H	11.51	11.81	12.66	12.94	14.50	18.09	18.38	19.23	19.52	21.07
	12H	11.48	11.73	12.63	12.87	14.46	18.23	18.48	19.37	19.62	21.20
12H	4H	11.40	11.76	12.53	12.89	14.43	17.20	17.57	18.33	18.70	20.23
	6H	11.75	12.05	12.90	13.18	14.74	17.85	18.15	19.00	19.29	20.84
	8H	11.82	12.07	12.97	13.21	14.80	18.08	18.33	19.23	19.47	21.06