

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563264

Luminaire Tested: **SQ4-PP3-025U-125D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563264
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9291.9 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 101.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563264
CATALOG NUMBER: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563264

CATALOG NUMBER: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	111	111	111	111	102	102	102	94	94	94	87	87	87	83
1	106	101	97	94	101	97	94	91	90	87	85	84	81	79	77	76	74	71
2	96	89	82	77	92	86	80	75	79	75	71	74	70	67	68	66	63	60
3	88	78	71	65	84	76	69	63	70	65	60	65	61	57	61	57	54	51
4	81	70	61	55	77	67	60	54	63	56	51	58	53	49	55	50	47	44
5	74	62	54	48	71	60	52	47	56	50	45	53	47	43	49	45	41	38
6	69	56	48	42	66	54	46	41	51	44	39	48	42	37	45	40	36	34
7	64	51	43	37	61	49	42	36	46	40	35	44	38	33	41	36	32	30
8	59	46	38	33	57	45	37	32	42	36	31	40	34	30	38	33	29	27
9	55	43	35	29	53	41	34	29	39	32	28	37	31	27	35	30	26	24
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	32	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13974	13974	13974
5°	14077	13991	13942
10°	14053	13953	13892
15°	13960	13884	13808
20°	13867	13789	13685
25°	13703	13608	13473
30°	13449	13379	13209
35°	13097	13008	12843
40°	12679	12599	12455
45°	12332	12245	12125
50°	11890	11814	11699
55°	11274	11125	11039
60°	10263	9970	9920
65°	9041	8665	8636
70°	7807	7484	7484
75°	6720	6625	6531
80°	5924	5996	5855
85°	4637	5060	5060



TEST NUMBER: P563264

CATALOG NUMBER: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.4	3.1
10°-20°	817.9	8.8
20°-30°	1225.1	13.2
30°-40°	1437.0	15.5
40°-50°	1441.5	15.5
50°-60°	1229.7	13.2
60°-70°	802.0	8.6
70°-80°	402.4	4.3
80°-90°	112.6	1.2
90°-100°	115.6	1.2
100°-110°	303.9	3.3
110°-120°	315.1	3.4
120°-130°	252.8	2.7
130°-140°	198.3	2.1
140°-150°	152.2	1.6
150°-160°	109.6	1.2
160°-170°	67.1	0.7
170°-180°	22.7	0.2
0°-30°	2329.5	25.1
0°-40°	3766.4	40.5
0°-60°	6437.6	69.3
0°-90°	7754.6	83.5
90°-120°	734.6	7.9
90°-150°	1337.9	14.4
90°-180°	1537.0	16.5
0°-180°	9291.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3029	3029	3029	3029	3029	
5°	3040	3011	3021	3011	3011	289
15°	2923	2894	2907	2896	2891	825
25°	2692	2661	2674	2650	2647	1238
35°	2326	2302	2310	2283	2281	1453
45°	1890	1877	1877	1858	1858	1456
55°	1402	1397	1383	1375	1373	1246
65°	828	813	794	789	791	827
75°	377	377	372	369	366	409
85°	88	95	96	96	96	103
90°	2	4	12	6	6	5
95°	15	60	199	103	70	17
105°	55	83	336	510	476	58
115°	97	118	269	537	613	96
125°	135	152	245	414	488	120
135°	161	178	237	334	379	125
145°	187	199	234	285	307	117
155°	211	217	234	257	264	97
165°	228	231	234	243	246	64
175°	237	237	236	239	239	23
180°	237	237	237	237	237	

TEST NUMBER: P563264

CATALOG NUMBER: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3029.3	3029.3	3029.3	3029.3	3029.3
2.5°	3048.4	3023.5	3029.3	3024.7	3012.3
5°	3039.9	3011.3	3021.3	3010.7	3010.7
7.5°	3019.2	2988.0	2997.9	2987.3	2986.8
10°	3000.1	2968.9	2978.8	2968.2	2965.6
12.5°	2972.5	2941.3	2953.3	2940.6	2940.1
15°	2923.1	2894.5	2907.1	2896.4	2891.2
17.5°	2867.3	2836.2	2851.4	2836.5	2834.4
20°	2824.8	2793.7	2808.9	2787.7	2787.7
22.5°	2773.9	2742.7	2760.1	2732.5	2732.5
25°	2692.1	2660.9	2673.5	2649.6	2647.0
27.5°	2594.9	2564.3	2577.4	2550.3	2549.8
30°	2524.8	2496.3	2511.6	2482.3	2479.7
32.5°	2448.4	2421.9	2433.0	2403.7	2401.1
35°	2325.7	2302.4	2309.8	2283.2	2280.6
37.5°	2196.7	2172.8	2181.3	2158.4	2157.4
40°	2105.4	2089.8	2092.1	2073.4	2068.2
42.5°	2020.4	2002.7	2005.0	1986.4	1985.4
45°	1890.3	1877.3	1877.0	1858.5	1858.5
47.5°	1752.3	1742.4	1739.5	1724.1	1723.6
50°	1656.7	1648.9	1646.1	1632.7	1630.1
52.5°	1556.9	1553.2	1544.1	1532.9	1532.4
55°	1401.8	1396.6	1383.2	1375.2	1372.6
57.5°	1233.5	1223.1	1208.0	1196.4	1198.4
60°	1112.4	1102.0	1080.6	1075.2	1075.2
62.5°	995.6	983.1	961.6	954.3	958.4
65°	828.3	812.8	793.8	788.6	791.2
67.5°	676.5	662.5	642.0	641.9	639.8
70°	578.8	571.0	554.9	554.9	554.9
72.5°	491.7	488.1	476.3	476.2	474.2
75°	377.0	377.0	371.7	369.0	366.4
77.5°	282.5	283.5	280.9	278.1	273.5
80°	223.0	228.2	225.7	223.0	220.4
82.5°	167.8	173.0	172.6	167.8	167.3
85°	87.6	95.4	95.6	95.6	95.6
87.5°	23.7	32.6	36.4	35.2	37.3
90°	1.5	4.5	12.2	6.1	6.1
92.5°	6.4	30.8	68.1	30.2	19.5
95°	15.2	59.8	199.2	102.6	69.9
97.5°	26.5	65.7	298.0	237.0	174.5
100°	35.0	70.6	328.4	332.8	258.5
102.5°	42.3	75.6	336.9	414.5	350.9
105°	54.7	83.0	336.0	510.1	475.9
107.5°	67.5	93.7	316.8	559.7	568.0
110°	76.0	99.8	301.0	572.5	608.1

TEST NUMBER: P563264

CATALOG NUMBER: SQ4-PP3-025U-125D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	84.5	107.1	286.4	564.4	619.1
115°	97.3	118.1	269.1	536.9	612.7
117.5°	109.8	128.8	257.2	498.8	582.9
120°	117.1	134.9	252.4	473.2	554.9
122.5°	124.4	142.2	248.7	447.6	528.2
125°	135.3	151.7	244.8	413.7	488.0
127.5°	144.1	160.8	241.4	386.4	449.1
130°	149.0	166.8	240.2	369.2	427.2
132.5°	153.9	171.7	239.0	354.5	406.5
135°	161.2	177.5	237.2	334.0	378.6
137.5°	168.8	184.8	236.9	318.6	355.2
140°	174.8	189.7	235.7	306.4	340.6
142.5°	179.7	193.4	235.7	297.7	327.2
145°	187.0	198.9	234.1	284.8	307.1
147.5°	194.3	205.9	234.1	274.1	292.5
150°	199.2	209.6	234.1	267.9	282.8
152.5°	204.0	212.1	234.1	263.0	274.3
155°	211.3	217.3	234.1	257.1	264.5
157.5°	216.8	222.5	234.1	251.9	257.2
160°	220.5	224.9	234.1	249.4	252.4
162.5°	224.1	227.4	234.1	247.0	249.9
165°	228.1	231.0	234.1	243.3	246.3
167.5°	231.7	233.2	235.7	241.8	243.0
170°	234.1	235.6	235.7	241.7	241.7
172.5°	235.3	235.6	235.7	240.5	239.3
175°	237.2	237.2	235.7	238.7	238.7
177.5°	237.2	237.2	236.0	238.4	237.2
180°	237.2	237.2	237.2	237.2	237.2

(END OF REPORT)