

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563312

Luminaire Tested: **SQ4-PP3-050U-075D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563312
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-075D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7744.6 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 78.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563312
CATALOG NUMBER: SQ4-PP3-050U-075D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563312

CATALOG NUMBER: SQ4-PP3-050U-075D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	64	61	59	56	54	51	49	47	42
3	83	74	67	61	78	69	63	58	61	56	51	53	49	46	45	42	40	36
4	76	66	58	52	71	62	54	49	54	48	44	47	43	39	40	37	34	31
5	70	58	50	44	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	44	38	60	49	42	37	44	38	33	38	33	30	33	29	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	26	30	26	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	26	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8241	8241	8241
5°	8302	8251	8222
10°	8288	8229	8193
15°	8233	8188	8143
20°	8179	8133	8071
25°	8081	8025	7946
30°	7932	7890	7790
35°	7724	7671	7574
40°	7477	7430	7345
45°	7273	7222	7150
50°	7012	6967	6900
55°	6649	6561	6511
60°	6053	5880	5850
65°	5332	5111	5093
70°	4603	4413	4413
75°	3962	3907	3852
80°	3493	3536	3454
85°	2736	2985	2985



TEST NUMBER: P563312

CATALOG NUMBER: SQ4-PP3-050U-075D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.9	2.2
10°-20°	482.4	6.2
20°-30°	722.5	9.3
30°-40°	847.5	10.9
40°-50°	850.1	11.0
50°-60°	725.2	9.4
60°-70°	473.0	6.1
70°-80°	237.3	3.1
80°-90°	67.5	0.9
90°-100°	233.1	3.0
100°-110°	633.2	8.2
110°-120°	651.0	8.4
120°-130°	520.5	6.7
130°-140°	409.0	5.3
140°-150°	313.6	4.0
150°-160°	225.5	2.9
160°-170°	137.9	1.8
170°-180°	46.5	0.6
0°-30°	1373.8	17.7
0°-40°	2221.3	28.7
0°-60°	3796.6	49.0
0°-90°	4574.4	59.1
90°-120°	1517.2	19.6
90°-150°	2760.3	35.6
90°-180°	3170.0	40.9
0°-180°	7744.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1786	1786	1786	1786	1786	
5°	1793	1776	1782	1776	1776	170
15°	1724	1707	1714	1708	1705	486
25°	1588	1569	1577	1563	1561	730
35°	1372	1358	1362	1346	1345	857
45°	1115	1107	1107	1096	1096	858
55°	827	824	816	811	810	735
65°	488	479	468	465	467	488
75°	222	222	219	218	216	241
85°	52	56	56	56	56	61
90°	2	6	11	14	14	4
95°	34	128	406	177	119	36
105°	112	175	696	1060	998	119
115°	200	243	557	1109	1263	197
125°	275	313	504	850	1002	245
135°	331	368	490	692	781	256
145°	382	410	484	588	632	240
155°	432	448	481	528	543	199
165°	468	474	482	503	504	132
175°	486	487	484	490	489	46
180°	486	486	486	486	486	

TEST NUMBER: P563312

CATALOG NUMBER: SQ4-PP3-050U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1786.5	1786.5	1786.5	1786.5	1786.5
2.5°	1797.8	1783.1	1786.5	1783.9	1776.5
5°	1792.8	1776.0	1781.9	1775.6	1775.6
7.5°	1780.6	1762.2	1768.1	1761.8	1761.5
10°	1769.3	1751.0	1756.8	1750.5	1749.0
12.5°	1753.0	1734.7	1741.8	1734.2	1733.9
15°	1723.9	1707.1	1714.5	1708.2	1705.1
17.5°	1691.0	1672.7	1681.6	1672.8	1671.6
20°	1666.0	1647.6	1656.6	1644.1	1644.1
22.5°	1635.9	1617.5	1627.8	1611.5	1611.5
25°	1587.7	1569.3	1576.7	1562.6	1561.1
27.5°	1530.4	1512.3	1520.1	1504.1	1503.8
30°	1489.1	1472.2	1481.2	1464.0	1462.4
32.5°	1444.0	1428.3	1434.9	1417.6	1416.1
35°	1371.6	1357.8	1362.2	1346.5	1345.0
37.5°	1295.5	1281.4	1286.4	1273.0	1272.3
40°	1241.7	1232.5	1233.8	1222.8	1219.7
42.5°	1191.6	1181.1	1182.5	1171.5	1170.9
45°	1114.8	1107.2	1107.0	1096.0	1096.0
47.5°	1033.4	1027.6	1025.9	1016.8	1016.5
50°	977.0	972.4	970.8	962.9	961.4
52.5°	918.2	916.0	910.7	904.1	903.8
55°	826.7	823.7	815.8	811.0	809.5
57.5°	727.5	721.3	712.4	705.6	706.8
60°	656.1	649.9	637.3	634.1	634.1
62.5°	587.2	579.8	567.1	562.8	565.2
65°	488.5	479.3	468.2	465.1	466.6
67.5°	399.0	390.7	378.6	378.6	377.4
70°	341.3	336.7	327.2	327.2	327.2
72.5°	290.0	287.8	280.9	280.9	279.6
75°	222.3	222.3	219.2	217.6	216.1
77.5°	166.6	167.2	165.7	164.0	161.3
80°	131.5	134.6	133.1	131.5	130.0
82.5°	99.0	102.0	101.8	98.9	98.6
85°	51.7	56.3	56.4	56.4	56.4
87.5°	14.1	19.9	22.2	22.9	24.1
90°	1.6	6.1	10.9	14.1	14.1
92.5°	14.1	63.8	110.8	47.6	40.3
95°	34.3	127.5	405.9	176.7	118.7
97.5°	56.8	140.8	622.3	484.1	340.0
100°	71.8	149.7	688.5	697.9	563.6
102.5°	86.8	158.5	706.0	863.1	744.7
105°	112.4	175.0	696.3	1060.2	997.6
107.5°	138.9	194.2	656.0	1161.9	1179.3
110°	157.7	208.1	626.0	1182.0	1256.8

TEST NUMBER: P563312

CATALOG NUMBER: SQ4-PP3-050U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	173.9	221.8	596.1	1165.3	1278.0
115°	199.8	242.6	557.3	1108.8	1263.0
117.5°	224.2	265.1	532.7	1028.7	1202.4
120°	240.4	280.1	521.4	975.0	1147.5
122.5°	254.2	293.8	513.9	921.1	1087.5
125°	274.8	312.9	504.3	849.6	1002.3
127.5°	293.2	331.0	499.0	795.4	926.4
130°	304.4	341.1	496.5	761.4	878.9
132.5°	315.7	352.3	494.0	732.4	836.5
135°	331.0	367.6	490.2	692.1	780.6
137.5°	347.5	380.8	488.3	656.5	730.9
140°	357.5	389.6	487.1	633.8	701.0
142.5°	367.5	397.1	485.8	616.1	672.2
145°	382.5	410.0	484.0	588.0	632.3
147.5°	399.4	422.9	482.4	565.9	600.7
150°	410.6	430.4	482.4	553.3	580.8
152.5°	419.3	436.7	481.2	541.9	564.5
155°	432.4	447.7	480.8	528.0	543.3
157.5°	445.3	457.2	480.8	518.6	530.2
160°	452.7	463.4	480.8	512.3	521.4
162.5°	460.2	468.5	482.1	507.2	513.9
165°	468.4	474.5	482.4	502.7	504.3
167.5°	476.8	479.8	484.0	497.4	498.6
170°	479.3	482.3	484.0	494.9	494.9
172.5°	481.8	483.6	484.0	492.4	492.4
175°	485.5	487.1	484.0	490.2	488.7
177.5°	486.8	486.8	483.0	488.0	485.5
180°	485.5	485.5	485.5	485.5	485.5

(END OF REPORT)