

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937251

Luminaire Tested: SQ4-FB-075U-100D-930-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937251
REPORT IS A COMBINATION OF REPORTS P933511 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-100D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7437.4 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 76.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937251
CATALOG NUMBER: SQ4-FB-075U-100D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P937251

CATALOG NUMBER: SQ4-FB-075U-100D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	58	52
1	98	93	89	85	90	86	82	79	73	70	68	61	59	57	50	49	47	50	49	47	42
2	88	80	74	69	81	74	69	64	63	59	55	53	50	47	43	41	39	43	41	39	34
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	32	38	35	32	28
4	73	62	53	47	67	57	50	44	49	43	38	41	36	33	33	30	27	33	30	27	24
5	67	55	46	40	61	51	43	37	43	37	33	36	32	28	30	26	23	30	26	23	20
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	27	23	20	27	23	20	17
7	56	44	35	30	52	41	33	28	35	29	24	29	25	21	24	20	18	24	20	18	15
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16	22	18	16	13
9	49	36	28	23	45	33	26	22	29	23	19	24	20	16	20	17	14	20	17	14	12
10	45	33	25	20	42	31	24	19	26	21	17	22	18	15	19	15	12	19	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3062	3062	3062
5°	2990	3537	4115
10°	2711	5156	6822
15°	2304	6735	8238
20°	1874	7802	8396
25°	1563	8163	8225
30°	1317	8211	8210
35°	1164	8073	8422
40°	1014	7894	8641
45°	917	7762	8675
50°	841	7642	8532
55°	805	7469	8154
60°	823	7137	7556
65°	855	6635	6735
70°	908	5783	5691
75°	1004	4711	4441
80°	1087	3263	2993
85°	948	1728	1531

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 8675 cd/sqm



TEST NUMBER: P937251

CATALOG NUMBER: SQ4-FB-075U-100D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.0	0.9
10°-20°	283.7	3.8
20°-30°	496.3	6.7
30°-40°	638.9	8.6
40°-50°	713.6	9.6
50°-60°	683.5	9.2
60°-70°	541.7	7.3
70°-80°	318.5	4.3
80°-90°	90.6	1.2
90°-100°	271.2	3.6
100°-110°	713.0	9.6
110°-120°	739.3	9.9
120°-130°	593.0	8.0
130°-140°	465.3	6.3
140°-150°	357.1	4.8
150°-160°	257.2	3.5
160°-170°	157.4	2.1
170°-180°	53.2	0.7
0°-30°	844.1	11.3
0°-40°	1483.0	19.9
0°-60°	2880.1	38.7
0°-90°	3830.8	51.5
90°-120°	1723.4	23.2
90°-150°	3138.8	42.2
90°-180°	3607.0	48.5
0°-180°	7437.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	482	517	582	659	683	45
15°	361	667	1124	1362	1405	101
25°	231	756	1338	1397	1399	106
35°	156	722	1260	1332	1384	97
45°	107	576	1114	1276	1334	82
55°	76	366	945	1098	1128	70
65°	60	194	702	789	800	60
75°	45	119	385	423	425	47
85°	16	37	96	105	107	17
90°	4	10	28	14	14	4
95°	36	140	467	241	164	40
105°	128	195	788	1197	1116	136
115°	228	277	631	1259	1438	225
125°	317	356	574	970	1145	282
135°	378	416	556	783	888	293
145°	439	467	549	668	721	275
155°	496	510	549	603	621	228
165°	535	542	549	571	578	151
175°	556	556	553	560	560	53
180°	556	556	556	556	556	



TEST NUMBER: P937251

CATALOG NUMBER: SQ4-FB-075U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	494.9	494.9	494.9	494.9	494.9	494.9	494.9	494.9	494.9	494.9	494.9
2.5°	494.9	494.9	498.1	499.7	502.8	504.4	507.7	510.9	520.3	522.0	525.2
5°	482.2	488.5	509.3	517.2	539.5	569.7	582.4	603.1	646.1	658.9	666.8
7.5°	463.1	477.4	528.4	541.1	596.8	676.4	709.8	754.3	822.8	856.2	883.2
10°	432.8	463.1	553.8	584.0	674.8	795.7	857.8	919.8	1023.3	1069.4	1086.9
12.5°	399.4	448.8	580.9	622.2	752.7	929.4	1004.2	1072.6	1190.4	1252.4	1262.0
15°	361.3	428.1	606.3	666.8	835.4	1040.8	1123.6	1207.9	1317.6	1362.2	1373.4
17.5°	327.9	412.2	630.2	693.9	899.1	1141.1	1225.4	1295.4	1384.5	1414.7	1422.7
20°	286.4	386.7	646.1	728.9	966.0	1214.2	1295.4	1349.5	1410.0	1429.1	1432.2
22.5°	256.2	359.7	655.6	741.6	1010.5	1258.8	1327.2	1370.2	1411.6	1417.9	1419.5
25°	230.8	329.4	654.0	755.9	1048.7	1285.8	1338.4	1370.2	1394.1	1397.2	1397.2
27.5°	206.9	296.0	647.7	759.1	1077.4	1292.2	1333.5	1355.9	1367.0	1373.4	1373.4
30°	186.2	264.2	631.8	752.7	1090.1	1285.8	1319.2	1330.4	1341.6	1351.0	1355.9
32.5°	170.3	233.9	607.9	740.0	1091.7	1269.9	1293.8	1300.1	1316.0	1338.4	1346.3
35°	155.9	203.7	580.9	722.5	1082.1	1244.5	1260.4	1266.7	1298.5	1332.0	1343.1
37.5°	141.6	181.4	545.9	692.3	1067.8	1214.2	1225.4	1236.5	1285.8	1325.6	1338.4
40°	127.3	162.3	504.4	658.9	1045.5	1177.6	1187.2	1204.7	1269.9	1316.0	1328.8
42.5°	116.2	146.4	459.9	623.9	1016.9	1136.2	1150.5	1176.0	1250.8	1300.1	1314.5
45°	106.6	130.5	412.2	576.1	980.3	1093.3	1114.0	1149.0	1228.5	1276.3	1289.1
47.5°	97.1	119.3	362.9	526.8	940.5	1050.3	1077.4	1117.1	1198.3	1244.5	1255.6
50°	89.1	108.2	313.5	474.3	897.5	1004.2	1036.0	1077.4	1160.1	1203.1	1217.4
52.5°	82.8	98.7	267.3	421.7	848.2	956.5	993.0	1036.0	1114.0	1155.4	1164.9
55°	76.4	90.7	227.6	366.0	797.3	905.5	945.3	986.6	1063.0	1098.0	1104.4
57.5°	73.2	84.3	194.2	313.5	743.2	848.2	892.8	931.0	1002.5	1029.6	1036.0
60°	68.4	79.6	168.7	268.9	684.3	794.1	832.3	870.5	931.0	953.2	958.0
62.5°	63.7	76.4	149.6	226.0	623.9	730.4	768.6	803.6	854.6	870.5	876.9
65°	60.5	73.2	135.3	194.2	561.8	663.6	701.8	732.0	773.4	789.3	792.5
67.5°	57.3	70.0	124.1	167.1	499.7	596.8	625.4	654.0	685.9	701.8	703.4
70°	52.5	66.8	114.6	148.0	436.0	520.3	544.3	574.5	599.9	607.9	612.7
72.5°	49.3	62.1	108.2	133.7	370.8	447.2	469.4	486.9	509.3	517.2	517.2
75°	44.6	55.7	101.8	119.3	303.9	366.0	385.1	402.6	420.1	423.3	418.5
77.5°	39.7	49.3	87.5	100.3	237.1	289.6	305.5	315.1	329.4	332.6	334.2
80°	33.4	43.0	68.4	78.0	171.8	213.3	224.4	232.3	245.1	245.1	248.3
82.5°	25.5	33.4	49.3	55.7	116.2	146.4	155.9	160.8	168.7	168.7	168.7
85°	15.9	20.7	31.8	36.6	70.0	89.1	95.5	97.1	103.4	105.0	105.0
87.5°	7.9	11.2	20.7	22.2	36.6	46.2	46.2	49.3	49.3	47.8	46.2
90°	3.7	6.7	9.7	10.4	16.4	24.3	28.3	25.2	19.0	14.2	14.2
92.5°	14.9	40.3	65.7	72.0	101.3	140.3	159.8	140.0	100.5	70.9	68.1
95°	35.8	82.3	128.7	140.4	249.3	394.5	467.1	416.8	316.2	240.8	232.3
97.5°	62.0	102.9	143.9	154.2	335.8	577.9	699.0	667.2	603.7	556.0	539.7
100°	82.1	119.3	156.5	165.8	367.3	636.0	770.3	772.6	777.3	780.8	761.4
102.5°	99.3	134.0	168.7	177.4	381.7	654.2	790.5	830.9	912.0	972.7	956.1
105°	128.5	157.9	187.3	194.6	392.4	656.3	788.2	879.0	1060.5	1196.7	1187.8
107.5°	158.4	185.7	213.1	219.9	394.4	627.1	743.4	870.1	1123.3	1313.2	1315.4
110°	178.5	203.2	227.9	234.1	391.4	601.2	706.1	847.6	1130.8	1343.1	1352.4



TEST NUMBER: P937251

CATALOG NUMBER: SQ4-FB-075U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	198.3	221.8	245.4	251.3	391.5	578.6	672.1	817.0	1106.7	1324.0	1338.3
115°	228.1	249.9	271.6	277.0	395.2	552.6	631.4	771.0	1050.1	1259.4	1279.2
117.5°	257.6	277.4	297.1	302.1	402.5	536.4	603.4	729.4	981.3	1170.2	1192.1
120°	274.8	293.4	312.0	316.6	408.5	530.9	592.2	707.3	937.4	1110.1	1131.4
122.5°	291.6	310.4	329.1	333.8	417.1	528.1	583.6	687.2	894.5	1049.9	1071.0
125°	317.3	334.4	351.6	355.8	428.6	525.7	574.3	662.3	838.4	970.4	989.8
127.5°	338.3	355.6	372.8	377.1	440.2	524.4	566.4	642.0	793.2	906.6	923.0
130°	349.5	368.1	386.6	391.3	448.7	525.2	563.5	630.8	765.3	866.3	881.4
132.5°	361.0	379.7	398.2	402.9	455.5	525.7	560.8	621.0	741.6	831.9	845.4
135°	378.2	395.2	412.1	416.4	463.0	525.2	556.3	606.7	707.7	783.3	795.0
137.5°	395.8	412.5	429.3	433.5	474.2	528.5	555.6	598.2	683.5	747.5	757.1
140°	410.3	425.8	441.2	445.1	481.1	529.0	552.9	589.8	663.5	718.8	727.7
142.5°	421.6	435.9	450.2	453.7	486.8	530.9	552.9	585.3	650.0	698.6	706.3
145°	438.8	451.2	463.6	466.7	494.2	530.9	549.3	575.8	628.7	668.3	674.1
147.5°	455.9	468.0	480.1	483.2	505.2	534.6	549.3	570.0	611.7	643.0	647.8
150°	467.1	478.0	489.0	491.8	510.9	536.5	549.3	566.8	602.0	628.4	632.4
152.5°	478.7	487.0	495.3	497.4	514.6	537.7	549.3	564.3	594.3	616.9	619.8
155°	495.9	502.0	508.1	509.7	522.8	540.4	549.3	561.2	585.1	603.1	605.0
157.5°	508.5	514.6	520.5	522.0	531.1	543.2	549.3	558.6	577.1	591.1	592.5
160°	517.1	521.8	526.4	527.6	534.8	544.4	549.3	557.2	573.1	585.1	585.9
162.5°	525.7	529.3	532.7	533.6	538.8	545.8	549.3	556.0	569.4	579.5	580.2
165°	535.0	538.3	541.4	542.2	544.5	547.6	549.3	554.1	563.7	570.9	571.7
167.5°	543.6	545.2	546.6	547.0	549.0	551.7	552.9	556.1	562.4	567.2	567.5
170°	549.3	550.8	552.2	552.6	552.7	552.9	552.9	556.1	562.4	567.2	567.2
172.5°	552.2	552.5	552.9	552.9	552.9	552.9	552.9	555.4	560.4	564.2	563.9
175°	556.3	556.3	556.3	556.3	555.2	553.7	552.9	554.6	557.7	560.1	560.1
177.5°	556.3	556.3	556.3	556.3	555.4	554.3	553.7	555.0	557.5	559.4	559.0
180°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3



TEST NUMBER: P937251

CATALOG NUMBER: SQ4-FB-075U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	494.9	494.9
2.5°	528.4	525.2
5°	679.5	682.7
7.5°	915.0	913.5
10°	1137.9	1152.1
12.5°	1300.1	1303.3
15°	1398.8	1405.2
17.5°	1437.0	1438.6
20°	1438.6	1435.4
22.5°	1421.1	1417.9
25°	1400.4	1398.8
27.5°	1381.3	1382.9
30°	1373.4	1378.1
32.5°	1373.4	1381.3
35°	1376.6	1384.5
37.5°	1375.0	1384.5
40°	1368.6	1379.7
42.5°	1351.0	1359.1
45°	1324.1	1333.5
47.5°	1289.1	1295.4
50°	1244.5	1250.8
52.5°	1188.8	1190.4
55°	1122.0	1128.3
57.5°	1050.3	1051.9
60°	970.7	975.5
62.5°	886.4	886.4
65°	797.3	800.4
67.5°	705.0	712.9
70°	611.1	612.7
72.5°	518.8	518.8
75°	423.3	424.9
77.5°	332.6	332.6
80°	246.7	248.3
82.5°	170.3	173.4
85°	106.6	106.6
87.5°	49.3	44.6
90°	14.2	14.2
92.5°	56.8	45.5
95°	198.1	163.9
97.5°	474.7	409.6
100°	683.8	606.3
102.5°	889.7	823.3
105°	1152.1	1116.4
107.5°	1324.0	1332.6
110°	1389.5	1426.7



TEST NUMBER: P937251

CATALOG NUMBER: SQ4-FB-075U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1395.4	1452.5
115°	1358.4	1437.5
117.5°	1279.9	1367.7
120°	1216.7	1302.0
122.5°	1155.1	1239.3
125°	1067.3	1144.8
127.5°	988.3	1053.7
130°	941.8	1002.1
132.5°	899.5	953.6
135°	841.6	888.3
137.5°	795.2	833.4
140°	763.4	799.1
142.5°	737.0	767.7
145°	697.4	720.6
147.5°	667.0	686.2
150°	647.9	663.5
152.5°	631.6	643.4
155°	612.8	620.6
157.5°	597.9	603.4
160°	589.0	592.2
162.5°	583.2	586.2
165°	574.9	578.0
167.5°	568.8	570.1
170°	567.2	567.2
172.5°	562.7	561.5
175°	560.1	560.1
177.5°	557.7	556.3
180°	556.3	556.3



TEST NUMBER: P937251
 CATALOG NUMBER: SQ4-FB-075U-100D-930-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.03	5.94	5.96	6.90	8.15	18.19	19.10	19.13	20.06	21.31
	3H	5.74	6.56	6.68	7.53	8.79	20.03	20.85	20.98	21.82	23.09
	4H	6.04	6.82	7.00	7.79	9.07	20.67	21.45	21.63	22.42	23.70
	6H	6.29	7.01	7.26	7.99	9.28	21.10	21.82	22.08	22.80	24.09
	8H	6.36	7.04	7.34	8.04	9.33	21.22	21.91	22.20	22.90	24.19
	12H	6.38	7.03	7.36	8.02	9.33	21.29	21.94	22.28	22.93	24.25
4H	2H	12.24	13.02	13.21	13.99	15.27	18.47	19.25	19.44	20.22	21.50
	3H	13.81	14.47	14.79	15.47	16.76	20.52	21.17	21.49	22.17	23.46
	4H	13.91	14.51	14.90	15.50	16.82	21.28	21.88	22.27	22.88	24.19
	6H	13.92	14.44	14.92	15.46	16.77	21.82	22.34	22.82	23.36	24.67
	8H	13.90	14.38	14.90	15.40	16.72	21.98	22.47	22.98	23.48	24.81
	12H	13.86	14.30	14.88	15.33	16.66	22.08	22.51	23.10	23.54	24.87
8H	4H	15.36	15.84	16.36	16.85	18.18	21.35	21.83	22.35	22.84	24.17
	6H	15.60	16.00	16.63	17.05	18.38	21.98	22.38	23.00	23.43	24.76
	8H	15.62	15.97	16.65	17.01	18.36	22.19	22.55	23.23	23.59	24.93
	12H	15.59	15.90	16.63	16.94	18.32	22.34	22.65	23.38	23.68	25.07
12H	4H	15.50	15.94	16.52	16.96	18.30	21.30	21.74	22.32	22.77	24.10
	6H	15.86	16.21	16.89	17.25	18.60	21.96	22.31	22.99	23.35	24.70
	8H	15.93	16.24	16.97	17.28	18.66	22.19	22.50	23.23	23.54	24.92